

OVERVIEW

Basic Upgradeable rPDUs provide reliable power distribution to critical IT equipment within a rack or cabinet.

Benefits

- With the Geist Upgradeable hot-swap technology, users may easily transform basic rPDUs to metered or monitored PDUs with the addition of the appropriate Interchangeable Monitoring Device (IMD).
- Reliable rack power distribution.
- Every unit is 100% tested for reliability and functionality.
- Simple and convenient configuration options for cord lengths and chassis colors.
- Standard three-year warranty, upgraded to a five-year warranty with product registration.



Part #: UI10028

Model Number: DU01X4B1-30CF17-2S02A9K00-S-A

Category: Basic

Sub Category: Upgradeable

Power Configuration: Variable, Variable, 22.0kW

Physical Configuration: 66in / 1683mm, Vertical

Product Summary: rPDU, Basic Upgradeable, 22.0kW, Variable Power Configuration, Vertical, (30) Combination C13/C19, Universal Inlet, Black Powder Coat.


Monitoring: No Monitoring (Upgradeable with IMD module)

Plug Form:



Universal Inlet

Receptacle:



Combination C13/C19
(Quantity: 30)

Chassis Color Options:



To discuss color options, contact your local sales representative.

Product Specification and Options

System Features

Monitoring	No Monitoring (Upgradeable with IMD module)
Maximum Input Power (Defined by Facility Side Cable)	63A Single Phase, 240V Max, 14.4kW 48A 3 Phase DELTA, 240V Max, 19.9kW 32A Three Phase WYE, 240/415V Max, 22.0kW

Frequency	50/60Hz
Over Current Protection	(6) 16A Double Pole Magnetic Breakers (10kAIC Rated)
Switch	Breaker/Switch Combination
Power Entry Location	Pivoting Connector
Plug Type	Universal Inlet
Alternating Phase/Circuits	Yes
Receptacle/Socket Type #1	Combination C13/C19
- Quantity on Face	30
- Quantity per Breaker	5
- Circuit Color ID	6 Circuit = Orange, Light Orange, Green, Light Green, Blue, Light Blue
- Style	Banks of 6
- Voltage per Receptacle/Socket	Defined by Facility Side Cable
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	Zero U
Toolless Mounting Hardware - Center to Center Spacing	49in and 61.25in / 1245mm and 1556mm
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	CE Marked
Certification/Agency Approvals	FCC Part 15 Class A Conformance
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL Listed 60950
Chassis Dimensions (LxWxD)	66.25in x 2in x 2.5in / 1682mm x 51mm x 64mm
Doghouse (D)	1.4in / 36mm
Shipped Weight	21lbs (9.53kg)