

## OVERVIEW

Basic Upgradeable rPDUs provide reliable power distribution to critical IT equipment within a rack or cabinet.

### Benefits

- With the Geist Upgradeable hot-swap technology, users may easily transform basic rPDUs to metered or monitored PDUs with the addition of the appropriate Interchangeable Monitoring Device (IMD).
- Reliable rack power distribution.
- Every unit is 100% tested for reliability and functionality.
- Simple and convenient configuration options for cord lengths and chassis colors.
- Standard three-year warranty, upgraded to a five-year warranty with product registration.



## Part #: UI10029

**Model Number:** DU01X5B1-48CF17-2S02A9K00-S-A

**Category:** Basic

**Sub Category:** Upgradeable

**Power Configuration:** Variable, Variable, 22.0kW

**Physical Configuration:** 66in / 1683mm, Vertical

**Product Summary:** rPDU, Basic Upgradeable, 22.0kW, Variable Power Configuration, Vertical, (48) Combination C13/C19, Universal Inlet, Black Powder Coat.

**Monitoring:** No Monitoring (Upgradeable with IMD module)

### Plug Form:



Universal Inlet

### Receptacle:



Combination C13/C19  
(Quantity: 48)

### Chassis Color Options:



To discuss color options, contact your local sales representative.

## Product Specification and Options

### System Features

<b>Monitoring</b>	No Monitoring (Upgradeable with IMD module)
<b>Maximum Input Power (Defined by Facility Side Cable)</b>	63A Single Phase, 240V Max, 14.4kW 48A 3 Phase DELTA, 240V Max, 19.9kW 32A Three Phase WYE, 240/415V Max, 22.0kW

<b>Frequency</b>	50/60Hz
<b>Over Current Protection</b>	(6) 16A Double Pole Magnetic Breakers (10kAIC Rated)
<b>Switch</b>	Breaker/Switch Combination
<b>Power Entry Location</b>	Pivoting Connector
<b>Plug Type</b>	Universal Inlet
<b>Alternating Phase/Circuits</b>	Yes
<b>Receptacle/Socket Type #1</b>	Combination C13/C19
<b>- Quantity on Face</b>	48
<b>- Quantity per Breaker</b>	8
<b>- Circuit Color ID</b>	6 Circuit = Orange, Light Orange, Green, Light Green, Blue, Light Blue
<b>- Style</b>	Banks of 6
<b>- Voltage per Receptacle/Socket</b>	Defined by Facility Side Cable
<b>Maximum Operating Temperature</b>	60C / 140F
<b>Heavy Steel - Powder Coat Finish</b>	Black
<b>Configuration</b>	Zero U
<b>Toolless Mounting Hardware - Center to Center Spacing</b>	49in and 61.25in / 1245mm and 1556mm
<b>Product Warranty</b>	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
<b>Certification/Agency Approvals</b>	CE Marked
<b>Certification/Agency Approvals</b>	FCC Part 15 Class A Conformance
<b>Certification/Agency Approvals</b>	RoHS Compliant
<b>Certification/Agency Approvals</b>	UL Listed 60950
<b>Chassis Dimensions (LxWxD)</b>	66.25in x 3.8in x 2.25in / 1683mm x 97mm x 57mm
<b>Shipped Weight</b>	25lbs (11.34kg)