

OVERVIEW

Basic rPDUs deliver reliable power to critical IT equipment within a rack or cabinet.

Benefits

- Reliable rack power distribution.
- Every unit is 100% tested for reliability and functionality.
- Simple and convenient configuration options for cord lengths and chassis colors.
- Standard three-year warranty, upgraded to a five-year warranty with product registration.



Part #: U1079

Model Number: DU00X5B1-48CF17-2S02A9K00-S-A

Category: Basic

Sub Category: Standard

Power Configuration: Variable, Max 22.0kW

Physical Configuration: 66in / 1683mm, Vertical

Product Summary: rPDU, Basic Standard, Max 22.0kW, Variable Power Configuration, Vertical, (48) Combination C13/C19, Universal Input, Black Powder Coat.

Plug Form:



Universal Input

Receptacle:



Combination C13/C19
(Quantity: 48)

Chassis Color Options:



To discuss color options, contact your local sales representative.

Product Specification and Options

System Features

Quantity Of Inputs	1
Maximum Input Power (Defined by Facility Side Cable)	63A Single Phase, 240V Max, 14.4kW 48A 3 Phase DELTA, 240V Max, 19.9kW 32A Three Phase WYE, 240/415V Max, 22.0kW
Frequency	50/60Hz
Over Current Protection	(6) 16A Double Pole Magnetic Breakers (10kAIC Rated)

Switch	Breaker/Switch Combination
Power Entry Location	Pivoting Connector
Plug Type	Universal Inlet
Alternating Phase/Circuits	Yes
Receptacle/Socket Type #1	Combination C13/C19
- Quantity on Face	48
- Quantity per Breaker	8
- Circuit Color ID	6 Circuit = Orange, Green, Blue, Light Orange, Light Green, Light Blue
- Style	Banks of 6
- Voltage per Receptacle/Socket	Defined by Facility Side Cable
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	Zero U
Toolless Mounting Hardware - Center to Center Spacing	49in and 61.25in / 1245mm and 1556mm
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	CE Marked
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL Listed 60950
Chassis Dimensions (LxWxD)	66.25in x 3.8in x 2.25in / 1683mm x 97mm x 57mm
Shipped Weight	25lbs (11.34kg)