

ASUSPRO Advanced Series | P3540

Compact and stamina-packed for business



Delivering a perfect blend of performance and mobility for business users, the compact 15.6-inch ASUSPRO P3540 combines long-lasting battery, legendary ASUSPRO durability, and slim bezels that give more screen in less space, making P3540 incredibly compact.

Productivity

Incredible power, anytime and anywhere

All-day battery life

P3540 gives you day-long power so you can get more done, wherever you are. Its high-capacity 70Wh battery can last up to 16 hours¹ on a single charge.

Comprehensive and reliable connections

P3540 has a comprehensive set of I/O ports for easy data transfers and versatile peripheral connections. For enhanced durability, the ports are solidly constructed and tested to endure over 5000 insertions.

Powerful performance

P3450 is powered by the latest 8th Gen Intel® Core™ processors, and offers an ultrafast SSD plus a high-capacity HDD, giving you responsive storage with no shortage of room for your files.

Faster, more stable Wi-Fi connection

P3540 includes Wi-Fi 5(802.11ac) for strong, stable signals and fast data transmission speeds. Plus, it is less prone to interference from other wireless devices operation on the same frequency band.

Design

Ultra-sophisticated design for business travelers

Maximum workspace, minimum burden

The compact, slim and 1.7kg-light design of P3540 makes it the perfect business travel companion, with its 15.6-inch NanoEdge display featuring extra-slim 5.6mm side bezels that maximize the size of the visual workspace while minimizing the overall footprint.

Robust and versatile 180° hinge

A full 180° of movement allows it to lay flat for easy screen sharing. The hinge is solidly mounted and torture-tested with 50,000 open/close cycles to ensure maximum durability.

Ergonomically designed keyboard

The exclusive ErgoLift hinge automatically tilts the keyboard to a comfortable typing position. The sculpted keycaps have a long 1.5mm travel giving a more responsive typing experience, and a numeric keypad is included for speedy data entry.

Reliability Designed to be tough

ASUSPRO P3540 is strongly built and undergoes stringent testing, ensuring it will survive whatever daily rigors, accidental impacts, or hostile environments.

Security Safeguard your data

ASUSPRO laptops provide multiple layers of security solutions to protect critical assets. ASUSPRO P3540 also introduces a brand-new webcam privacy shield that simply slides over the webcam to disable it for your privacy.

Management Simplify business process

ASUSPRO laptops are designed to help simplify asset-management processes for both MIS staff and end users through exclusive ASUS Business Manager and optional ASUS Control Center.

SPECIFICATIONS

P3540

Model	ASUSPRO P3540
Processor	Intel® Core™ i7 8565U Processor Intel® Core™ i5 8265U Processor Intel® Core™ i3 8145U Processor
Operating System	Windows 10 Pro (ASUS recommends Windows 10 Pro) Windows 10 Home
On Board Memory	DDR4 4GB (2400MHz)
Memory Slot	1
Memory Max.	up to DDR4 20G (2400MHz)
SSD	SATA3 128GB / 256GB / 512GB M.2 SSD
HDD	SATA 500GB / 1TB 5400RPM HDD SATA 500GB / 1TB 7200RPM HDD
EMMC / ISSD	N/A
Display	15.6" HD (1366x768), sRGB 62% (NTSC: 45%), Anti-Glare 15.6" FHD (1920x1080), sRGB 62% (NTSC: 45%), Anti-Glare 15.6" FHD IPS (1920x1080), sRGB 62% (NTSC: 45%), Anti-Glare
Touch Panel	N/A
External Video display Mode	HDMI 1.4
Discrete GPU	Nvidia MX110 + 2GB VRAM
Integrate GPU	Intel® UHD Graphics 620
Video Camera	HD 720p CMOS module
Fingerprint	Yes
Wireless	802.11ac + Bluetooth 4.2 (Dual band) 2x2
LAN	10/100/1000 Mbps
Card Reader	Spec: 3 in 1 (SD/ SDHC/ SDXC)
Interface	2 x USB3.1 Gen 1 Type-A ; 2 x USB3.1 Gen 1 Type-C ; 1 x HDMI out ; 1 x VGA port (D-sub) ; 1 X SD card reader 1 x RJ45 LAN Jack for LAN insert ; 1 x Headphone-out & Audio-in Combo Jack
Audio	Built-in microphone Built-in Stereo 2W Speakers
Weight	Starting from 1.7kg with Battery
Dimension	35.7 x 23.6 x 1.94 cm (W x H x D)
AC Adapter	65W AC Adapter, Plug Type : ø4.5 (mm) Output : 19 V DC, A, 65 W ; Input : 100 -240 V AC, 50/60 Hz universal
Battery	50WHrs, 3S1P, 3-cell Li-ion / 70WHrs, 4S1P, 4-cell Li-ion
Keyboard Type	Chiclet keyboard
Security	Kensington Lock Slot TPM 2.0 (Hardware TPM)
Certificates	UL, CE Marking Compliance, FCC Compliance, BSMI, CCC, CB, Energy star7.0, IDA, WEEE, Erp 2013, RoHS
Warranty	3-year limited International hardware warranty. (* different by country)

1. Battery life test configuration: Intel® Core™ i3-8145U, 4GB RAM, HD display, 500GB SATA SSD. Battery tests conducted by ASUS in December 2018 using the MobileMark® 2014 Office Productivity scenario. Test settings: Wi-Fi enabled, display brightness set to 83%. Actual battery life may vary depending on product configuration, usage, operational conditions and power management settings. Battery life will decrease over the lifetime of the battery.

2. All specifications are subject to change without notice. Please check with your supplier for exact offers.

3. Products may not be available in all markets.

4. Brand and product names mentioned are trademarks of their respective companies.

5. Product specifications may differ from country to country. We recommend that you check with your local dealers for the specifications of the products available in your country.

6. Colors of products may not be perfectly accurate due to variations caused by photography and monitor settings.

7. Although we endeavor to present the most accurate and comprehensive information at the time of publication, we reserve the right to make changes without prior notice.



Slim NanoEdge display




180° lay-flat hinge



Webcam privacy shield

OMNI-CONNECTIVITY

Multiple connections ensuring a seamless interface



3-Year international warranty

100% free of charge,
with no hidden costs.



Pick Up & Return service

Enjoy a door-to-door service
including pick up, repair, and return.



Warranty extension

Extend service coverage to match
the expected length of use time.

Disclaimer :

ASUSPRO Service Package may differ from country to country. We recommend that you check with your local dealers for the specifications of the products available in your country.

ASUSPRO