

Polacoat Da-Glas

Rear Projection Surface


The Da-Glas is a glass rigid rear projection screen with eight coating options formulated to fit your application requirements. The Da-Glas is a rigid rear projection screen, and coatings are permanently bonded to the substrate and cannot peel off.

Features

- Standard sizes up to 10' high X 20' wide
- Four factory framing options available:
 1. Base
 2. Standard
 3. Deluxe
 4. Self-trimming
- Larger sizes available upon request.

Optional Accessories:

- Light Baffles
- Green Laser Pointers
- Red Laser Pointers
- RF PowerPoint Remote with Green Laser Pointer



16:9 HDTV Format

Viewing Area (H x W)		Nominal Diagonal		Thickness	
in.	cm	in.	cm	in.	cm
40½" x 72"	103 x 183	82"	208	¼"	0.635
45" x 80"	114 x 203	92"	234	¼"	0.635
52" x 92"	132 x 234	106"	269	¼"	0.635
58" x 104"	147 x 366	119"	302	½"	1.27
65" x 116"	165 x 295	133"	338	½"	1.27
78" x 139"	198 x 353	159"	404	½"	1.27
94½" x 168"	240 x 427	193"	490	½"	1.27

16:10 Wide Format

Viewing Area (H x W)		Nominal Diagonal		Thickness	
in.	cm	in.	cm	in.	cm
50" x 80"	127 x 203	94"	239	¼"	0.635
57½" x 92"	146 x 234	109"	277	¼"	0.635
60" x 96"	152 x 244	113"	287	½"	1.27
65" x 104"	165 x 264	123"	312	½"	1.27
69" x 110"	175 x 279	130"	330	½"	1.27
72½" x 116"	184 x 295	137"	348	½"	1.27
87" x 139"	221 x 353	164"	417	½"	1.27

4:3 Video Format

Viewing Area (H x W)		Nominal Diagonal		Thickness	
in.	cm	in.	cm	in.	cm
43¼" x 57¾"	110 x 147	72"	183	¼"	0.635
50½" x 67¼"	128 x 171	84"	213	¼"	0.635
60" x 80"	152 x 203	100"	254	¼"	0.635
72" x 96"	183 x 244	120"	305	½"	1.27
81" x 108"	206 x 274	135"	343	½"	1.27
90" x 120"	229 x 305	150"	381	½"	1.27
108" x 144"	274 x 366	180"	457	½"	1.27

Available with the Following Optical Coatings



DA-50 WA

Half Angle: 43° Gain: 0.5



DA-75 WA

Half Angle: 78° Gain: 0.75



DA-100 WA

Half Angle: 52° Gain: 1.0



DA-100

Half Angle: 35° Gain: 1.0



DA-130

Half Angle: 34° Gain: 1.3




DA-150

Half Angle: 32° Gain: 1.5



DA-180

Half Angle: 30° Gain: 1.8



DA-230

Half Angle: 25° Gain: 2.3



Video Vision


Half Angle: 55° Gain: 1.0

Frame Options




Base Frame

- Mitered corners eliminate rear light leaks without caulking.
- Constructed of lightweight extruded aluminum U-channel.
- For 1/4" thick substrate only.
- Black anodized finish.
- Frame dimensions equal viewing area plus 2½".




Standard Frame

- Same great features as the deluxe frame but 1" x 1¾" base tube.
- Dovetail frame eliminates light leakage.
- For 1/4" thick substrate only.
- Black anodized finish.
- Frame insert size equals screen viewing area plus 4".



Deluxe Frame

- Impressive architectural design adds sophistication to any installation.
- 1¾" x 3" rectangular base tube.
- Dovetail frame eliminates light leakage.
- For screen panels up to 10' x 20'
- Black anodized finish.
- Frame insert size equals screen viewing area plus 5½".



Self-Trimming Frame

- Eliminates the need for finish trim for fast, easy installation.
- Built-in 1½" wide molding to hide opening.
- For screen panels up to 9' x 16'
- Black anodized finish.
- Frame insert size equals screen viewing area plus 2¾".



A BRAND OF MILESTONE AV TECHNOLOGIES | www.milestone.com

P 800.622.3737 / 574.267.8101 **F** 877.325.4832 / 574.267.804

E info@da-lite.com

In British Columbia, Milestone AV Technologies ULC carries on business as MAVT Milestone AV Technologies ULC.

©2018 Milestone AV Technologies. DL-0474 (Rev. 4) 0618.

Da-Lite is a registered trademark of Milestone AV Technologies. All other brand names or marks are used for identification purposes and are trademarks of their respective owners. All patents are protected under existing designations. Other patents pending.