



TAA 
COMPLIANT

15 Inch Fanless Dual Screen Touch POS

PC15-W41N-42P2

POS TOUCH

PC15 is a fanless with dual screen POS system that pushes the limits in modular design to the highest level. Every part of this POS system is design to be easily detachable, ensuring its users the ease of maintenance and longevity of the machine. The full-flat LCD monitor utilizes the advanced Projective Capacity Technology (PCT) and supports multi-touch operation.



1024 x 768 Resolution



PCAP Touch Technology



HDMI Digital Input



Dual Core Intel CPU



SATA III HDD Storage



IP65 Front Protection



TAA Compliant



3-Year Warranty

15" Fanless / Dual Screen Touch POS



FEATURES


- Fanless Design
- 6th / 7th Generation Intel® Core Processor
- DDR4 Memory, SATA 3.0, SATA III, RAID 0/1, Intel i-AMT
- Support Up To 2 External Signage Display
- Aluminum Back Cover for Optimal Thermal Dissipated
- IP65 / NEMA-4 Front Bezel Compliant
- Optional 10-Inch 2nd Display
- TAA Compliant
- 3-Year Warranty

SPECIFICATIONS


DISPLAY	PC15-W41N-42P
Screen Size	15 In
Resolution	1024 x 768
Touch Screen	10-Points PCAP Touch
Tilt Angle	15 to 80 degrees
MAIN BOARD	
CPU	Intel® i3-6100TE (2.7GHz, Dual Core, 4M Cache)
Chipset	Q170 Chipset
System Memory	2 DDR4 SO-DIMM Socket, up to 32GB
Graphic	Intel® HD Graphics
STORAGE	
HDD Type	1 x 2.5" SATA III
RAID	RAID 0 / 1
INTERFACE	
Parallel	1 x DB-25 Parallel Port
USB Ports	4 x USB 3.0, 2 x USB 2.0 or Power USB (1 x 12V/2A and 1 x 24V/3A)
Serial Ports	4 x COM (COM1/2 DB9 with RI/+5VDC Output by BIOS, COM3-4 8P8C with RI/+5VDC/ +12VDC Output by Jumper)
LAN	2 x RJ45, Giga LAN Support, 1 x Intel I219 LAN, RJ45, 1 x Realtek RTL811G, RJ45
VGA	1 x Reserved (MAX. Resolution: 1920 x 1080) for 2nd Display
HDMI	1 x HDMI
Cash Drawer	1 x RJ-11, +12VDC / +24VDC by Jumper Select
Audio	1 x Line Out
DC In / Out	1 x +12VDC / 1 x +12VDC
MECHANICAL	
Power Adapter	+12V/7.5A, 90W External Power, +12V/12.5A, 150W External Power (Option fo Power USB) 100VAC ~ 240VAC, 50/60Hz
Compliance	FCC/CE/LVD/BSMI/CB/WEEE/RoHS
Color	Black / White
TEMPERATURE	
Operating	32° F ~ 104° F (0° C ~ 40° C)
DIMENSIONS (WxHxD)	
Inch (in)	14.0 x 12.5 x 8.1
Millimeter (mm)	356 x 318 x 207
WEIGHT	
Net Weight	19.8 lbs (9kg)
OPTIONS	
Optional Peripheral	2nd Display
	MSR / EMB Reader, NFC, Chip Card Reader
	Barcode Reader

Specifications subject to change without any notice


INPUT AND ADVANTAGES



MSR or EMB reader slot



2nd display or custom display slot



Barcode reader slot

DIMENSIONS

Unit: Inch

