




## C32BD-A6-4000

GVision's CCTV security monitors are design for 24 / 7 / 365 operating. It support HDMI, VGA, BNC CVBS looping. C32BD security CCTV monitor is featured 3D Comb Filter, Anti-Pixel burn technology and display superior quality of picutre on the screen.

### DIMENSION

Unit: Inch



### FEATURES

- 32-Inch Screen Size
- 1920 x 1080 FHD Resolution
- BNC CVBS **Looping** Inputs
- Video Inputs: HDMI / VGA / BNC CVBS In / Out
- 3D Comb Filter / Noise Reduction / Anti Pixel Burn
- LED Backlight Unit
- 24/7 Operation Commercial CCTV Monitor
- 3-Year Warranty

1080P  
FULL HD

C32BD-A6-4000

DISPLAY	
Screen Size	32 In
Resolution	1920 x 1080
Active Area (mm)	701.7 x 396.3
Backlight	LED
Aspect Ratio	16 : 9
Viewing Angle	178° / 178°
Response Time	5ms (G2G)
Brightness	260cd/m <sup>2</sup>
Contrast Ratio	1000:1
Color Depth	16.7M
INTERFACE	
CVBS BNC In	1
CVBS BNC Out	1
HDMI In	1
VGA In	1
AUDIO	
Speaker	5W x 2
FEATURES	
Filter	3D combo filter
Noise Reduction	Yes
Anti Picture Burn-in	Yes
Remote Control	Yes
CABINET	
Color	Black
POWER	
Consumption	< 45W
Electrical Ratings	AC 100V ~ 240V, 50/60Hz
TEMPERATURE	
Operating	-4° F ~ 122° F (-20° C ~ 50° C)
Storage	-22° F ~ 158° F (-30° C ~ 70° C)
DIMENSIONS (WxHxD)	
Inch w/o Stand (in)	28.94 x 17.06 x 2.53
Millimeter w/o Stand (mm)	735.1 x 433.5 x 64.3
WEIGHT	
Net Weight	8.70 lbs (3.95 Kg)
VESA™	
Mount Size (mm)	100 x 100
ACCESSORY	
Accessories	Remote control, signal cable, user's manual, Power adaptor

Specifications subject to change without any notice