



LATITUDE 3310 FOR EDUCATION

Made to last beyond the bell



DESIGNED KID-PROOF

The Latitude 3310 is built to withstand the demands of the modern learning environment. It is designed with rounded corners and rubberized edges for drop protection. Additionally, it comes with captive keys for better pick resistance.



TESTED FOR ENDURANCE

Rigorously tested to stand up to the steep demands of student use. It survives 30-inch drops onto steel, tens of thousands of hinge-cycle tests, thousands of 4-inch microdrops from multiple angles, 12-ounce liquid spills on its spill-resistant keyboard, and it passes 15 MIL-STD 810G tests.



BUILT TO PERFORM

With up to 10 hours of battery life, this PC handles even the longest school days. Plus, students will power through any assignment with up to Intel Core i5 processors and DDR4 memory supporting up to 16GB.



CONSTRUCTED FOR COLLABORATION

A 180-degree hinge, as well as a 13.3" screen with optional Full High Definition Touch, help make collaboration a reality.

Recommended Accessories

LATITUDE 3310 FOR EDUCATION

ULTIMATE CLASSROOM SOLUTIONS



DELL COMPACT CHARGING CART | 36 DEVICES

Secure, charge and transport up to 36 laptops in a cart that easily rolls from one classroom to the next.



DELL 70 INTERACTIVE CONFERENCE ROOM MONITOR | C7017T

Ideal for collaboration, this interactive touch monitor with up to 10-point touch allows you to annotate with your fingers or write with a stylus. Presentations are displayed in crisp FHD resolution.

LEARNING ON-THE-GO



DELL ESSENTIAL SLEEVE 15

Wherever the school day takes you, protect your laptop from spills, bumps, and scratches with the water-resistant, form-fitting neoprene Dell Essential Sleeve 15.



DELL STEREO HEADSET | UC150

Students will experience great audio clarity with the Dell Pro Stereo Headset UC150 and can get started right away with plug and play technology.



DELL MOBILE WIRELESS MOUSE | MS3320W

Work seamlessly with dual mode connectivity (2.4GHz wireless or bluetooth) and 36 months* battery life.

Features & Technical Specifications

LATITUDE 3310

Feature	Latitude 3310 Technical Specifications ¹
Processors ¹	Intel® Celeron DC, Pentium DC, Core i3 & Core i5 Processors
Operating System Options ¹	Microsoft® Windows 10 Pro 64 bit Microsoft® Windows 10 Home 64 bit Microsoft® Windows 10 S Mode Ubuntu
Memory Options ^{1,2,3}	DDR4 2133MHz & 2400MHz; supporting up to 16GB
Chipset ¹	Integrated with the Processor
Graphics ^{1,13}	Intel® HD Graphics
Display ¹	13.3" HD (1366 x 768) Non-Touch Anti-Glare, Camera & Microphone, WLAN Capable 13.3" FHD (1920 x 1080) Embedded Touch, Camera & Microphone, WLAN Capable
Storage Options ^{1,3}	64GB eMMC ; 128GB SSD ; 256GB SSD
Security ¹	Intel PTT Dell Client Command Suite Dell BIOS Verification Optional Dell Endpoint Security and Management Software VMware Carbon Black Endpoint Standard VMware Carbon Black Endpoint Standard + Secureworks Threat Detection and Response Dell Encryption Enterprise Dell Encryption Personal Carbonite VMware Workspace ONE Absolute® Endpoint Visibility and Control Netskope Dell Supply Chain Defense
Docking ¹	Optional USB or USB Type-C Dock available
Optical Drive Options	External Options Only
Multimedia ¹	High Quality Speakers Headset/mic combo jack Integrated webcam with microphone
Battery Options ^{1,5}	3 Cell 42Whr ExpressCharge™ Capable Battery 4 Cell 56Whr ExpressCharge™ Capable Battery 4 Cell 56Whr Long Life Battery (includes 3 year limited hardware warranty)
Power Options ¹	65W adapter, 7.4mm barrel
Connectivity Options	RJ45 Ethernet: 10/100/1000 Wireless LAN: Intel® Dual Band Wireless AC 9560 (802.11ac) 2x2 + Bluetooth 5.0
Ports, Slots & Chassis ¹	2 USB 3.1 Gen 1 1 USB Type-C (Intel® Celeron, No USB Type-C) HDMI RJ45 Micro SD Card Reader Headphone/Microphone Combo Jack Wedge-Shaped Lock Slot
Dimensions & Weight ^{1,15}	Width: 12.98" / 329.6mm Height: 0.88" / 22.3mm Depth: 9.07" / 230.5mm Starting weight: 1.56Kg/3.45lbs
Regulatory and Environmental Compliance ¹	Regulatory Model: P95G Regulatory Type: P95G002 ENERGY STAR 7.0 ¹ EPEAT Bronze Registered. For specific country participation and rating, please see www.epeat.net BFR/PVC free ⁹ TCO NB 8.0
Input ¹	Spill and Pick resistant keyboard ; Multi-touch Touchpad
Warranty and Service ¹	Limited Hardware Warranty ⁴ Standard 1 year Mail-in Service after Remote Diagnosis ¹¹ optional 3, 4 and 5 year hardware warranty extensions and 3-5 year Dell ProSupport contracts available ¹²
Peripheral Ecosystem ¹	Purpose built ecosystem to enable productivity on the go or in the classroom. Includes Dell Cases, Dell Mobile Carts, and Dell Interactive Touch Monitors



LATITUDE 3310 FOR EDUCATION

Made to last beyond the bell

1 Offering may vary by country and by configuration

2 A 64-bit operating system is required to support 4GB or more of system memory.

3 GB means 1 billion bytes and TB equals 1 trillion bytes; actual capacity varies with preloaded material and operating environment and will be less.

4 Limited Hardware Warranty: For copy of Limited Hardware Warranty, write Dell USA LP, Attn: Warranties, One Dell Way, Round Rock, TX 78682 or see www.dell.com/warranty

5 Battery support is dependent upon graphics support. Check technical guides for detailed support

6 COMPUTRACE Not a Dell offer. Certain conditions apply. For full details, see terms and conditions at www.absolute.com/en/about/legal/agreements.

7 Intel Rapid Storage Technology requires a HDD, mSATA, or an SSD, as primary storage device and Windows OS required

8 Wireless antenna available only at time of system purchase

9 Dell Education Series are brominated flame retardant free (BFR-free) and polyvinyl chloride free (PVC-free); meeting the definition of BFR-/PVC-free as set forth in the iNEMI Position Statement on the 'Definition of Low-Halogen Electronics (BFR-/CFR-/PVC-free)'. Plastic parts contain less than 1,000 ppm (0.1%) of bromine (if the Br source is from BFRs) and less than 1,000 ppm (0.1%) of chlorine (if the Cl source is from CFRs or PVC or PVC copolymers). All printed circuit board (PCB) and substrate laminates contain bromine/chlorine total less than 1,500 ppm (0.15%) with a maximum chlorine of 900 ppm (0.09%) and maximum bromine being 900 ppm (0.09%).

10 Mobile Broadband Subject to service provider's broadband subscription and coverage area; additional charges apply.

11 Onsite Service after Remote Diagnosis: Remote Diagnosis is determination by online/phone technician of cause of issue; may involve customer access to inside of system and multiple or extended sessions. If issue is covered by Limited Hardware Warranty (www.dell.com/warranty) and not resolved remotely, technician and/or part will be dispatched, usually within 1 business day following completion of Remote Diagnosis. Availability varies. Other conditions apply.

12 Dell Services: Availability and terms of Dell Services vary by region. For more information, visit www.dell.com/servicedescriptions.

13 GB means 1 billion bytes and TB equals 1 trillion bytes; significant system memory may be used to support graphics, depending on system memory size and other factors.

14 Miracast Wireless Technology: Requires a compatible media adapter (sold separately) and an HDMI-enabled display.

15 Weights vary depending on configuration and manufacturing variability.

* Based on Dell internal analysis of battery life usage model calculations, Nov 2019. Results vary depending on usage and computing conditions.