

HP ScanJet Pro 3000 s4 Sheet-feed Scanner (6FW07A)



Get fast, two-sided scans in a single pass—recommended for 4000 pages per day.

Fast, affordable, and designed to handle everything from simple color jobs to complex workflows. Quickly and reliably digitize larger projects with scan speeds up to 40 ppm/80 ipm and a 50-page ADF. [1] Recommended for 4,000 pages per day.



Small size. Fast scans. Same reliable results.

Produce scans at up to 40 ppm/80 ipm[1] with two-sided scanning that captures both sides at once.

Optimize workflows with one-touch scanning

Streamline routine work with one-touch scanning—create one-button, custom settings for recurring scan jobs.

Capture business documents like a pro

Define scan profiles for common document types, and scan to multiple destinations with HP Scan software.

Featuring



One-pass duplex scanning

One-touch scanning

4000-page duty cycle

HP Scan software

50-page ADF

Compact size

Specifications

Scanner advanced features	HP EveryPage (Ultrasonic sensor), Auto-color detect, auto-crop, auto-exposure, auto orient, OCR, zonal OCR, zonal barcode, edge removal, background cleanup, remove hole, color drop out, straighten the page, scan to cloud, scan to email, PDF security, misfeed detection advance setting, Citrix Ready
Connectivity, standard	USB 3.0
Software included	Windows: HP WIA scan driver, HP TWAIN scan driver (32-bit and 64-bit), HP Scan, HP Scanner Tools Utility, I.R.I.S Readiris Pro, I.R.I.S Cardiris, OpenText ISIS
Compatible Operating Systems	Microsoft® Windows® (10, 8.1, 7, XP: 32-bit and 64-bit, 2008 R2, 2012 R2, 2016, 2019); MacOS (Catalina 10.15, Mojave 10.14, High Sierra 10.13); Linux (Ubuntu, Fedora, Debian, RHEL, Linux Mint, Open Suse, Manjaro); Citrix ready
Environmental	RoHS-Compliant
Energy star certified	Yes
Energy efficiency	CECP; ENERGY STAR® 3.0 certified; EPEAT® Silver
Digital sending standard features	Scan to PC, Scan to USB Drive
Scan file format	For text & images: PDF, PDF/A, Encrypted PDF, JPEG, PNG, BMP, TIFF, Word, Excel, PowerPoint, Text (.txt), Rich Text (.rtf) and Searchable PDF
Scan input modes	One default scan mode on front-panel for HP scan in Win OS, HP Easy Scan/ICA in Mac OS and third parties applications via TWAIN, ISIS and WIA
Scan technology	CMOS CIS (Contact Image Sensor)
Scanner type	Sheetfed
Minimum dimensions (W x D x H)	300 x 172 x 154 mm
Minimum dimensions (W x D x H)	11.8 x 6.8 x 6.1 in
Weight	2.7 kg
Weight	6.0 lb
Power consumption	4.4 Watts (ready), 24 Watts (scanning), 1.1 Watts (sleep), 0.1 Watts (auto-off), 0.1 Watts (off) ^[1] (Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. Energy Star value typically based on measurement of 115V device.)
Power supply type	External power adapter
What's in the box	Power cord; Power Adapter; USB Cable; Scanner Engine; Flyers; Install Guide
Services (Care Pack)	U9JR0E - HP 3 year Standard Exchange Scanjet Pro 3xxx Service; U9JR1E - HP 3 year Next Business Day Exchange Scanjet Pro 3xxx Service; U9JR2E - HP 3 year Next Business Day Onsite Exchange Scanjet Pro 3xxx Service; U9JR3E - HP 3 year Return to Depot Scanjet Pro 3xxx Service; U9JR4PE - HP 1 year Post Warranty Standard Exchange Scanjet Pro 3xxx Service; U9JR5PE - HP 1 year Post Warranty Next Business Day Exchange Scanjet Pro 3xxx Service; U9JR6PE - HP 1 year Post Warranty Next Business Day Onsite Exchange Scanjet Pro 3xxx Service; U9JR7PE - HP 1 year Post Warranty Return to Depot Scanjet Pro 3xxx Service; U9JT1E - HP Installation Service wireless/network Personal Scanner & Printer
Warranty	One-year bench limited warranty whole unit replacement, phone and Web support included. Warranty may vary by country as required by law. Go to hp.com/support to learn about HP world-class service and support options in your region.

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

[1] Scan speed measured at 300 dpi (black-and-white, grayscale, and color). Actual processing speeds may vary depending on scan resolution, network conditions, computer performance, and application software.

Technical Specifications Footnotes

[1] Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. Energy Star value typically based on measurement of 115V device.

© Copyright 2020 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

