



HP ScanJet Enterprise Flow 5000 s5 (6FW09A)



Overview

Give your office high-volume scanning performance. Recommended for 7500 pages per day.

Give your office powerful scan speed and accuracy. Built-in software and an 80-page automatic document feeder help you save time. Scan at up to 65 ppm/130 ipm.[2] Recommended for 7,500 pages per day.

Fast, smooth scanning—even unattended

Capture entire documents with one-pass duplex scanning up to 130 ipm.[1,2]

Professional-grade scanning that helps save time

Save time and simplify complex scan jobs with HP Scan Premium

Peak workflow performance. Smarter scanning.

Identify new devices and gain insight into scanning with HP Web Jetadmin remote discovery and monitoring.[4]

Features



One-pass duplex scanning

7500-page duty cycle



HP EveryPage, ultrasonic sensor

80-page ADF



HP Scan Premium

Scan originals in a variety of sizes and weights

[1] Black-and-white scan speed measured at 300 dpi using included HP Scan Premium. Actual processing speeds may vary depending on scan resolution, network conditions, computer performance, and application software.

[2] Color scan speed measured at 300 dpi. Actual processing speeds may vary depending on scan resolution, network conditions, computer performance, and application software.

[4] HP Web Jetadmin is available for download at no additional charge at <http://www.hp.com/go/webjetadmin>

Specifications

| | |
|--|--|
| Scanner advanced features | Auto exposure, Auto threshold, Auto detect color, Background smooth/removal, Auto detect size, Straighten content, Enhance content, Multi-streaming, Auto feed, Multi-feed detection sensor, Advanced multi-feed detection, Auto orient, Multi-color dropout, Channel color dropout, Edge erase, Delete blank page, Merge pages, Hole fill, Digital stamps, Metadata capture, PDF permissions, Document separation (Blank page, Barcode, Zonal barcode, Zonal OCR) |
| Connectivity, standard | USB 3.0 |
| Software included | Windows: HP WIA scan driver, HP TWAIN scan driver (32-bit and 64-bit), HP Scan Premium, HP Scanner Tools Utility, OpenText ISIS |
| Compatible Operating Systems | Microsoft® Windows® (10, 8.1, 7, XP: 32-bit and 64-bit, 2008 R2, 2012 R2, 2016, 2019); MacOS (Catalina 10.15, Mojave 10.14, High Sierra 10.13); Linux (Ubuntu, Fedora, Debian, RHEL, Linux Mint, Open Suse, Manjaro) |
| Sustainable impact specifications | RoHS-compliant |
| Energy star certified | Yes |
| Ecolabels | CECP; ENERGY STAR® 3.0 certified; EPEAT® Silver ^[2] |
| Digital sending standard features | Scan to PC, Scan to USB Drive |
| Scan file format | For text & images: PDF, PDF/A, Encrypted PDF, JPEG, PNG, BMP, TIFF, Word, Excel, PowerPoint, Text (.txt), Rich Text (.rtf) and Searchable PDF |
| Scan input modes | Two scan modes (simplex/duplex) with convenient 2x16 character LCD on front-panel for HP scan in Win OS, HP Easy Scan/ICA in Mac OS and third parties applications via TWAIN, ISIS and WIA |
| Scan technology | CMOS CIS (Contact Image Sensor) |
| Scanner type | Sheetfed |
| Display | 2-line 16 character per line LCD display |
| Minimum dimensions (W x D x H) | 310 x 198 x 190 mm |
| Minimum dimensions (W x D x H) | 12.2 x 7.8 x 7.5 in |
| Weight | 3.8 kg |
| Weight | 8.4 lb |
| Power consumption | 4.1 watts (ready), 38 Watts (scanning), 1.3 watts (sleep), 0.1 watts (off), 0.1 watts (auto-off) ^[1] <i>(Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. Energy Star value typically based on measurement of 115V device.)</i> |
| Power supply type | External power adapter |
| What's in the box | Power cord; Power Adapter; USB Cable; Scanner Engine; Flyers; Install Guide |
| Manufacturer Warranty | One-year bench limited warranty whole unit replacement, phone and Web support included. Warranty may vary by country as required by law. Go to hp.com/support to learn about HP world-class service and support options in your region. |

Additional specifications

| | |
|--|--|
| Accessories | HP SJ 5000 s4/7000 s3 Roller Replacement Kit (L2756A : 100,000 sheets); HP 5-pack Carrier Sheet Kit (8PA50A); 10 Pack Cleaning Cloth Kit (C9943B) |
| Acoustic power emissions (active, printing) | 65 (dB), 6.5 (B) |
| Automatic document feeder capacity | Standard, 80 sheets |
| Automatic document feeder scan speed | Up to 65ppm/130 ipm |
| Automatic document feeder scan speed | Up to 65ppm/130 ipm |
| Bit depth | 24-bit (external), 48-bit (internal) |
| Business filter | cMPS |
| Cable included | Power cord; power adapter; USB cable |
| Cartons per layer | 12 |
| Color scanning | Yes |
| Component type | Printer |
| Control panel | 2-line 16 character per line LCD display, Simplex button, Duplex button, Cancel button, Power button with a LED, Up button, Down button and Tool button |
| Count of layers in pallet | 6 |
| Country of origin | Made in China |
| Duplex ADF scanning | Yes |
| Duty cycle (daily) | Recommended daily duty cycle: 7500 pages |
| Ecolabels footnote | EPEAT® registered where applicable. EPEAT registration varies by country. See http://www.epeat.net for registration status by country. |
| Electromagnetic compatibility | CISPR 22:2008 & CISPR 32: 2012/ EN 55032:2012 - Class B, EN 61000-3-2: 2014, EN 61000-3-3: 2013, EN 55024: 2010, FCC Title 47 CFR, Part 15 Class B / ICES-003, Issue 6, GB9254-2008, GB17625.1-2012 |
| Levels of grayscale | 256 |
| Light source (scanning) | LED |
| Mac compatible | Yes |
| Maximum dimensions (W x D x H) | 12.2 x 17.7 x 12.6 in |
| Maximum dimensions (W x D x H) | 310 x 448 x 319 mm |
| Media size (ADF) | U.S.-Letter: 215.9 x 279.4 mm (8.5 x 11 in); U.S.-Legal: 215.9 x 355.6 mm (8.5 x 14 in); U.S.-Executive: 184.2 x 266.7 mm (7.25 x 10.5 in); ISO A4: 210 x 297 mm (8.3 x 11.7 in); JIS B5: 182 x 257 mm (7.2 x 10.1 in); ISO B5: 176 x 250 mm (7.0 x 9.9 in); ISO A5: 148 x 210 mm (5.8 x 8.3 in); ISO A6: 105 x 148 mm (5.8 x 4.1 in); ISO A7: 74 x 104 mm (2.9 x 4.1 in); ISO A8: 52 x 74 mm (2.0 x 2.9 in); Custom: 5.08 x 7.36 cm to 21.6 x 309.9 cm (2.0 x 2.9 in to 8.5 x 122 in) |

| | |
|--|---|
| Media types | Cut Sheet Paper, Printed Paper (Laser and ink), Pre-Punched Paper, Bank Checks, Business Cards, Freight Bills, Carbonless forms, Plastic Carrier sheets for easily damaged documents, Previously stapled media with staple removed, Plastic cards (up to 1.24 mm) |
| Media weights, supported ADF | 11.4 to 93.3 lb |
| Media weights, supported ADF | 43 to 350 g/m ² |
| Memory | 512 MB |
| Minimum System Requirements | macOS Catalina 10.15, macOS Mojave 10.14, macOS High Sierra 10.13, Microsoft® Windows® 10, 8.1, 7, XP: 32-bit and 64-bit, 2008 R2, 2012 R2, 2016, 2019, 2 GB available hard disk space, CD-ROM/DVD drive or Internet connection, USB port, Microsoft® Internet Explorer |
| Minimum System Requirements for Macintosh | macOS Catalina 10.15, macOS Mojave 10.14, macOS High Sierra 10.13; 1 GB HD; Internet required; USB |
| Multifeed detection | Yes |
| Operating humidity range | 15 to 80% RH |
| Operating temperature range | 10 to 35°C |
| Operating temperature range | 50 to 95°F |
| Output resolution dpi settings | 75; 150; 200; 240; 300; 400; 500; 600; 1200 ppi |
| Package dimensions (W x D x H) | 15.6 x 9.76 x 11.9 in |
| Package dimensions (W x D x H) | 397 x 248 x 303 mm |
| Package weight | 12.3 lb |
| Package weight | 5.6 kg |
| Pallet dimensions | 47.2 x 39.4 x 77.6 in |
| Pallet dimensions (W x D x H) | 1200 x 1000 x 1972 mm |
| Pallet weight | 939 lb |
| Pallet weight | 426 kg |
| Power | Input Voltage range: 90 - 264 VAC, Rated Frequency: 50 - 60HZ, Worldwide use |
| Printer black pages (MPV black) | 1260 |
| Printer color pages (MPV color) | 840 |
| Processor speed | ARM-1176 666 MHz |
| Product long name specifications | HP ScanJet Enterprise Flow 5000 s5 Scanner; Scan speed 65 ppm/130 ipm (@300 ppi BWGC); Max Resolution: ADF 600 x 600 ppi optical, ADF 1200 x 1200 ppi software; Up to 7,500 pages per daily duty cycle; 2-Lines LCD display + Buttons |
| Quantity per pallet | 72 |
| RMN number | SHNGD-1604 |
| Recommended operating humidity range | 30% to 70% relative humidity (RH) |
| Recommended operating temperature range | 17.5 to 25°C |

| | |
|--|--|
| Recommended operating temperature range | 63.5 to 77°F |
| Safety | IEC 60950-1:2005 +A1:2009+A2:2013/EN60950-1:2006 +A11:2009 +A1:2010+A12:2011+A2:2013; IEC 62479:2010 / EN 62479:2010; IEC 62471:2006/ EN62471:2008; GB4943-2011 |
| Scan resolution, hardware | 600 x 600 dpi |
| Scan resolution, optical | Up to 600 dpi |
| Scan size (ADF), maximum | 8.5 x 122 in |
| Scan size (ADF), maximum | 216 x 3100 mm |
| Scan size (ADF), minimum | 2 x 2 in |
| Scan size (ADF), minimum | 50.8 x 50.8 mm |
| Scan speed footnote | Sheet feed speeds: (All resolutions up to and including 300 ppi) Simplex 65 A-4 pages per minute Duplex 130 A-4 images per minute |
| Scanning options (ADF) | Single-pass duplex |
| Security management | Power button to on/off device |
| Storage temperature range | -40 to 140°F |
| Storage temperature range | -40 to 60°C |
| Tariff numbers | 8471608000 |
| Twain version | Windows: 32-bit and 64-bit TWAIN version 2.1; Mac: n/a |
| UNSPSC code | 43211711 |
| UPC number | (201) 193905029860; (AB2) 193905029921; (ABG) 193905029938; (ABT) 193905029884; (ABY) 193905029891; (AC4) 193905029976; (AC8) 193905029983; (ACJ) 193905029945; (ACQ) 193905029914; (AKV) 193905029990; (B13) 193905252657; (B19) 193905029877; (BAZ) 193905029907; (BBU) 193905029952; (BGJ) 193905029969 |

[1] Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. Energy Star value typically based on measurement of 115V device.

[2] EPEAT® registered where applicable. EPEAT registration varies by country. See <http://www.epeat.net> for registration status by country.

Ink/Toner/Paper/Printer Supplies

HP Maintenance Kits

★ : Recommended

HP ScanJet Maintenance Kits

| | |
|---|-----------------|
| HP ScanJet 5000 s4/7000 s3 Roller Replacement Kit | L2756A ★ |
| HP 5-pack Carrier Sheet Kit | 8PA50A |

Services

HP Care Pack Services

★ : Recommended

Imaging and Printing Commercial Care Pack Services

| | |
|--|---------|
| HP 1 year Post Warranty Next business day Exchange Scanjet 5000x Hardware Service | UH373PE |
| HP 1 year Post Warranty Next business day Onsite Exchange ScanJet 5000x Hardware Service | UH374PE |
| HP 3 year Next business day Exchange ScanJet 5000x Hardware Service | UH370E |
| HP 4 year Next business day Exchange Scanjet 5000x Service | U0MF6E |
| HP 5 year Next business day Exchange Scanjet 5000x Service | U0MF5E |
| HP Installation Service with network configuration for Workgroup Printer(1 unit) | U9JT2E |

Imaging and Printing Hardware Support Onsite Svc

| | |
|--|--------|
| HP 3 year Next business day Onsite Exchange ScanJet 5000x Hardware Service | UH372E |
| HP 4 year Next business day Onsite Exchange 5000x Hardware Support | U0MF7E |
| HP 5 year Next business day Onsite Exchange 5000x Hardware Support | U0QN0E |

Accessories

Maintenance and Cleaning Kits

★ : Recommended

Cleaning Kits

| | |
|-------------------------------|--------|
| HP ADF Cleaning Cloth Package | C9943B |
|-------------------------------|--------|

Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Aug 23, 2024 7:38 AM UTC+0000