



msi

MONITOR Optix G32C4



SPECIFICATION

Panel Size	31.5" (80cm)
Panel Resolution	1920 x 1080 (FHD)
Refresh Rate	165 Hz
Response time	1ms
Panel Type	Samsung VA
Brightness (nits)	250 nits
Viewing Angle	178° (H) / 178° (V)
Aspect Ratio	16:9
Curvature	1500R
Contrast Ratio	3000:1
DCR	100000000:1
Active Display Area (mm)	698.4(H) x 392.85(V)
Pixel Pitch (H x V)	0.36375(H) x 0.36375(V)
Surface Treatment	Anti-glare
Display Colors	16.7M
DCI-P3 / sRGB	95% / 120%
Video ports	1x DP (1.2a) 2x HDMI (1.4b)
Audio ports	1x Earphone out
Kensington Lock	Yes
VESA Mounting	100 x 100 mm
Control	5-way OSD navigation joystick
Power Type	External Adaptor 20V 3.25A
Power Input	100~240V, 50~60Hz
Power consumption	58W
Signal Frequency	53.28 to 183.15KHz (H) 48 to 165Hz (V)
Adjustment (Tilt)	-5° ~ 20°
Dimension (W x H x D)	709.4 x 509.5 x 248.9 mm / 27.93 x 20.06 x 9.8 inch
Weight (NW / GW)	6.4kg / 10.0kg 14.11lbs / 22.05lbs
Frameless Design	Yes
Note	Display Port: 1920 x 1080 (Up to 165Hz) HDMI: 1920 x 1080 (Up to 144Hz) The color gamut follows the CIE 1976 testing standard.

FEATURE



Curved Gaming

MSI Curved Gaming Monitor will give you the most immersive and competitive edge you need to take down your opponents.



165Hz High Refresh Rate

Experience smooth gaming with a blazing fast 165Hz refresh rate, that gives you the upperhand in fast moving games



1ms Fast Response Time

Eliminate screen tearing and choppy frame rates with 1ms response time.



Wide Color Gamut

Game colors and details will look more realistic and refined, to push game immersion to its limits.



Frameless Design

With the narrow bezel, you will not even notice the monitor at all in the heat of the moment.



FreeSync technology

AMD FreeSync® will prevent screen tearing or stuttering, producing ultra-smooth and lag-free gameplay.

CONNECTIONS



- 1. 5-way joystick navigator
- 2. 1x DC Jack
- 3. 2x HDMI 1.4b
- 4. 1x Display Port 1.2a
- 5. 1x Earphone out
- 6. 1x Kensington lock