

ProductSheet
HP DeskJet 2652 All-in-One Printer (V1N05A)



Save big with the wireless HP DeskJet 2600 All-in-One.

Save time and money with HP's most affordable wireless all-in-one printer to date. With a hassle-free setup and easy printing from your mobile devices, the HP DeskJet 2652 All-in-One removes the complications of your everyday printing needs.



Easily print from your mobile device.[1]

Easily print from a variety of smartphones and tablets.[1]

More ink. More savings.[2]

Print up to twice as many pages with Original HP high-yield ink cartridges.[2]

Wirelessly print, copy, and scan

Print, copy, and scan while saving money and space with a wireless all-in-one printer.

Featuring

Recycle today for a better tomorrow



Specifications

Print quality black (best)	Up to 1200 x 1200 rendered dpi
Print quality color (best)	Up to 4800 x 1200 optimized dpi color (when printing from a computer on selected HP photo papers and 1200 input dpi)
Print speed black (ISO, A4)	Up to 5.5 ppm
Print Speed Color (ISO)	Up to 5.5 ppm
Print speed color (ISO)	Up to 5.5 ppm
Print speed	Print speed up to 7.5 ppm (black) and 5.5 ppm (color)
Functions	Print, copy, scan
Duplex printing	Manual (driver support provided)
Duty cycle (monthly, A4)	Up to 1000 pages
Duty cycle (monthly, letter)	Up to 1000 pages
Printer smart software features	Manual Duplex
Replacement cartridges	HP 65 Black Ink Cartridge (~120 pages); HP 65 Tri-color Ink Cartridge (~100 pages); HP 65XL Black Ink Cartridge (~300 pages); HP 65XL Tri-color Ink Cartridge (~300 pages) ^[5]
Connectivity, standard	1 Hi-Speed USB 2.0
Network capabilities	Wifi
Wireless capability	Yes
Mobile printing capability	Apple AirPrint™; Chrome OS
Network protocols, supported	Wireless Network Supported
Compatible Operating Systems	Windows 11; Windows 10; Windows 8; Windows 8.1; Windows 7; Windows Vista; Windows Server; macOS 10.11 El Capitan; macOS 10.12 Sierra; Chrome OS
Sustainable impact specifications	None
Energy star certified	Yes
Ecolabels	ENERGY STAR® certified
Digital sending standard features	No
Scan file format	JPEG, TIFF, PDF, BMP, PNG
Scan input modes	Front-panel scan
Scan technology	Contact Image Sensor (CIS)
Scanner type	Flatbed
Display	Icon LCD display
Minimum dimensions (W x D x H)	425 x 304 x 149 mm
Minimum dimensions (W x D x H)	16.74 x 11.97 x 5.87 in
Weight	3.42 kg
Weight	7.55 lb
Power supply type	Internal
What's in the box	HP DeskJet 2652 All-in-One Printer; HP 65 Setup Black Ink Cartridge (~115 pages); HP 65 Setup Tri-color Ink Cartridge (tri-color composite yield ~100 pages); Regulatory flyer; Setup Poster; Bonus Software; Power cord; [For ink volume and page yield information, visit hp.com/go/learnaboutsupplies]
Manufacturer Warranty	One-year limited hardware warranty; 24-hour, 7 days a week support

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

[1]For details on local printing requirements see [hp.com/go/mobile printing](http://hp.com/go/mobile%20printing)

[2]Based on cartridge yields for HP 65/304XL ink cartridges compared with HP 65/304 standard ink cartridges. For more information, see <http://hp.com/go/learnaboutsupplies>

Technical Specifications Footnotes

[5] Average based on ISO/IEC 24711 or HP testing methodology and continuous printing. Actual yield varies considerably based on content of printed pages and other factors. For details see hp.com/go/learnaboutsupplies

Learn more at

hp.com

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

