eDatasheet HP ScanJet Enterprise Flow 5000 s5 (6FW09A)

Give your office high-volume scanning performance. Recommended for 7500 pages per day.

Give your office powerful scan speed and accuracy. Built-in software and an 80page automatic document feeder help you save time. Scan at up to 65 ppm/130 ipm.[2] Recommended for 7,500 pages per day.





Fast, smooth scanning—even unattended

Capture entire documents with one-pass duplex scanning up to 130 ipm.[1,2]

Peak workflow performance. Smarter scanning.

Identify new devices and gain insight into scanning with HP Web Jetadmin remote discovery and monitoring.[4]

Professional-grade scanning that helps save time

Save time and simplify complex scan jobs with HP Scan Premium

Featuring

One-pass duplex scanning

7500-page duty cycle

HP EveryPage, ultrasonic sensor

80-page ADF

HP Scan Premium

Scan originals in a variety of sizes and weights



Specifications

Scanner advanced features	Auto exposure, Auto threshold, Auto detect color, Background smooth/removal, Auto detect size, Straighten content, Enhance content, Multi-streaming, Auto feed, Multi-feed detection sensor, Advanced multi-feed detection, Auto orient, Multi-color dropout, Channel color dropout, Edge erase, Delete blank page, Merge pages, Hole fill, Digital stamps, Metadata capture, PDF permissions, PDF digital signatures, Document separation (Blank page, Barcode, Zonal barcode, Zonal OCR)
Connectivity, standard	USB 3.0
Software included	Windows: HP WIA scan driver, HP TWAIN scan driver (32-bit and 64-bit), HP Scan Premium, HP Scanner Tools Utility, I.R.I.S Readiris Pro, I.R.I.S Cardiris, OpenText ISIS
Compatible Operating Systems	Microsoft® Windows® (10, 8.1, 7, XP: 32-bit and 64-bit, 2008 R2, 2012 R2, 2016, 2019); MacOS (Catalina 10.15, Mojave 10.14, High Sierra 10.13); Linux (Ubuntu, Fedora, Debian, RHEL, Linux Mint, Open Suse, Manjaro)
Environmental	RoHS-compliant
Energy star certified	Yes
Energy efficiency	CECP; ENERGY STAR [®] 3.0 certified; EPEAT [®] Silver ^[2]
Digital sending standard features	Scan to PC, Scan to USB Drive
Scan file format	For text & images: PDF, PDF/A, Encrypted PDF, JPEG, PNG, BMP, TIFF, Word, Excel, PowerPoint, Text (.txt), Rich Text (.rtf) and Searchable PDF
Scan input modes	Two scan modes (simplex/duplex) with convenient 2x16 character LCD on front-panel for HP scan in Win OS, HP Easy Scan/ICA in Mac OS and third parties applications via TWAIN, ISIS and WIA
Scan technology	CMOS CIS (Contact Image Sensor)
Scanner type	Sheetfed
Display	2-line 16 character per line LCD display
Minimum dimensions (W x D x H)	310 x 198 x 190 mm
Minimum dimensions (W x D x H)	12.2 x 7.8 x 7.5 in
Weight	3.8 kg
Weight	8.4 lb
Power consumption	4.1 watts (ready), 38 Watts (scanning), 1.3 watts (sleep), 0.1 watts (off), 0.1 watts (auto-off) ^[1] (Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. Energy Star value typically based on measurement of 115V device.)
Power supply type	External power adapter
What's in the box	Power cord; Power Adapter; USB Cable; Scanner Engine; Flyers; Install Guide
Services (Care Pack)	UK001E - HP 3 year Standard Exchange ScanJet 5xxx Service; UH370E - HP 3 year Next Business Day Exchange ScanJet 5xxx Service; U0MF6E - HP 4 year Next Business Day Exchange ScanJet 5xxx Service; U0MF5E - HP 5 year Next Business Day Exchange ScanJet 5xxx Service; UH372E - HP 3 year Next Business Day Onsite Exchange ScanJet 5xxx Service; U0MF7E - HP 4 year Next Business Day Onsite Exchange ScanJet 5xxx Service; U0QN0E - HP 5 year Next Business Day Onsite Exchange ScanJet 5xxx Service; UH369E - HP 3 year Return to Depot ScanJet 5xxx Service; UK513PE - HP 1 year Post Warranty Standard Exchange ScanJet 5xxx Service; UH373PE – HP 1 year Post Warranty Next Business Day Exchange ScanJet 5xxx Service; UH374PE - HP 1 year Post Warranty Next Business Day Onsite Exchange ScanJet 5xxx Service; UD3B7PE - HP 1 year Post Warranty Return to Depot ScanJet 5xxx Service; U9JT2E - HP Installation Service wireless/network Workgroup Scanner & Printer
Warranty	One-year bench limited warranty whole unit replacement, phone and Web support included. Warranty may vary by country as required by law. Go to hp.com/support to learn about HP world-class service and support options in your region.

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

[1] Black-and-white scan speed measured at 300 dpi using included HP Scan Premium. Actual processing speeds may vary depending on scan resolution, network conditions, computer performance, and application software.

[2] Color scan speed measured at 300 dpi. Actual processing speeds may vary depending on scan resolution, network conditions, computer performance, and application software.

[4] HP Web Jetadmin is available for download at no additional charge at http://www.hp.com/go/webjetadmin

Technical Specifications Footnotes

[1] Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. Energy Star value typically based on measurement of 115V device.

[2] EPEAT® registered where applicable. EPEAT registration varies by country. See http://www.epeat.net for registration status by country.

© Copyright 2020 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

