imageCLASS LBP113w

Black and White | Compact | Printer

Print up to 23 ppm

Print up to 8-1/2" x 14"

150-sheet maximum paper capacity

Standard one-year warranty

Designed for personal and home office users, the imageCLASS LBP113w model features a compact design while still delivering speedy overall performance to accomplish daily tasks.

WORKFLOW EFFICIENCY

- Supports various mobile printing solutions.
- Designed for smaller print jobs with first-print-out time as fast as 6.3 seconds.
- Easily connect mobile devices without a router using Wi-Fi® Direct Connection.

USER EXPERIENCE

- Canon's signature reliability and engine technologies help keep productivity high and help minimize the impact on support resources.
- Space-saving, compact design conforms to personal or home office environments.

SUSTAINABILITY

- A combination of fusing technologies and low-melting-point toner minimizes power requirements and helps achieve lower energy consumption.
- Encourage environmentally conscious work practices by enabling settings that can help save paper and energy.
- ENERGY STAR® certified and currently rated EPEAT® Silver.[1]

GENUINE® CONSUMABLES

Always look for the Canon anti-counterfeiting hologram on your Canon GENUINE product packaging.

- Cartridge 047 (Item No.: 2164C001)
  Yields 1,600 Pages
- Drum 049 (Item No.: 2165C001)
  Yields 12,000 Pages

Use of Canon GENUINE toner cartridges helps provide longer equipment life, high yields, reliable performance, high-quality output, and minimal jamming or issues.

Starter Cartridge yielding 700 pages included in box.

EXTENDED SERVICE PLANS AVAILABLE FOR PURCHASE

Canon eCarePAK (Exchange/Carry-In)
Canon Extended Service Plans offer coverage beyond the standard one-year warranty[2] up to four years. Canon's service and support network is 100% U.S.-based.

One-Year:	5707B038
Two-Year:	5707B039
Three-Year:	5707B040
Four-Year:	5707B041

eCarePAK
Extended Service Plan

SPECIFICATIONS

Main Unit

Core Functions
Standard: Print

Item Code
2207C004

Control Panel
5-Line

Memory
256 MB

Standard Interface Connection
USB 2.0 x1 (Device) High-Speed, Wi-Fi 802.11b/g/n,
Wi-Fi Direct Connection

Paper Capacity (Letter, 20 lb. Bond)
Standard: 150 Sheets

Paper Sources (Letter, 20 lb. Bond)
Standard: 150-sheet Paper Cassette

Paper Output Capacity (Letter, 20 lb. Bond)
Standard: 50 Sheets

Supported Media Types
Cassette: Plain, Recycled, Thick, Bond, Label, Envelope (One Envelope)

Supported Media Sizes
Cassette: Letter, Legal, Statement, Executive Custom (Min. 3" x 5" to Max. 8.5" x 14")

Supported Media Weights
Cassette: 16 lb. Bond to 43 lb. Bond (60 g/m^2 to 163 g/m^2)

Warm-up Time
From Power On: 15 Seconds or Less
From Sleep
Mode: 1.6 Seconds or Less

Dimensions (W x D x H)
Standard: 14.8" x 11.5" x 8.8" (376 mm x 291 mm x 222 mm)

Weight
Machine Only: Approx. 12.1 lb. (5.5 kg)
Boxed Weight: Approx. 18.1 lb. (8.2 kg)

Print Specifications

Printing Method
Laser Beam Printing

Print Speed[3]
Up to 23 ppm (Letter); Up to 18 ppm (Legal)

First-Print-Out Time
Approx. 6.3 Seconds

Recommended Monthly Page Volume
150 - 1500

Print Resolution (dpi)
Up to 600 x 600

Standard Page Description Languages
UFR II LT

Printing from Mobile and Cloud-based Services[4]
Apple® AirPrint,® Canon PRINT Business, Mopria™ Print Service, Google Cloud Print™[5]

Operating System
UFR II/PCL: Windows® 7/Windows 8.1/Windows 10/ Windows Server 2008/Windows Server 2008 R2/Windows Server 2012/Windows Server 2012 R2/Windows Server 2016 Mac OS X v10.8.5 (or later)

Security Specifications

Network
Standard: IP Address Filtering, TLS Encrypted Communication, SNMP V3.0, IPv6

Wi-Fi Authentication Methods
Wi-Fi
Infrastructure
Mode: WEP 64/128 bit, WPA-PSK (TKIP/AES), WPA2-PSK (TKIP/AES)
Wi-Fi Access
Point: WPA2-PSK (AES)

Environmental Specifications

Operating Environment
Temperature: 50 to 86° F
Humidity: 20 to 80% RH (no condensation)

Power Requirements
AC 120-127 V:4.1 A, 60 Hz

Power Consumption
Maximum: Approx. 850 W
Standby: Approx. 3.4 W
Sleep Mode: Approx. 0.4 W
Typical
Electricity
Consumption
(TEC) Rating: 0.6 kWh

Standards
ENERGY STAR® Qualified, Rated EPEAT Silver[1]

---

[1] For current EPEAT ratings (Gold/Silver/Bronze), please visit **epeat.net**.
[2] Warranty program is subject to certain conditions and restrictions. See warranty card for details.
[3] Print speed is based on internal testing. Print speed may vary, depending on the number of copies selected as well as the settings for size, type, and orientation of paper.
[4] Canon PRINT Business is a free app available on the App Store® and Google Play™ Store. For more information, including compatibility, please visit **usa.canon.com/mobile-app**. Please see the respective websites for Apple AirPrint and Mopria Print Service for compatibility and additional information.
[5] Subscription to a third-party cloud service required. Subject to third-party cloud service providers' terms and conditions.

USA.CANON.COM

CANON
SEE IMPOSSIBLE