

# KODAK NUSCAN Q800

## DOCUMENT CAMERA VISUAL PRESENTER



## Powerful OCR Text Recognition

The KODAK NUSCAN Q800 Document Camera Visual Presenter is the ideal tool for presentations, image capturing and video recording. With this visual presenter and your computer, you can capture, using fixed-focus, real-time images of 3D Objects, magazines, books, documents, pictures and business cards and present them through a monitor or projector. With the addition of fixed-focus, the unique down-facing lens makes repetitive image capturing, demonstrations, tutorials and lectures comfortable and simple. Along with these great features, you can use the included NUSCAN software with your NUSCAN Q800 to take snapshots or record videos of just about anything, edit images and videos with the advanced editing tools, plus enjoy the convenience of sharing.

- 8.0 Megapixel CMOS Sensor
- Image Capturing
- OCR Function
- 1D/2D Barcode Scanning
- Video Recording



8.0 MP  
CMOS



Image  
Capturing



OCR  
Function



1D/2D Barcode  
Scanning



Video  
Recording



# KODAK NUSCAN Q800

## DOCUMENT CAMERA VISUAL PRESENTER

### SPECIFICATIONS

Image Sensor	8.0 Megapixel CMOS Color Sensor
Interface	USB 2.0
Resolution	3264 x 2448
Image File Format	JPEG
Document File Format	PDF (Image/Searchable/Txt), Word, TXT, Excel
Video File Format	AVI, MP4, FLV, WMV
Shooting Area	Up to A3 Size – (420 x 297 mm / 16.5 x 11.7 inch)
Focus	Fixed, Auto-Zoom
Video Frame Rate	1280 x 960 (SXGA) , 640 x 480 (VGA)
Video Compression	MPEG, YUY2
LED Lights	4 pcs
White Balance	Auto
Operating Dimension	10.24" x 3.15" x 7.87" (260 x 80 x 200mm)
Folded Dimension	10.24" x 3.15" x 3.15" (260 x 80 x 80mm)
Weight	1.87 lbs. (850g)
Power	5V by USB Powered
System Requirements	WINDOWS 10/8/7/Vista/XP
Supplied Contents	NUSCAN Q800 x1, USB Cable x1, Software CD x1, Scan Mat x1, Quick Start Guide x 1

Item	Product Description	UPC	Package Dim.	Package Weight	Master Carton Qty
Kodak NuScan Q800	8MP Document Camera Visual Presenter	783750100496	19.2" x 5.6" x 4.4"	3.7 lbs	8

© 2019 Adesso, Inc. The Kodak trademark, logo and trade dress are used under license from Kodak. All Information contained in this document is subject to change without notice.

