



- 4K slim bezel commercial display
- Wireless presentation across devices and rooms
- Easy cast function pairing with USB-C dongle sender
- USB plug-n-play for photos, music & video
- Multitasking with powerful embedded player & OPS PC slot

The ViewSonic® CDE7520 is a 75" premium 4K commercial display. With features including a razor-sharp resolution of 3840 x 2160, 450-nit high brightness, 178-degree ultra- wide viewing angles, 2 x 12W speakers, and wireless screen sharing, the display is designed with the meeting room scenario in mind. The built-in screen sharing software\*, ViewBoard® Cast and Stream, as well as ViewBoard® Cast USB-C sender enable multiple users, whether on-site or on-line, to participate in conferences and share content with each other simultaneously, transforming the CDE7520 into a dynamic content hub. This reliable commercial display is equipped with a quad-core processor and 16GB internal memory, allowing constant multimedia play from internal storage or a USB flash drive. Supporting remote configuration and content management system, the ViewSonic® CDE7520 is also suitable for diverse signage applications. \*Chrome, Android, Windows, Mac OS, and iOS complaint

## Technical Specifications

<b>Display</b>	Panel Size	75"
	Type/ Tech	TFT LCD Module. IPS type, DLED backlight
	Display Area (mm)	1649.664(H) × 927.936(V) (75" diagonal)
	Native Resolution	3840 x 2160
	Aspect Ratio	16:9
	Colors	1.07G colors
	Brightness	450 nits (typ.)
	Contrast Ratio	1200:1 Typ.
	Response Time	8 ms
	Viewing Angles	H = 178, V = 178 typ.
	Backlight Life	30,000 Hours (min)
	Surface Treatment	Anti-glare, 3H hardness, Haze 25%
	Bezel	Slim
	Orientation	Landscape
<b>INPUT</b>	HDMI	x2
	RGB / VGA	x1
	DisplayPort	x1
	Audio	x1 (3.5mm)
	RS-232	x1
	OPS	x1 : OPS slot (Intel OPS Standard) , x1 : LB-Wi-Fi-001 WiFi dongle
<b>OUTPUT</b>	HDMI	x1 support 4K 60Hz
	Audio	x1 (3.5mm)
	SPDIF	x1 (Fiber)
<b>LAN</b>	RJ45	x1
<b>USB</b>	Type A	2.0 Type A : x 2 (USB Playback), 3.0 Type A : x 1 (USB Playback)
<b>Micro SD card slot</b>	Micro SD card slot	No
<b>SPEAKERS</b>	SPEAKERS	Max. 16Wx2
<b>COMPATIBILITY</b>	RGB PC/HDMI PC	Up to 1920x1080@60Hz. Refer to timing table
	HDMI	480i, 480p,720p,1080i,1080p, 4K2K@60Hz
	DisplayPort	480i, 480p,720p,1080i,1080p, 4K2K@60Hz
	Android Version	Android 8.0
<b>POWER</b>	Voltage	100V-240V,50/60Hz (AC)
	Consumption	Normal 240 W, Max 300 W
<b>ERGONOMICS</b>	Wall Mount (VESA® )	400x200 mm
<b>OPERATING CONDITIONS</b>	Temperature (°	0 to 40°C

C)	Humidity	20% ~ 80% non-condensing
----	----------	--------------------------

---

**DIMENSIONS (W x H x**

<b>D)</b>	Physical (inch / mm)	65.83 x 37.59 x 2.76 in/ 1672.0 x 955.0 x 70.0 mm
	Packaging (inch / mm)	71.97 x 43.23 x 8.66 in/1828 x 1098 x 220 mm

---

<b>WEIGHT</b>	Net (lb / kg)	29.30 kg / 64.60 lbs (w/o stand)
	Gross (lb / kg)	41.7 kg/91.93 lbs

---

<b>REGULATIONS</b>	REGULATIONS	cULus, FCC, Energy Star, EPEAT, MX-CoC, Mexico Energy, CE, CB, RoHS, ErP, REACH, WEEE, Custom Union, UkrSEPRO, RCM, MEPS
--------------------	-------------	--

---

<b>PACKAGE CONTENTS</b>	PACKAGE CONTENTS	1. CDE7520 commercial display, 2. Remote control with batteries, 3. Quick start guide, 4. Power cables (1.5mm), 5. HDMI cable (3 mm), 6. Wall mount screw, 7. RS232 adapter
-------------------------	------------------	---

## **ViewSonic® Limited Warranty**

---

ViewSonic provides customers with the security of a manufacturers warranty against defected products. The type and duration of the applicable warranty service varies by product type, country of purchase and can also vary on an individual basis according to customer requirements agreed at time of purchase. The warranty will expire after the end of the warranty period.

---

For more product information, visit us at [www.viewsoniceurope.com](http://www.viewsoniceurope.com)

All rights reserved by ViewSonic Corporation. All other Corporate names and trademarks are the property of their respective companies. E&EO. All prices and specifications are subject to change without written notice. Images are for illustrative purpose only. Terms & Conditions Apply.