

**msi**

GRAPHICS CARD

GEFORCE® GTX 1650 D6 GAMING X

SPECIFICATION

Model Name	GeForce® GTX 1650 D6 GAMING X
Graphics Processing Unit	NVIDIA® GeForce® GTX 1650
Interface	PCI Express x16 3.0
Cores	896 Units
Core Clocks	Boost: 1725 MHz
Memory Speed	12 Gbps
Memory	4GB GDDR6
Memory Bus	128-bit
Output	DisplayPort x 2 (v1.4) / HDMI 2.0b x 1
HDCP Support	2.2
Power consumption	85 W
Power connectors	6-pin x 1
Recommended PSU	300 W
Card Dimension(mm)	245 x 127 x 39 mm
Weight (Card / Package)	582 g / 1193 g
DirectX Version Support	12 API
OpenGL Version Support	4.6
Maximum Displays	3
G-SYNC® technology	Y
Digital Maximum Resolution	7680x4320

CONNECTIONS



1. HDMI
2. DisplayPort

TRUE GAMING

© 2018 Micro-Star Int'l Co.,Ltd. MSI is a registered trademark of Micro-Star Int'l Co.,Ltd. All rights reserved. © 2016 NVIDIA, the NVIDIA logo, GeForce, SHIELD, and NVIDIA G-SYNC are trademarks and/or registered trademarks of NVIDIA Corporation in the U.S. and other countries.

FEATURE



TORX FAN 3.0

Award-winning fan design combining two different fin designs for cool & quiet gaming.



Mastery of Aerodynamics

Using groundbreaking aerodynamic techniques, the heatsink is optimized for efficient heat dissipation.



ZERO FROZR

Eliminates fan noise by stopping the fans in low-load situations so you can focus on your game.



DRAGON CENTER

A consolidated platform that offers all software including MYSTIC LIGHT functionality for your MSI Gaming product.



MSI Afterburner

The ultimate overclocking software with advanced control options and real-time hardware monitor.



OC PERFORMANCE

MSI OC graphics cards are equipped with higher clock speeds out of the box for increased performance.



NVIDIA® G-SYNC®

Gives you more of what you want in a gaming experience. Incredibly smooth, tear-free gameplay at refresh rates up to 240 Hz.