



UniFi Protect ViewPort PoE



The UniFi Protect ViewPort allows you to view your UniFi Protect camera feeds on an HDMI display. It uses Power over Ethernet and connects to the local network hosting your cameras and connects via HDMI to a display. The UniFi Protect ViewPort offers 4K video output at 30 frames per second. Protect systems can be viewed in custom high-density camera matrix configurations.

Mechanical

Dimensions	157 x 52 x 37 mm (6.18 x 2.05 x 1.46")
Weight	Without Mount: 230 g (8.11 oz) With TV Mount: 252 g (8.89 oz)
Enclosure Material	Polycarbonate
Mount Material	Polycarbonate

Hardware

Processor	The Qualcomm® QCS605 SoC
Memory Information	4GB Low Power DDR4X
Management Interface	UniFi Protect
Networking Interface	10/100/1000 Mbps RJ45 Ethernet Port
Max. Power Consumption	9.5W
Power Method	802.3af PoE
Power Supply	802.3af PoE
ESD/EMP Protection	Air: ± 8kV, Contact: ± 4kV
Operating Temperature	0 to 40° C (32 to 104° F)
Operating Humidity	20 to 80% Noncondensing
Button	Factory Reset
Bluetooth	5.0
Antennas	Bluetooth
Antenna Gain	2 dB
Certifications	FCC, IC, CE

