



24" IPS monitor with ultra-slim bezel and ultra-flat front

Stylish edge-to-edge design makes the ProLite XU2493HSU perfect for multi-monitor set-ups. The IPS panel technology offers accurate and consistent colour reproduction with wide viewing angles. High contrast and brightness values mean the monitor will provide excellent performance for photographic and web design.

Available also with height adjustable stand: [ProLite XUB2493HS-B1 \(1920x1080\)](#) and [ProLite XUB2493HSU-B1 \(1920x1080\)](#)



IPS Technology

IPS technology offers higher contrast, darker blacks and much better viewing angles than standard TN technology. The screen will look good no matter from what angle you look at it.



Flicker-free + Blue light

The ultimate solution for the comfort and health of your eyes. Flicker-free monitors with the blue light reducer function substantially reduce the strain and fatigue caused by flickering and blue light emittance of regular monitors.

01 DISPLAY CHARACTERISTICS

Design	ultra slim
Diagonal	23.8", 60.5cm
Panel	IPS panel technology LED, matte finish
Native resolution	1920 x 1080 @60Hz (2.1 megapixel Full HD)
Aspect ratio	16:9
Brightness	250 cd/m ² typical
Static contrast	1000:1 typical
Advanced contrast	80M:1
Response time (GTG)	4ms
Viewing zone	horizontal/vertical: 178°/178°, right/left: 89°/89°, up/down: 89°/89°
Colour support	16.7mln 8bit (6bit + Hi-FRC) (sRGB: 96%; NTSC: 72%)
Horizontal Sync	30 - 84KHz
Vertical Sync	55 - 75Hz
Viewable area W x H	527 x 296.5mm, 20.7 x 11.7"
Pixel pitch	0.275mm
Colour	matte, black

02 INTERFACES / CONNECTORS / CONTROLS

Signal input	VGA x1 (1920 x 1080 @60Hz) HDMI x1 (1920 x 1080 @75Hz) DisplayPort x1 (1920 x 1080 @75Hz)
USB HUB	x2 (v.2.0)
Headphone connector	yes

03 FEATURES

OSD languages	EN, DE, FR, ES, IT, PT, RU, JP, NL, PL
Control buttons	Signal / Auto Adjust, + / Volume, - / Eco, Menu, Power
User controls	picture adjust (contrast, brightness, i-Style Colour, adv. aontrast, Eco, OD, X-Res technology), image settings (auto adjust, pixel clock, phase, H. position, V. position, sharp and soft, aspect), colour settings (gamma, 6-axis, colour temperature), OSD (OSD H. position, OSD V. position, OSD time, language), extra (reset, DDC/CI, signal select, audio source, HDMI range, opening logo, LED, information, volume)
Speakers	2 x 2W
Convenience	Kensington-lock™ prepared, DDC/CI, DDC2B, Mac OSX

04 MECHANICAL

Display position adjustments	tilt
Tilt angle	21.5° up; 3.5° down
VESA mounting	100 x 100mm

05 ACCESSORIES INCLUDED

Cables	power, USB, HDMI
Other	quick start guide, safety guide

06 POWER MANAGEMENT


Power supply unit	internal
Power supply	AC 100 - 240V, 50/60Hz
Power usage	19W typical, 0.5W stand by, 0.5W off mode

07 SUSTAINABILITY

Regulations	CE, TÜV-Bauart, EAC, VCCI-B, PSE, Energy Star
Energy efficiency class	A+
Other	REACH SVHC above 0.1%: Lead

08 DIMENSIONS / WEIGHT

Product dimensions W x H x D	539.5 x 415 x 199.5mm
Weight (without box)	3.3kg
EAN code	4948570117499



09 EU ENERGY EFFICIENCY LABEL

Manufacturer	iiyama
Model	ProLite XU2493HSU-B1
Energy efficiency class	A+
Visible screen diagonal	61cm; 23.8"; (24" segment)
ON mode power consumption	19W
Power in Standby	0.5W stand by
Power in OFF Mode	0.5W off mode
Resolution	1920 x 1080

All trademarks and registered trademarks acknowledged. E & O E. Specification subject to change without notice. All LCD's comply with ISO-9241-307:2008 in connection with pixel defects.

© IIYAMA CORPORATION. ALL RIGHTS RESERVED