

Smart Tab M10 FHD Plus with the Google Assistant ZA5W0146US

Product
Lenovo TB-X606F

Region
NA

Country/Region
USA

Machine Type
ZA5W

TopSeller
No

Processor
MediaTek Helio P22T (8C, 8x A53 @2.3GHz)

Graphics
Integrated IMG GE8320 GPU

Chipset
MediaTek SoC Platform

Memory
4GB Soldered LPDDR4X-3200

Display
10.3" FHD (1920x1200) TDDI 330nits

Touchscreen
10-point Multi-touch

Expandable Memory
MicroSD card (Up to 256GB)

Storage
64GB eMMC

WLAN + Bluetooth
11a/b/g/n/ac, 1x1 + BT5.0

WWAN
None

Card Slot
MicroSD Card Holder Tray

Bundled Accessories
Cradle

Color
Iron Grey

Case Material
Metal

Camera
Front 5.0MP / Rear 8.0MP

Microphone
2x, Array

VoiceCall
No

Battery
Integrated 5000mAh

Power Adapter
5V / 2.0A

Operating System
Android Pie

Bundled Service
Not Available

Base Warranty
1-year, Mail-In

End of Support
Not Available

EAN / UPC / JAN
194632277364

Announce Date
2020-01-07

Notes:

Battery life is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences.

California Electronic Waste Recycling Fee

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

 WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.

© Lenovo, 2020. All rights reserved.



Smart Tab M10 FHD Plus with the Google Assistant Platform Specifications

Product Specifications Reference (PSREF)

Processor	MediaTek® Processor MediaTek Helio P22T (8xARM Cortex-A53, up to 2.3GHz)						Camera	Front / Focus Mode		Rear / Focus Mode		Type	Zoom	Flash Light				
Graphics	Integrated IMG GE8320 GPU							5.0MP	Fixed Focus	8.0MP	Auto Focus	CMOS	Digital	No				
Display	Size	Resolution	Type	Brightness	Color Gamut	Viewing Angle	Audio	Dual side speaker, tuned with Dolby Atmos®, Dual array microphones (with dedicated DSP), 3.5mm (0.14inch) combo audio / microphone jack (CTIA)										
	10.3" (261.62mm)	FHD (1920 x 1200)	TDDI	Typ. 330nits Min. 280nits	Typ. 70.3% NTSC Min. 65% NTSC	160°	Keyboard	None	None	Smart Charging Station (Cradle)	with USB Type-C and Micro-USB cable							
Multi-touch	Capacitive-type multi-touch, supports 10-point touch						Touchpad	None										
Memory	2GB or 4GB / 3200MHz LPDDR4X, soldered to systemboard						Bundled Accy	None										
Storage	32GB, 64GB or 128GB eMMC (Embedded Multi Media Card), flash memory on board						Security chip	None										
Card slot	One single card slot (WiFi model) or one dual-card slot (LTE model), supports Nano-SIM card + MicroSD card (up to 256GB, FAT32)						Fingerprint reader	None										
Bluetooth®	Bluetooth 5.0						VoiceCall (Opt)	Yes (India models only)										
WLAN	802.11 a/b/g/n/ac, 1x1, 2.4 GHz / 5 GHz Wi-Fi Dual Bands						Battery type	Li-ion Polymer 5000mAh (Minimum) / 5100mAh (Typical)										
WWAN (Optional)	4G LTE connectivity						Battery life	Standby Time: 1048hrs Online Video playback Time: Up to 8.5hrs Browsing Time: Up to 9hrs * Battery life varies significantly with settings, usage, & other factors										
LTE Band	GSM: B2/B3/B5/B8 WCDMA: B1/B2/B5(B6/B19)/B8 FDD LTE: B1/B2/B3(expanded Band3)/B4/B5(B19)/B7/B8/B20 TDD LTE: B38/B40						AC adapter	5V/2A										
							Charging time	Over 3.5hrs										
NFC	None						Preload	Android® Pie Lenovo applications • Tips • Kid's Mode										
WIFI Direct	Yes							Third-party applications • Netflix • Dolby Atmos • Google • Gmail • Google Chrome • Google Photos • Google Play Store										
WIFI Display	Yes																	
WHDI	None																	
FM Radio	Yes																	
A-GPS (Optional)	Yes (LTE model)																	
GPS (Optional)	Yes (LTE model)																	
Glonass (Opt)	Yes (LTE model)																	
Beidou (Optional)	Yes (LTE model)																	
Vibrator	Yes																	
G-sensor	Accelerometer sensor																	
P-sensor	Proximity sensor																	
L-sensor	Ambient sensor																	
E-compass	None																	
Hall Sensor	Yes																	
Gyroscope	None																	
Proofing	None																	
Dimensions	Tablet: 9.61" x 6.03" x 0.32"; 244.2mm x 153.3mm x 8.15mm Cradle: 4.92" x 3.62" x 0.66"; 125mm x 92mm x 17mm																	
Weight	Tablet: 460g / 1.01lb Cradle: 245g / 0.54lb																	
Case color	Iron Grey																	
Case material	Metal																	
Ports	Two Pogo Pin, one USB Type-C 2.0, supports OTG, 3.5mm (0.14inch) combo audio / microphone jack (CTIA), One single card slot (WiFi model) or one dual-card slot (LTE model), supports Nano-SIM card + MicroSD card (up to 256GB, FAT32)																	
Buttons	* Depending on many factors, actual data transfer speed may be lower than theoretical speed Power key, volume key																	

Note: The specifications above may not be available in all regions

Lenovo
May 2020



Smart Tab M10 FHD Plus with the Google Assistant

Lenovo

