



Thin, bright, and dynamic the EVO LCD Touch Display is a perfect solution for customer engagement at the point of sale. Featuring a vivid, 8" display and 10 point multi-touch, the EVO LCD Touch Display can be used in any point of sale application.

10 Point Multi-Touch

Eliminate paper receipts with digital signature capture or increase customer loyalty engagement by offering customers a simple way to interact at the point of sale.

Vivid Color Display

The EVO LCD Touch Display features an 8" LCD display with a TruFlat zero bezel screen.

Dynamic Mounting Options

The EVO LCD Touch Display can be mounted with it's included stand or to any standard 75MM VESA mount.

Simple Installation

Utilizing an on-board graphics adapter the EVO LCD Touch Display can be connected to any Windows computer with the included USB cable. No HDMI or VGA port needed!

Wide Viewing Angles

Designed to be used from multiple viewing points, a 140° viewing angle provides an impressive display in any installation.



MODEL	EVO-SRD1-TLCD8
Screen Size	8"
Resolution	800x600
Brightness	250 Nits
Back Light	LED
Aspect Ratio	4:3
Contrast Ratio	500:1
Viewing Angle (U/D/L/R)	50°/70°/70°/70°
Response Time	25ms
Touch	10-Point Multi-touch PCAP
Power Consumption	2.5W

PHYSICAL	
Housing	ABS
Weight	2.7 lb with stand
Dimensions (WxDxH) With Stand	5.75" x 5.75" x 8.5"
Tilt Angle	0° - 90°
Housing Color	Black
Cable Length	6 Feet

ENVIRONMENTAL	
Operating Temperature	32°F - 104°F (0°C - 40°C)
Humidity	20% - 90% RH non-condensing
Warranty	3-year warranty with free *2-day Advance Exchange Service
Certifications	CE, FCC, LVD
Supported OS	Windows 7, Windows 8.1, Windows 10

WARRANTY EXTENSIONS	
ZWE-TMC	2-Year Warranty Extension
ZOE-TMC3	Next Business Day Protection*
ZOE-TMC5	2-Year Warranty Extension + Next Business Day Protection*

*Available in USA and Canada