



With a sleek yet robust design, the EVO TP6 is the perfect enterprise-grade POS solution. The EVO TP6 features a 15" TruFlat projected capacitive touchscreen, a range of Intel CPUs, cable free accessories and a versatile dual hinge design.



Resilient Touch Display

The EVO TP6 features a 15" LCD screen with TruFlat projected capacitive (PCAP) multi-touch technology built to take the rigors of heavy use.



Versatile Platform

A dual hinge design allows for efficient shipping and almost unlimited tilt angles. Built-in VESA mounting extends the versatility of the platform to any wall mount installation.



Fan-less Design

A fan-less design provides a sleek, clean look and silent operation. No vent openings mean better protection from dust and water reaching an IP54 ingress protection rating.



Efficient High Performance CPUs

With support for Intel CPUs ranging from the efficient J1900 to the powerful Core i5, the EVO TP6 is sure to fit any application



MODEL	EVO-TP6D-F	EVO-TP6D-P	EVO-TP6D-3	EVO-TP6D-5	EVO-TP6W-3
Processor	Intel Celeron J1900	Intel Pentium 4405U	Intel Core i3-6100U	Intel Core i5-6200U	Intel Core i3-6100U
Bezel	TruFlat Zero Bezel				
Chip Set	Processor Integrated				
System Memory	1 x DDR3L SO-DIMM 4GB - 8GB			1 x DDR3L SO-DIMM 8GB	
Hard Drive	2.5" 64-500GB SSD or 2.5" 500GB HDD				
LCD Display	15" (381mm) TFT LCD			18.5" (470mm) TFT LCD	
Resolution	1024x768			1920x1080	
Touch	PCAP, 10 Point Multi-Touch				
Brightness	300 nits	350 nits			
Graphic Engine	Intel HD Graphics DX11 and OCL1.1	Intel HD Graphics DX12 and OCL4.2			
Electrical	65W/19V	90W/19V			
Supported OS	Win 7 Pro (x32/x64), POSReady 7(x32/x64), Win 10 IoT(x32/x64)	Win 8.1 Embedded (x64), Win 8.1 Pro (x64), Win 10 IoT (x64), Win 10 Pro (x64)			

PORTS	EVO-TP6D-F	EVO-TP6D-P	EVO-TP6D-3	EVO-TP6D-5	EVO-TP6W-3
USB	4 x USB 2.0 / 1 x USB 3.0	2 x USB 2.0 Type A / 4 x USB 3.0			
Serial	3 x RJ45 with 0V/5V/12V power				
LAN	1 x RJ45				
WLAN (Optional)	Dual Band 802.11 a/b/g/n/ac 2.4GHz/5GHz				N/A
Cash Drawer Port	1 x RJ11 (12V/24V)				
VGA	1 x DB15				

PHYSICAL	
Housing	Die Cast Aluminum
Weight	EVO- TP6D 13.2lbs, EVO-TP6W 9.6lbs
Dimensions (WxDxH)	EVO- TP6D - 14.2" x 8" x 10.9" EVO-TP6W - 18.1" x 8" x 11.4"
Tilt	Dual Hinge
Housing Color	Black
Wall Mount	100mm VESA (75mm or 100mm with base)

OPTIONAL ACCESSORIES	
3 Track MSR	EVO-MR6
Fingerprint Reader	EVO-BR6
2 Line Customer Display	EVO-RD6-LCM
8.4" LCD Customer Display	EVO-RD6-LCD8

ENVIRONMENTAL	
Operating Temperature	32°F - 95°F (0°C - 35°C)
Humidity	20% - 80% RH non-condensing
Certifications	FCC Class B, CE, LVD, NOM
IP Rating	IP54 (Front)
Viewing Angle	Horizontal: 140°, Vertical 130°

WARRANTY EXTENSION AND UPGRADES	
ZWE-TPC	2-Year Warranty Extension
ZOE-TPC3	*Next Business Day Protection
ZOE-TPC5	*2-Year Warranty Extension + Next Business Day Protection

*Available in USA and Canada.