

# HP ScanJet Enterprise Flow N7000 snw1 (6FW10A)



**Give your office high-volume scanning performance.  
Recommended for 7500 pages per day.**

Give your office high-volume scanning performance. HP Scan Premium helps you save time and capture confidently. Achieve black-and-white scan speeds up to 75 ppm/150 ipm.[1]  
Recommended for 7,500 pages per day.



**Fast, smooth scanning—even unattended**

Capture entire documents with one-pass duplex scanning up to 150 ipm.[1,3]

**Peak workflow performance. Smarter scanning.**

Identify new devices and gain insight into scanning with HP Web Jetadmin remote discovery and monitoring.[5]

**Professional-grade scanning that helps save time**

Save time and simplify complex scan jobs with HP Scan Premium

**Featuring**

Support Ethernet, WiFi and WiFi direct


One-pass duplex scanning

7500-page duty cycle

HP EveryPage, ultrasonic sensor

80-page ADF

HP Scan Premium



## Specifications

<b>Scanner advanced features</b>	Auto exposure, Auto threshold, Auto detect color, Background smooth/removal, Auto detect size, Straighten content, Enhance content, Multi-streaming, Auto feed, Multi-feed detection sensor, Advanced multi-feed detection, Auto orient, Multi-color dropout, Channel color dropout, Edge erase, Delete blank page, Merge pages, Hole fill, Digital stamps, Metadata capture, PDF permissions, PDF digital signatures, Document separation (Blank page, Barcode, Zonal barcode, Zonal OCR)
<b>Connectivity, standard</b>	Ethernet 10/100/1000 Base-T, USB 3.0, WiFi 802.11 b/g/n, WiFi Direct
<b>Wireless capability</b>	Yes, WiFi 802.11 b/g/n, WiFi Direct
<b>Network protocols, supported</b>	ARP;ICMP; IGMP;UDP;TCP;DHCP;APIPA;DNS;mDNS;LLMNR;WSD;WS-Scan;SNTP;SMB;SNMP;FTP;SFTP;SMTP;HTTP Server Part;HTTPS
<b>Software included</b>	Windows: HP WIA scan driver, HP TWAIN scan driver (32-bit and 64-bit), HP Scan Premium, HP Scanner Tools Utility, I.R.I.S Readiris Pro, I.R.I.S Cardiris, OpenText ISIS
<b>Compatible Operating Systems</b>	Microsoft® Windows® (10, 8.1, 7, XP: 32-bit and 64-bit, 2008 R2, 2012 R2, 2016, 2019); MacOS (Catalina 10.15, Mojave 10.14, High Sierra 10.13); Linux (Ubuntu, Fedora, Debian, RHEL, Linux Mint, Open Suse, Manjaro); Citrix ready
<b>Sustainable impact specifications</b>	RoHS-Compliant
<b>Energy star certified</b>	Yes
<b>Ecolabels</b>	CECP; ENERGY STAR® 3.0 certified; EPEAT® Silver <sup>[2]</sup>
<b>Digital sending standard features</b>	Scan to PC, Scan to USB Drive, Scan to Email, Scan to Network Folder, Scan to SharePoint, Scan to Shortcut, Scan to Cloud
<b>Scan file format</b>	For text & images: PDF, PDF/A, Encrypted PDF, JPEG, PNG, BMP, TIFF, Word, Excel, PowerPoint, Text (.txt), Rich Text (.rtf) and Searchable PDF
<b>Scan input modes</b>	Two scan modes (simplex/duplex) with 10.9 cm (4.3 inch) Color touch screen on front-panel for HP scan in Win OS, HP Easy Scan/ICA in Mac OS and third parties applications via TWAIN, ISIS and WIA
<b>Scan technology</b>	CMOS CIS (Contact Image Sensor)
<b>Scanner type</b>	Sheetfed
<b>Display</b>	Resistive, RGB color and 2.8 "touch panel with a resolution of 140 dpi (240 x 320 dots).
<b>Minimum dimensions (W x D x H)</b>	310 x 198 x 190 mm
<b>Minimum dimensions (W x D x H)</b>	12.2 x 7.8 x 7.5 in
<b>Weight</b>	4.0 kg
<b>Weight</b>	8.8 lb
<b>Power consumption</b>	5.8 Watts (ready), 38 Watts (scanning), 1.9 Watts (sleep), 0.1 Watts (auto-off), 0.1 Watts (off) <sup>[1]</sup> (Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. Energy Star value typically based on measurement of 115V device. )
<b>Power supply type</b>	External power adapter
<b>What's in the box</b>	Power cord; Power Adapter; USB Cable; Scanner Engine; Flyers; Install Guide
<b>Manufacturer Warranty</b>	One-year bench limited warranty whole unit replacement, phone and Web support included. Warranty may vary by country as required by law. Go to <a href="http://hp.com/support">hp.com/support</a> to learn about HP world-class service and support options in your region.

## Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

## Messaging Footnotes

[1] Black-and-white scan speed measured at 300 dpi using included HP Scan Premium. Actual processing speeds may vary depending on scan resolution, network conditions, computer performance, and application software.

[3] Color scan speed measured at 300 dpi. Actual processing speeds may vary depending on scan resolution, network conditions, computer performance, and application software.

[5] HP Web Jetadmin is available for download at no additional charge at <http://www.hp.com/go/webjetadmin>

## Technical Specifications Footnotes

[1] Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. Energy Star value typically based on measurement of 115V device.

[2] EPEAT® registered where applicable. EPEAT registration varies by country. See <http://www.epeat.net> for registration status by country.

---

© Copyright 2022 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

