

Lenovo Legion 5 15IMH05H 81Y6005TUK

Product

Lenovo Legion 5 15IMH05H

Region

WE

Country/Region

UK Group

Machine Type

81Y6

Processor

Intel Core i5-10300H (4C / 8T, 2.5 / 4.5GHz, 8MB)

Graphics

NVIDIA GeForce RTX 2060 6GB GDDR6

Chipset

Intel HM470

Memory

1x 8GB SO-DIMM DDR4-2933

Storage

256GB SSD M.2 2280 PCIe NVMe

Display

15.6" FHD (1920x1080) IPS 300nits Anti-glare, 144Hz, 100% sRGB Gamut, Dolby Vision

Touchscreen

None

Optical

None

Media Reader

None

Ethernet

100/1000M

WLAN + Bluetooth

11ax, 2x2 + BT5.0

Bundled Accessories

None

Case Material

PC / ABS

Camera

720p

Microphone

2x, Array

Color

Phantom Black

Keyboard

Backlit, English (UK)

Fingerprint Reader

None

TPM

FW TPM 2.0

Battery

Integrated 80Wh

Power Adapter

230W Slim Tip

Operating System

Windows 10 Home 64, English

Bundled Software

Office Trial

Base Warranty

1-year, Depot

Bundled Service

None

EAN / UPC / JAN

195042339185

End of Support

2026-05-27

Announce Date

2020-05-18



WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

<https://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.

© Lenovo, 2020. All rights reserved.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.

© Lenovo, 2020. All rights reserved.



Lenovo Legion 5 15IMH05H Platform Specifications

Product Specifications Reference (PSREF)

Processor	10th Generation Intel® Core™ i5 / i7 Processor								Media reader Ports	None Four USB 3.1 Gen 1 (one Always On), one USB 3.1 Type-C Gen 1 (with the function of DisplayPort 1.2), HDMI 2.0, Ethernet (RJ-45), headphone / microphone combo jack, security keyhole, AC power adapter jack * Depending on many factors, actual data transfer speed may be lower than theoretical speed Optional: Lenovo Legion M300 RGB Gaming Mouse (USB connector)															
	Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Types	Processor Graphics																	
	i5-10300H	4	8	2.5 GHz	4.5 GHz	8MB		Intel UHD Graphics																	
	i7-10750H	6	12	2.6 GHz	5.0 GHz	12MB	DDR4-2933																		
	i7-10875H	8	16	2.3 GHz	5.1 GHz	16MB																			
Graphics	<table border="1"> <tr> <td>Integrated Graphics</td> <td colspan="7">Discrete Graphics (Memory)</td> </tr> <tr> <td>Intel UHD Graphics</td> <td colspan="7">NVIDIA® GeForce® GTX 1660 Ti (6GB GDDR6 memory), VR ready NVIDIA GeForce RTX 2060 (6GB GDDR6 memory), VR ready</td> </tr> </table>							Integrated Graphics	Discrete Graphics (Memory)							Intel UHD Graphics	NVIDIA® GeForce® GTX 1660 Ti (6GB GDDR6 memory), VR ready NVIDIA GeForce RTX 2060 (6GB GDDR6 memory), VR ready							Camera	720p HD, 1.0MP resolution, privacy shutter, fixed focus, integrated dual array microphone
Integrated Graphics	Discrete Graphics (Memory)																								
Intel UHD Graphics	NVIDIA® GeForce® GTX 1660 Ti (6GB GDDR6 memory), VR ready NVIDIA GeForce RTX 2060 (6GB GDDR6 memory), VR ready																								
	supports external digital monitor via HDMI or USB Type-C; supports three independent displays; Max resolution: 4096x2160@60Hz (HDMI); 3840x2160@30Hz (USB Type-C)								Audio support	HD Audio, Realtek ALC3287 codec / Dolby Atmos® for Gaming Certification, Harman speakers, 2W x 2, dual array microphone, headphone / microphone combo jack															
Chipset Memory	Intel HM470 Chipset 16GB max offering / 2933MHz DDR4, dual-channel capable, two DDR4 SO-DIMM sockets								Keyboard	6-row, multimedia Fn keys, white backlight or 4-Zone RGB LED backlight, numeric keypad, anti-ghost															
Display	<p>One of the following, configurable by model:</p> <ul style="list-style-type: none"> 15.6" (396mm) FHD (1920x1080), anti-glare, LED backlight, IPS, 250 nits, 16:9 aspect ratio, 45% NTSC gamut, refresh rate 120Hz 15.6" (396mm) FHD (1920x1080), anti-glare, LED backlight, IPS, 300 nits, 16:9 aspect ratio, 100% sRGB gamut, refresh rate 60Hz 15.6" (396mm) FHD (1920x1080), anti-glare, LED backlight, IPS, 300 nits, 16:9 aspect ratio, 100% sRGB gamut, refresh rate 144Hz, Dolby® Vision 15.6" (396mm) FHD (1920x1080), anti-glare, LED backlight, IPS, 500 nits, 16:9 aspect ratio, 100% sRGB gamut, refresh rate 240Hz, Dolby Vision 								Touchpad	Buttonless Mylar surface multi-touch touchpad															
Multi-touch	None								Security	Power-on password, hard-disk password, supervisor password, security keyhole															
Storage	<p>Up to 2 drives:</p> <ul style="list-style-type: none"> HDD / SATA 6.0Gb/s, 2.5" wide, 7mm high M.2 2280 SSD / PCIe NVMe, PCIe 3.0 x 4 M.2 2242 SSD / PCIe NVMe, PCIe 3.0 x 4 								Security chip	Firmware TPM 2.0 integrated in chipset															
Optical	None								Fingerprint reader	None															
Ethernet	Gigabit Ethernet connection								Battery	Integrated Li-Polymer 60Wh or 80Wh battery, supports Rapid Charge Pro (30 minutes 50%)															
WLAN	802.11ax 2x2 Wi-Fi + Bluetooth 5.0, M.2 Card								Max battery life	MobileMark® 2018: 7.7 hr (80Wh) or 6.8 hr (60Wh)															
Bluetooth™	Bluetooth 5.0 wireless, integrated in Wi-Fi + Bluetooth combo adapter									* Battery life varies significantly with hardware configurations, settings, usage, & other factors															
Dimensions	WxDxH: 14.3" x 10.22" x 0.93-1.03"; 363.06mm x 259.61mm x 23.57-26.1mm								AC adapter	230W slim tip AC adapter															
Weight	Starting at 5.42 lb / 2.46 kg								Preload (optional)	Preloaded operating system															
Case color	Phantom black									• Windows® 10 Home 64															
Case material	PC/ABS plastic									• Windows 10 Pro 64															
Lighting	Legion "Y" logo with white backlit on display cover									Preloaded applications (only some listed)															
										• Microsoft Office Trial (with 30-day license)															
										• Microsoft Office Home and Business 2019															
										• Microsoft Office Home and Student 2019															
										• Microsoft 365 Family															
										• Microsoft 365 Personal															
										• Microsoft Office Professional 2019															
										• Microsoft Office Personal 2019															
									Limited warranty	One of the following, configurable by model:															
										• 1-year depot repair service															
										• 1-year depot repair with 2-year system board repair service															
										• 2-year/1-yr battery depot repair service															
									Environment	ErP lot3; RoHS-compliant															

Note: The specifications above may not be available in all regions.

Lenovo

June 2020

Lenovo

Lenovo Legion 5 15IMH05H

Lenovo



intel
inside



intel
inside



intel
inside



intel
inside



intel
inside



intel
inside