

ThinkPad X13 Yoga Gen 1 20SX0028CA

Product

ThinkPad X13 Yoga Gen 1

Region

NA

Country/Region

Canada

Machine Type

20SX

TopSeller

TopSeller

Processor

Intel Core i7-10610U (4C / 8T, 1.8 / 4.9GHz, 8MB)

Graphics

Integrated Intel UHD Graphics

Chipset

Intel SoC Platform

Memory

16GB Soldered DDR4-2666

Storage

512GB SSD M.2 2280 PCIe NVMe Opal2

Display

13.3" FHD (1920x1080) IPS 500nits AR (anti-reflection) / AS (anti-smudge), ThinkPad Privacy Guard

Touchscreen

10-point Multi-touch

Pen

ThinkPad Pen Pro (Garaged)

Media Reader

MicroSD Reader

Ethernet

100/1000M via Optional Adapter

Optical

None

WLAN + Bluetooth

Intel AX201 11ax, 2x2 + BT5.0

WWAN

None

SIM Card

None

Smart Card Reader

None

Monitor Cable

None

Bundled Accessories

None

Case Material

CF Hybrid PA + 55% GF

Camera

720p + IR with ThinkShutter

Microphone

2x, Array

Color

Black

Keyboard

Backlit, French

Fingerprint Reader

Touch Style, Match-on-Chip

NFC

None

TPM

Discrete TPM 2.0

Battery

Integrated 50Wh

Power Adapter

65W USB-C

System Management

Intel vPro

Operating System

Windows 10 Pro 64, French

Bundled Software

None

Base Warranty

3-year, Depot

Bundled Service

None

EAN / UPC / JAN

194778818896

End of Support

2026-12-05

Announce Date

2020-05-19

Recommended Services**Best**

3Y Lenovo Protect (Premier Support + Keep Your Drive + Accidental Damage Protection + Sealed Battery) (5PS0N73216)

Better

3Y Lenovo Support (Premier Support + Keep Your Drive + Sealed Battery) (5PS0N73159)

Good

3Y Premier Support Upgrade from 3Y Depot/CCI (5WS0T36160)

Notes:

Battery life is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences.

California Electronic Waste Recycling Fee

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to:

<https://www.calrecycle.ca.gov/Electronics/Consumer>

L WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2020. All rights reserved.



Lenovo™

ThinkPad X13 Yoga Gen 1 Platform Specifications

Product Specifications Reference (PSREF)

Processor	10th Generation Intel® Core™ i5 / i7 Processor											Dimensions Weight Case color Case material	WxDxH: 12.22" x 8.62" x 0.63"; 310.4mm x 219mm x 15.95mm Starting at 2.76 lb /1.25 kg Black Display cover: CF Hybrid PA + 55% GF Bottom: CF Hybrid PA + 55% GF
	Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Types	Processor Graphics					
	i5-10210U	4	8	1.6 GHz	4.2 GHz	6MB	DDR4-2666	Intel UHD Graphics					
	i5-10310U			1.7 GHz	4.4 GHz	6MB							
	i7-10510U			1.8 GHz	4.9 GHz	8MB							
	i7-10610U			1.8 GHz	4.9 GHz	8MB							
	i7-10710U	6	12	1.1 GHz	4.7 GHz	12MB							
i7-10810U	1.1 GHz			4.9 GHz	12MB								
Graphics	Intel UHD Graphics in processor; supports up to 3 independent displays via native display and two external monitors; supports external monitors via HDMI (up to 4096x2160@24Hz), USB-C (up to 4096x2304@60Hz) or Thunderbolt (up to 4096x2304@60Hz)											Smart card reader	Optional: Smart card reader
Chipset	Intel SoC (System on Chip) platform											Media reader	MicroSD card reader, in the combo slot with nano-SIM card
Memory	8GB or 16GB / 2666MHz DDR4 / soldered to systemboard, no sockets * Installed memory is actually 3200MHz but run at 2666MHz due to Intel limitation											Ports	Two USB 3.2 Gen 1 (one Always On), one USB 3.2 Type-C Gen 1 (with the function of Power Delivery and DisplayPort), one USB 3.2 Type-C Gen 2 / Thunderbolt 3 (with the function of PD and DP), HDMI 1.4b, Ethernet extension connector, combo slot of nano-SIM card (WWAN models) and microSD card reader, headphone / microphone combo jack, optional smart card reader, side docking connector, security keyhole * Depending on many factors, actual data transfer speed may be lower than theoretical speed
Display	Size	Resolution	Type	Surface	Touch	Bright-ness	Aspect Ratio	Contrast Ratio	Color Gamut	Viewing Angle	Monitor cable (optional)	• Lenovo HDMI to VGA Monitor Adapter • Lenovo USB-C to VGA Adapter • Lenovo USB-C to DisplayPort Adapter Optional: ThinkPad Ethernet Extension Adapter Gen 2	
	13.3"	FHD (1920x1080)	IPS	Anti-reflection Anti-smudge	Multi-touch	300 nits	16:9	800:1	72%	170°	Bundled Accy		
	13.3"	FHD (1920x1080) Low Power	IPS	Anti-reflection Anti-smudge	Multi-touch	400 nits	16:9	1500:1	72%	170°	Camera (optional)	• HD720p camera with ThinkShutter camera privacy, fixed focus • IR camera and HD720p camera with ThinkShutter camera privacy, fixed focus	
	13.3"	FHD (1920x1080) ThinkPad Privacy Guard	IPS	Anti-reflection Anti-smudge	Multi-touch	500 nits	16:9	1000:1	72%	170°	Audio support	HD Audio, Realtek® ALC3287 codec / Dolby® Audio speaker system, 2W x 2 / dual array far-field microphone, headphone / microphone combo jack	
	13.3"	UHD (3840x2160)	OLED	Anti-reflection Anti-smudge	Multi-touch	400 nits	16:9	100000:1	100% DCI-P3	170°	Keyboard	6-row, spill-resistant, multimedia Fn keys with Unified Communications controls, LED backlight	
	Multi-touch	Capacitive-type multi-touch, supports 10-finger gesture, anti-reflection (AR), AS (anti-smudge), could reduce the brightness by up to 10%											UltraNav™
Hinge	Yoga hinge, 360 degree											Security	Power-on password, hard disk password, supervisor password, security keyhole
Convert-mode	Laptop, tent, stand and tablet											Security chip	• Firmware TPM 2.0 integrated in chipset • Discrete TPM 2.0 TCG Certified
Pen	ThinkPad Pen Pro, active pen for multi-touch display, on-board rechargeable											System Mgt (opt)	Intel vPro Technology
Storage	• M.2 2242 SSD / PCIe NVMe, PCIe 3.0 x 2 • M.2 2280 SSD / PCIe NVMe, PCIe 3.0 x 4 • Intel Optane™ Memory H10 with Solid State Storage, M.2 2280, PCIe NVMe 3.0 x 4											Fingerprint reader	Touch style match on chip fingerprint reader on the palm rest
Optical	None											NFC (optional)	Near Field Communication
Ethernet	Native Intel Ethernet Connection I219-V (Non-vPro) or I219-LM (vPro) via optional ThinkPad Ethernet Extension Adapter Gen 2											Battery	Integrated Li-ion 50Wh battery, supports Rapid Charge (charge up to 80% in 1hr) with 65W AC adapter
WLAN + Bluetooth™ (opt)	Intel Wi-Fi 6 AX201, Wi-Fi 2x2 802.11ax + Bluetooth 5.0 * Intel AX201 card supports BT5.1 but is limited to BT5.0 by Windows OS											Max battery life	MobileMark® 2014: 18.2 hr MobileMark 2018: 12.05 hr * Battery life varies significantly with hardware configurations, settings, usage, & other factors
WWAN (optional)	• Integrated Mobile Broadband 4G LTE-A, Fibocom L850-GL, M.2 card • Integrated Mobile Broadband 4G LTE-A, Fibocom L860-GL, MIMO 2x2, M.2 card * For non-WWAN model, it means the model is NOT WWAN upgradable											AC adapter	• 45W USB-C AC adapter • 65W USB-C AC adapter • 65W USB-C slim AC adapter
SIM card (opt)	Gemalto eSIM Card											Operating system	Optional: Windows® 10 Home 64 or Windows 10 Pro 64
												Limited warranty (optional)	• 1-year depot repair service • 1-year depot with 2-year system board repair service • 1-year limited onsite service • 1-year + 2-year depot repair service • 1-year + 2-year limited onsite service • 3-year/1-yr battery depot repair service • 3-year/1-yr battery limited onsite service
												Mil-Spec test	MIL-STD-810G military testing
												Environment	EPEAT™ Gold; ENERGY STAR® 8.0; RoHS-compliant

Note: The specifications above may not be available in all regions.

Lenovo
June 2020

Lenovo

ThinkPad X13 Yoga Gen 1

