

**msi**®

M O T H E R B O A R D

B450M BAZOOKA MAX WIFI

BLAST AWAY THE COMPETITION

**FEATURE****Turbo M.2**

Delivering Speeds Up to 32Gb/s

**Core Boost**

With premium layout and fully digital power design to support more cores and provide better performance.

**DDR4 Boost**

Advanced technology to deliver pure data signals for the best gaming performance and stability.

**Audio Boost**

Reward your ears with studio grade sound quality for the most immersive audio experience.

**PCI-E Steel Armor**

Protecting VGA cards against bending and EMI

**Mystic Light Extension**


Control additional RGB strips or other RGB components added to your system with Mystic Light APP and mobile device.

**Intel WiFi solution**

Build in Intel® Wi-Fi / Bluetooth, delivering AC speeds up to 433Mbps without any cable limitation.

SPECIFICATION

Model Name	B450M BAZOOKA MAX WIFI
CPU Support	Supports 1st, 2nd and 3rd Gen AMD Ryzen™ / Ryzen™ with Radeon™ Vega Graphics and 2nd Gen AMD Ryzen™ with Radeon™ Graphics / Athlon™ with Radeon™ Vega Graphics Desktop Processors for Socket AM4
CPU Socket	Socket AM4
Chipset	AMD® B450 Chipset
Graphics Interface	2 x PCI-E 3.0 x16 slots
Memory Support	4 DIMMs, Dual Channel DDR4-4133+(OC)
Storage	1 x M.2 slot, 4 x SATA 6Gb/s
SATA RAID	RAID 0, 1, 10 – Available on ports SATA1 to SATA4
USB ports	6 x USB 3.2 (Gen1) + 8 x USB 2.0
LAN	Realtek® 8111H Gigabit LAN
Audio	8-Channel(7.1) HD Audio with Audio Boost

CONNECTIONS

1. PS/2 Combo Port
2. USB 2.0 Ports
3. LAN Port
4. HD Audio Connectors
5. USB 2.0 Ports
6. HDMI Port
7. Intel Wi-Fi
8. USB 3.2 Gen1 Type A
9. USB 3.2 Gen1 Type A
10. USB 3.2 Gen1 Type A