

34WN650-W.AUS

34" 21:9 WFHD IPS HDR 400 Monitor with FreeSync

34" UltraWide FHD (2560 x 1080) IPS Display

3-Side Virtually Borderless Design

sRGB 99% Color Gamut / VESA DisplayHDR 400

Color Calibrated

AMD FreeSync

Tilt/Height Adjustable Stand



PICTURE QUALITY

Screen Size	34"
Panel Type	IPS
Color Gamut (Typ.)	sRGB 99% (CIE1931)
Color Depth(Number of Colors)	16.7M
Pixel Pitch(mm)	0.312 x 0.310 mm
Response Time (GTG)	5ms (GtG at Faster)
Refresh Rate	75Hz
Aspect Ratio	21:9
Resolution	2560X1080
Brightness	400 cd/m ² (Typ.)
Contrast Ratio	1000:1
Viewing Angle	178°(R/L), 178°(U/D)

INPUT/OUTPUT

HDMI	Yes x 2
DisplayPort	Yes x 1
Headphone Out	Yes

POWER

Type	Adapter
Input	100-240Vac, 50/60Hz
Power Save/Sleep Mode (Max)	Less than 0.3W
DC Off (Max)	Less than 0.5W
Power Consumption (Typ.)	33W
Power Consumption (Max.)	42W

SPECIAL FEATURES

Color Weakness Mode	Yes
Adaptive Sync	AMD FreeSync™
Black Stabilizer	Yes
Dynamic Action Sync	Yes
Crosshair	Yes
Flicker Safe	Yes
Smart Energy Saving	Yes
Reader Mode	Yes
Super Resolution +	Yes
Color Calibrated	Yes
Dual controller	Yes
On Screen Control (OSC)	Yes
HDR (High Dynamic Range)	HDR10
VESA DisplayHDR™	DisplayHDR™ 400
HDR Effect	Yes

SOUND

Speaker	Yes
Speaker Output	7W x 2
Maxx Audio	Yes
Speaker Channel	2ch

DIMENSIONS / WEIGHTS

With Stand (WxHxD)	32.2" x 22.3" x 8.9" (UP) 32.2" x 17.9" x 8.9" (DOWN)
Without Stand (WxHxD)	32.2" x 14.4" x 1.8"
Shipping Dimensions (WxHxD)	37.01" x 20.3" x 8.6"
With Stand Weight	16.9 lbs
Without Stand Weight	13.2 lbs
Shipping Weight	24.5 lbs

STAND

Display Position Adjustments	Tilt/Height
------------------------------	-------------

CABINET / ACCESSORIES

Wall Mount Size (mm)	100 x 100 mm
HDMI	Yes

WARRANTY

Limited Warranty	1 Year Parts and Labor
UPC	719192641594