

# IdeaPad Flex 3 CB 11IGL05 82BB0023CF

**Product**

IdeaPad Flex 3 CB 11IGL05

**Region**

NA

**Country/Region**

Canada

**Machine Type**

82BB

**TopSeller**

No

**Processor**

Intel Celeron N4000 (2C / 2T, 1.1 / 2.6GHz, 4MB)

**Graphics**

Integrated Intel UHD Graphics 600

**Chipset**

Intel SoC Platform

**Memory**

4GB Soldered LPDDR4-2400

**Storage**

64GB eMMC 5.1

**Display**

11.6" HD (1366x768) IPS 250nits Glossy, touch

**Touchscreen**

10-point Multi-touch

**Pen**

None

**Optical**

None

**Card Reader**

MicroSD Card Reader

**Ethernet**

None

**WLAN + Bluetooth**

11ac, 2x2 + BT4.2

**Bundled Accessories**

None

**Camera**

720p

**Microphone**

Mono

**Surface Treatment**

AL Anodizing Stamping

**Case Material**

Aluminium (Top), PC + ABS (Bottom)

**Case Color**

Abyss Blue

**Keyboard**

Non-backlit, French / English

**Fingerprint Reader**

None

**NFC**

None

**Security Chip**

Google Security Chip H1

**Battery**

Integrated 42Wh

**Power Adapter**

45W USB-C

**Operating System**

Chrome OS

**Bundled Software**

None

**Base Warranty**

1-year, Mail-in

**Bundled Service**

None

**EAN / UPC / JAN**

195235179598

**End of Support**

2026-04-03

**Announce Date**

2020-07-27

**Notes:****California Electronic Waste Recycling Fee**

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to:

<https://www.calrecycle.ca.gov/Electronics/Consumer>

**L** [WWW.LENOVO.COM](http://WWW.LENOVO.COM)

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2020. All rights reserved.



Lenovo™

# IdeaPad Flex 3 CB 11IGL05 Intel Platform Specifications

Product Specifications Reference (PSREF)

Processor	Intel® Celeron® Processor								Dimensions	WxDxH: 11.41" x 8.18" x 0.70"; 290mm x 207.8mm x 17.8mm	
	Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Types	Processor Graphics	Weight	1.2 kg / 2.64 lb	
	Cel N4000	2	2	1.1 GHz	2.6 GHz	4MB	LPDDR4-2400	Intel UHD Graphics 600	Case color	Abyss Blue or Almond	
	Cel N4020				2.8 GHz				Case material	Display cover: Aluminum Bottom: PC/ABS plastic	
Graphics	Intel UHD Graphics 600 in processor; supports external digital monitor via USB Type-C; supports three independent displays; Max resolution: 4096x2160 @60Hz (USB Type-C)								Camera	HD720p, fixed focus	
									Audio support	HD Audio, Maxim Integrated™ MAX98357A codec / stereo speakers, 2W x 2 / mono microphone, 3.5mm (0.14inch) combo audio / microphone jack (CTIA)	
Chipset	Intel SoC (System on Chip) platform								Keyboard	6-row	
Memory	8GB max offering / 2400MHz LPDDR4, soldered to systemboard, no sockets								Touchpad	Buttonless Mylar® (BoPET) surface multi-touch touchpad	
Display	11.6" (294mm) HD (1366x768), WVA, glossy, glass, LED backlight, 250 nits, 16:9 aspect ratio, 50% NTSC gamut Supports 10-finger gesture 4 modes: notebook, tablet, stand and tent; 360° hinge None								Security	Security keyhole	
Multi-touch									Security chip	Google Security Chip H1	
									Fingerprint reader	None	
									Battery	Integrated Li-Polymer 42Wh battery	
Multi-mode									Max battery life	Google power load test® 2014: 10 hrs	
Pen									* Battery life varies significantly with hardware configurations, settings, usage, & other factors		
									AC adapter	45W USB-C AC adapter	
Storage	eMMC 5.1 (embedded Multi Media Card) flash memory on board								Preload	Google Chrome OS™	
Optical	None								Limited warranty	One of the following, configurable by model: • 1-year depot repair service • 1-year depot with 2-year system board repair service • 2-year/1-yr battery depot repair service	
Ethernet	None								Environment	ENERGY STAR® 8.0; ErP lot3; RoHS-compliant	
WLAN	WiFi 5 (802.11ac), 2x2 Wi-Fi + Bluetooth 4.2, M.2 Card										
Bluetooth™	Bluetooth 4.2 wireless, integrated in Wi-Fi + Bluetooth combo adapter										
Media reader	MicroSD™ Card Two USB 3.1 Type-A Gen 1, MicroSD card reader, Two USB 3.1 Gen 1 Type-C™ (with the function of power delivery, data transfer and DisplayPort 1.1a), 3.5mm (0.14inch) headphone / microphone combo jack (CTIA) * Depending on many factors, actual data transfer speed may be lower than theoretical speed										
Ports											

Note: The specifications above may not be available in all regions and might change by regions.

Lenovo  
July 2020

Lenovo™

# IdeaPad Flex 3 CB 11IGL05

Lenovo™

