

**msi**®

MONITOR

Optix MAG240CR

SEE BEYOND THE GAME. VISUALIZE YOUR VICTORY.

**FEATURE****Curved Gaming**

MSI Curved Gaming Monitor will give you the most immersive and competitive edge you need to take down your opponents.

**165Hz High Refresh Rate**

Experience smooth gaming with a blazing fast 165Hz refresh rate, that gives you the upperhand in fast moving games

**1ms Fast Response Time**

Eliminate screen tearing and choppy frame rates with 1ms response time.

**Mystic Light**

Make your build look on fire or cold as ice. You are in control. Customize colors and effects with RGB LED.

**Gaming OSD APP**

Customize and set the ultimate monitor modes with keyboard & mouse in a very easy way.

**Adjustable Stand**

Maximize your productivity and comfort with the adjustable stand.

CONNECTIONS

| | |
|-------------------------|-----------------------|
| 1. 1x USB 2.0 Type B | 5. 1x Earphone |
| 2. 1x HDMI (2.0) | 6. 1x DC jack |
| 3. 1x HDMI(1.4) | 7. 1x Kensington Lock |
| 4. 1x Display Port(1.2) | |

SPECIFICATION

| | |
|--------------------------|---|
| DCI-P3 / sRGB | 97.46% / 124.13% |
| Panel Size | 23.6" (60 cm) |
| Aspect ratio | 16:9 |
| Panel Resolution | 1920 x 1080 (FHD) |
| Pixel Pitch (H x V) | 0.27156 (H) x 0.27156 (V) |
| Refresh Rate | 165Hz |
| Response time | 1ms (MPRT) |
| Viewing angle | 178° (H) / 178° (V) |
| Curved | 1800R |
| Brightness | 250 cd / m ² |
| Contrast Ratio | 3000:1 |
| Power consumption | 33W |
| Control | 5-way OSD navigation joystick |
| Dimension (W x H x D) | 536.6 x 389.3 x 205.4 mm ; 21.13 x 15.33 x 8.09 inch |
| Weight | 4.89kg / 7.1kg ; 10.78lbs / 15.65lbs |
| Panel Type | VA |
| DCR | 100000000:1 |
| Active Display Area (mm) | 521.3952(H) x 293.2848(V) |
| Surface Treatment | Anti-glare |
| Display Colors | 16.7M |
| Video ports | 1x Display Port (1.2) 1x HDMI (2.0) 1x HDMI (1.4a) |
| VESA Mounting | 75 mm x 75 mm |
| Power Type | External Adaptor 12V 4A |
| Power Input | 100-240V, 50-60Hz |
| Signal Frequency | 30 to 160KHz 60 to 165Hz |
| Adjustment (Tilt) | -5° ~ 20° |
| Note | Display Port: 1920 x 1080 (Up to 165Hz) HDMI 2.0: 1920 x 1080 (Up to 165Hz) HDMI 1.4a: 1920 x 1080 (Up to 144Hz) DCI-P3 and sRGB follow CIE1976 Standard |
| Audio ports | 1x Earphone out |
| Kensington Lock | Yes |
| Adjustment (Swivel) | -30° ~ 30° |
| Adjustment (Height) | 0 ~ 65 mm |