



DU-1000

Keyboard with Polycarbonate Case

The DU-1000 from iKey features the convenience of a full numeric keypad and a lightweight polycarbonate case. Suitable for 19-inch rack applications, the DU-1000 offers 104-key functionality and USB compatibility. It has 12 function keys as well as mounting holes in case. This model replaces the DP-1000.

- Features:
- 10-Key Numeric Pad
 - 104-Key Functionality
 - Polycarbonate Case with Mounting Holes
 - PS/2 or USB configurations available

Product Code DU-1000

CERTIFICATIONS	NEMA 4X, UL60950, FCC Part 15 Class B
SHOCK	3x11 ms pulses of 50g on each of 3 axes
CABLE	LENGTH: 10 feet (3 meters) DESIGN: PS/2 or Single-Cable USB
KEY SWITCH	MATERIAL: Industrial silicone rubber LIFE: 10 million cycles TRAVEL: 0.055 in. (1.4mm) ACTUATION FORCE: 6.35 oz. +/- 1.06 oz. (180g +/- 30g) FEEDBACK: Tactile with mechanical snap
VIBRATION	POWER SPECTRAL DENSITY: 0.04g/Hz FREQUENCY RANGE: 20Hz - 2 kHz DURATION OF TEST PER AXIS: 3 hours
POWER	PS/2 or AT/Serial: 50mA@5V (from Keyboard port) USB: 50mA@5V (from CPU port)
COMPATIBILITY	PS/2: All Windows Operating Systems USB: All Windows and Macintosh OS
TEMPERATURE RANGE	STORAGE: -40C to +90C (-40F to +194F) OPERATING: -40C to +70C (-40F to +158F)
WEIGHT	2.25 lbs +/- 0.10 lbs (1.02 kg +/- 0.05 kg)
WARRANTY	1 year limited warranty
HUMIDITY	100%
DIMENSIONS	14.94" x 6.63" x 1.81" (w-h-d) 379.5mm x 168.4mm x 45.9mm
MODEL NUMBERS	DU-1000-PS2: With PS/2 cable DU-1000-USB: With USB cable