

Eaton EMI347-03

Catalog Number: EMI347-03

Eaton Metered Input rack PDU, 0U, 14.4kW max, 200-240V, 40 A, 3 ft cord, Three-phase, Outlets: (48) C13, (12) C19, CS8365, input

General specifications



Product Name	Catalog Number
Eaton metered input rack PDU	EMI347-03
UPC	Product Length/Depth
786685985183	63.2 in
Product Height	Product Width
2.09 in	4.1 in
Product Weight	Warranty
15.4 lb	3 year
Compliances	Certifications
Contact Manufacturer	UL Listed

defaultTaxonomyAttributeLabel

Type

PDU

Form factor

0U (Vertical)

Outlet control

No

Operating Temperature

0° to 60°C (32° to 140°F)

Mounting direction

Vertical

Color

Black

Input connection

CS8365

Cord length

3 ft

Wattage

14.4 kW max

Amperage Rating

40A

Input voltage

200-240V

Phase

Three-phase

Frequency rating

50-60 Hz

Outlets

(48) C13, (12) C19

Number of Outputs C13

48

Number of Outputs C19

12

Circuit breaker

(6) 20A

Ethernet interface

Resources

Certification reports

[Eaton RoHS Declaration of Conformity: ePDU G3](#)

Drawings

[Eaton ePDU G3 Metered Input EMI347-03 technical drawing](#)

[Eaton PDU EMI347-03 technical drawing](#)

Manuals and user guides

[Eaton ePDU G3 EMP installation and connection quick start guide](#)

[Eaton ePDU G3 instruction set - system objects](#)

[Eaton ePDU G3 installation and connectivity quick start guide](#)

[Eaton ePDU G3 operations manual](#)

Service and troubleshooting

[EMI347-03 eNMC replacement configuration file](#)

Specifications and datasheets

[Eaton Specification Sheet - EMI347-03](#)

Yes

Serial interface

RS-232

Switchable

No

Fitted with:

Ampere Meter

Series

Metered Input



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)