



^ Overview

Dimensions

442 x 325 x 44 mm
(17.4 x 12.8 x 1.7")

UniFi Application Suite

Protect

✓

Access

✓

Managed Cameras

(60) HD
(30) 2K
(18) 4K

Managed Access Hubs

150

Storage Capacity

(4) 3.5" drive bays

Data Protection

✓

Vantage Point

✓

Networking Interface

(1) 10G SFP+ port
(1) GbE RJ45 port

Power Redundancy

✓

Form Factor

Rack mount (1U)

Door Access Support

✓

^ Hardware

Hard Drive Capacity

(4) 2.5/3.5" HDD / SSD support

Max. Power Budget for Drives

75W

Max. Power Consumption

100W

Power Method

(1) Universal AC input, 100—240V AC, 2A Max., 50/60 Hz
(1) USP-RPS DC input, 11.5V DC, 10.43A

Power Supply

AC/DC, internal, 120W

Processor

Quad ARM® Cortex®-A57 cores at 1.7GHz

Memory

4GB

Management

Ethernet

Weight

Without mounting brackets: 5.1 kg (11.3 lb)
With mounting brackets: 5.2 kg (11.5 lb)

Enclosure Material

SGCC steel

Mount Material

SGCC steel

Ambient Operating Temperature

-5 to 40° C (23 to 104° F)

Ambient Operating Humidity

5 to 95% noncondensing

NDA Compliant

✓

Certifications

CE, FCC, IC, SRRC, Anatel: 01924-21-08356

