

Avery Dennison® Monarch® 1130® and 1131® Handheld Labelers

EFFICIENT PRICE MANAGEMENT

The Avery Dennison® Monarch® 1130® and 1131® handheld labelers feature a large label capacity for labeling up to 2,500 products without stopping, so products get to the sales floor more quickly.*

Easy-to-Read Labels Improve Checkout Accuracy

Print is clear and easy to read; there's no question about pricing at checkout.

Large Selection of Stock Labels

- Variety of colors, including fluorescents
- Preprinted with merchandise-moving promotional messages
- Tear-away part gum label for "after the sale" pricing that eliminates the need to reprice
- Durable label that can withstand the toughest of outdoor elements
- Special features such as security slits to deter price switching are available

ABOUT MONARCH LABELERS

- Red "touchpoints" are incorporated throughout the labelers to help guide the user through important tasks such as loading, clearing jams and removing the ink rollers
- Instructional videos are easily accessed by scanning the QR code conveniently located on the labeler
- Most labelers take about 75% less time to load labels and roughly 97% less time to change ink rollers than other similar labelers on the market
- Made in the USA from practically indestructible ABS plastic and drop tested to ensure they'll last for decades
- All of our labelers are covered by a one-year warranty and we also offer 48-hour turnaround repairs on all labelers

ELEVATING BRANDS. ACCELERATING PERFORMANCE

For more information call: 800.543.6650, prompt 5 or email: shopmonarch@averydennison.com



SALE

Fluorescent Red



Innovative, intelligent and sustainable labeling and printing solutions that accelerate supply chain performance, increase productivity and elevate the consumer experience.

Avery Dennison® Monarch® 1130® and 1131® Handheld Labelers



SPECIFICATIONS

OPERATING METHOD
Squeeze, release and apply

INKING METHOD
Disposable porous roller

WEIGHT
14.1 oz. (400g) when loaded with one roll of labels

FEED DIRECTION
Landscape (horizontal)

PRINT DIRECTION
Landscape (horizontal)

LINES OF PRINT
One

MAX. BANDS PER PRINTHEAD
1130: Six
1131: Eight

CHARACTER HEIGHT
Maximum 5mm

LABEL DIMENSIONS
0.62" (15.7mm) x 0.44" (11.2mm)

NUMBER OF LABELS PER ROLL
2,500

NUMBER OF ROLLS PER SLEEVE
Ten

LIMITED WRITTEN WARRANTY
One year

AMERICAS

170 Monarch Lane
Miamisburg, OH 45342
937 865 2123 (direct)
Tel +800 543 6650
(8:00 a.m.–6:30 p.m., EDT)
Fax +937 865 6663

ASIA


No. 7 Chun Ying Street
Tseung Kwan O Industrial
Estate
New Territories, Hong Kong
Tel +852 2372 3169
Fax +852 2995 0014

WESTERN EUROPE

1 Thomas Road
Wooburn Green
Bucks HP10 0PE
Tel +(44) 1628 859500
Fax +(44) 1628 859567


ASIA PACIFIC

NEW SOUTH WA
61 Vore Street
Silverwater NSW 2128
Tel +(02) 9647 1833
Fax +(02) 9647 1914
Toll free (Outside Sydney only)



Model MO113104
prints in 8 positions

JAN	.	.	1	1	1	1	1	1
FEB	1	1	2	2	2	2	2	2
MAR	2	2	3	3	3	3	3	3
APR	3	3	4	4	4	4	4	4
MAY	4	4	5	5	5	5	5	5
JUN	5	5	6	6	6	6	6	6
JUL	6	6	7	7	7	7	7	7
AUG	7	7	8	8	8	8	8	8
SEP	8	8	9	9	9	9	9	9
OCT	9	9	0	0	0	0	0	0
NOV	0	0	1	1	1	1	1	1
DEC	1	1	2	2	2	2	2	2
TX	-	-	\$:	:	:	:	:



Model MO113107
prints in 8 positions

1	1	1	1
2	2	2	2	1	1	1	1	1
3	3	3	3	2	2	2	2	2
4	4	4	4	3	3	3	3	3
5	5	5	5	4	4	4	4	4
6	6	6	6	5	5	5	5	5
7	7	7	7	6	6	6	6	6
8	8	8	8	7	7	7	7	7
9	9	9	9	8	8	8	8	8
0	0	0	0	9	9	9	9	9
\$	\$	\$	\$	0	0	0	0	0
FOR	FOR	FOR	FOR	///	///	///	///	///
///	///	///	///	---	---	---	---	---



Model 1130-01
prints in 6 positions

1	1	.	.	1	1
2	2	1	1	2	2
3	3	2	2	3	3
4	4	3	3	4	4
5	5	4	4	5	5
6	6	5	5	6	6
7	7	6	6	7	7
8	8	7	7	8	8
9	9	8	8	9	9
0	0	9	9	0	0
\$	\$	0	0	TX	TX
FOR	FOR	///	///	---	---
///	///	---	---	---	---

SERVICE

The Monarch 1130 and 1131 Handheld labelers are backed by the best service organization in the industry. This includes 24-hour turnaround repair and your guarantee of 100% satisfaction. Discover for yourself how these quality labelers will help you complete your necessary marking tasks easily and efficiently.

Accelerating supply chain
performance and elevating
the consumer experience.

The information contained herein is believed to be reliable but Avery Dennison makes no representations concerning the accuracy or correctness of the data. This product, like any other should be tested by the customer/user thoroughly under end user conditions to ensure the product meets the particular requirements. Independent results may vary. Avery Dennison and the logo are registered trademarks of Avery Dennison Corp. Third party trademarks and/or trade names used herein are the property of their respective owner(s). ©2017 Avery Dennison Corporation, All Rights Reserved.