

KODAK PIXPRO WPZ2

DIGITAL CAMERA



WPZ2 RUGGED CAMERA

The KODAK PIXPRO WPZ2 Digital Camera is the perfect companion to get wet. Shockproof, dustproof, and adventure ready, the WPZ2 was built to take on the go and be used in, on and under the water. With a host of scene modes and 1080p HD video to help you capture your best shots, the WPZ2 is not going to miss a beat. Built-in Wi-Fi® allows you to connect the WPZ2 to your iOS™/ANDROID™ device and share your outdoor adventures with friends or on social media. KODAK PIXPRO Digital Cameras – Tell your story.

FEATURES:

- 16 MP CMOS Sensor
- 4x Optical Zoom
- 1080p HD Video
- 15m Waterproof
- 2m Shockproof/Dustproof
- Wi-Fi® Connection
- Li-ion Battery



PIXPRO Remote Viewer App



4X
Optical
Zoom

16MP
CMOS

1080p
Full HD

15m/49FT
Waterproof

2m/6FT
Shockproof

Lithium-ion
Battery



Available
Colors:

YELLOW



KODAK PIXPRO WPZ2

DIGITAL CAMERA

SPECIFICATIONS		WPZ2
Effective Image Sensor Pixels	16.35 Megapixels	
Total Image Sensor Pixels	16.76 Megapixels [1/2.3" BSI CMOS]	
Lens	Focal Length [35mm film equivalent] 4.9 mm (Wide) — 19.6 mm (Tele) [27 mm (Wide) — 108 mm (Tele)] F number F3.0 (Wide) — F6.6 (Tele) Lens Construction 7 groups 7 elements Optical Zoom 4x Focusing Range Normal: (Wide) 60cm — ∞ (Tele) 100 — ∞ Macro: 5cm — ∞ (Wide Only)	
Autofocus System	TTL Autofocus	
Anti-Handshake	Digital Image Stabilization	
Digital Zoom	6x Digital Zoom (Combined Zoom: 24x)	
Number of Recording Pixels		
Still Image	(4:3) 16MP: 4608×3456, 10MP: 3648×2736, 5MP: 2592×1944, 3MP: 2048×1536, 0.3MP: 640x480, (3:2) 14MP: 4608×3072, (16:9) 12MP: 4608×2592, 2MP: 1920x1080	
Movie	1920x1080: 30fps, 1280x720: 60 fps / 30fps, 640x480: 30fps; High Speed Movie 640x480: 120fps	
Image Compression	Best, Fine, Normal	
DCF, DPOF (Ver1.1) Support	Yes	
File Format		
Still Image	Exif 2.3 (JPEG)	
Movie	MOV [Image: H. 264; Audio: Linear PCM (Stereo)]	
Shooting Modes	Auto, P, M, Wi-Fi, SCN, Movie, Underwater, Panorama, Children, Portrait, Night Portrait, Landscape, Sport, Sunset, Fireworks, Snow, Party, Beach, Night Landscape, Glass, Panning Shot, Indoor, Leaf, Museum, Imaging Stabilization	
Detection Features	Face, Smile, Blink	
Waterproof	Up to 15m / 49ft	
Shockproof	Up to 2m / 6ft	
Dustproof	Equivalent to JIS/IEC (IP6X)	
Red-Eye Removal	Yes	
HDR (High Dynamic Range)	Yes (Post-Processing)	
Scan Panorama	Up to 360°	
LCD Display	2.7 inch (230K Pixels)	
ISO Sensitivity	Auto, ISO 100/200/400/800/1600/3200	
AF Method	Single AF, Multi-AF (TTL 25-point), Face-Detection	
Exposure Metering Method	Artificial Intelligence AE (AiAE), Center-Weighted Average, Spot (Fixed to Center of Frame), Face AE	
Exposure Control Method	Program AE (AE-Lock Available)	
Exposure Compensation	+/- 3EV in 1/3 Step Increments	
Shutter Speed	1/2000 ~ 4 Seconds (Manual: 30 Seconds)	
Burst Mode	Approx. 6fps (Full Resolution)	
Playback Modes	Single, Index (9/16 Thumbnails), Slide Show, Date, Burst Shooting, Zoom (Approx. x2 ~ x8)	
White Balance Control	Auto (AWB), Daylight, Cloudy, Fluorescent, Fluorescent CWF, Incandescent, Manual, Underwater, Color Temperature, Setting(1900K ~ 10000K)	
Flash		
Flash Method	Internal	
Flash Modes	Auto, Red-Eye Reduction, Fill Flash, Slow Synchro, Red-Eye Reduction + Slow Synchro, Force Off	
Shooting Range	(Wide) Approx. 0.3m ~ 5.2m (ISO800) (Tele) Approx. 1.0m ~ 2.4m (ISO800)	
Recycle Time	6 seconds or less	
Recording Media	Internal Memory: Approx. 8MB, micro SD/ micro SDHC Card (Up to 32GB Support/Class 4 or Higher) [MMC Card Not Supported]	
Other Features	Wi-Fi (802.11 b/g/n), Remote Control (via iOS™/ANDROID™ Device), Multi-Language Support (26 Languages)	
Jacks	USB 2.0 (Micro 5 pin USB)	
Power	Rechargeable Li-ion Battery (LB-015), 3.7V 700mAh, In-Camera Charging	
Shooting Capability (Battery Performance)	Approx.200 Shots (Based on CIPA Standards), Approx. 1h 10min for Video (@1080p/30fps)	
Operation Environment	Temperature: 32° – 104°F / 0° – 40°C, Humidity: 0 – 90%	
Dimensions (WxHxD)	Approx. 95 x 63 x 25mm / 3.74 x 2.48 x .98in (Based on CIPA Standards)	
Weight	Approx. 6.21 oz. / 176g (Body Only)	
Supplied Accessories	Rechargeable Li-ion Battery, Wrist Strap, Quick Start Guide, USB cable, AC adapter, Warranty Card, and Service Card	

JK Imaging Ltd.

17239 So. Main Street, Gardena, CA 90248 (888) 978-0806

© 2020 JK Imaging, Ltd. The Kodak trademark, logo and trade dress are used under license from Eastman Kodak Company.
All information contained in this document is subject to change without notice. Document Number/Sequence: U.DIS.0061.0620.en.04

To learn more about KODAK PIXPRO Digital Cameras:
visit: kodakpixpro.com

