



Let's Talk R360 Camera Specs

Ideal for warehouses, gyms, and large open areas



12MP Progressive CMOS sensor



Up to 3008x3008 Full-HD video resolution



180° Diagonal FoV
180° Horizontal FoV
180° Vertical FoV



Immersive view – live, real-time dewarping



Up to 60 days of on-camera storage



IP66 weather resistance



Optional unlimited cloud storage available



Camera starts at \$1299



Rhombus 10-year Warranty included

About the R360

For organizations that want maximum visibility and minimal camera presence, the R360 provides a 360° view of your environment and offers multiple ways to monitor your space.

180° View displays both directions on the same horizontal plane. Immersive View is a revolutionary feature that provides live, real-time dewarping, enabling end-users to dive into the video and move around within the scene for unparalleled situational awareness.

Camera Specs

Night Vision: Infrared illuminators (100ft in low light)

Aperture: F/2.8

Ethernet: 10 / 100Mbps, MDI/MDI-X Auto Sensing

Power-over-Ethernet: Standard 802.3af for one-cable installation

AC Power: Enabled with optional adapter

Power Consumption: Max 9.9 watts

Onboard Storage Included: High-endurance 512GB

Dimensions: 130mm (5.11in) x 58mm (3.54in)

Operating Temperature: -30° to 55° C (-22° to 131° F)

Operating Humidity: 10% - 90% RH

In the Box: Torx key, mounting screws, anchors, waterproof ethernet connector

Baseline Steady State: 10 - 30 Kbps per camera

HD WAN Live Streaming: 530 - 720 Kbps per camera

CE, FCC, NDAA, TAA Compliant