



## ioSafe Duo Pro

Two copies of your data, both safe from disaster



### FIREPROOF

Built to protect your data up to 1550° F for 30 minutes, the Duo Pro can withstand house or office fires easily. While the computer might go up in smoke, your hard drives will remain pristine.



### TWICE THE BACKUP

The Duo Pro makes two copies of your data simultaneously on two different NAS hard drives. This redundancy means your hard work is protected even if one of the hard drives breaks down.



### SPEED & RELIABILITY

The Duo Pro is fast. Seriously fast. The 10 Gbps Duo Pro connects to your computer with either a USB Type-C or standard Type-A cable. It's also equipped with NAS hard drives, which are designed for sustained use.



### WATERPROOF

If there's a fire, there's a good chance the sprinklers will drown any electronics that didn't burn up. The Duo Pro is ready for that though, capable of protecting data for up to 72 hours in 10 feet of water!



### DATA RECOVERY SERVICE

Should disaster strike, whether in the form of fire, water, or simply a failed hard drive, we'll help you get back in business. We'll even provide forensic data recovery if necessary!



### THEFTPROOF

With a built-in Kensington security slot and our optional floor mount and padlock kit, the Duo Pro can be physically secured anywhere.

# ioSafe Duo Pro

## Product Specifications

### Data Protection

DataCast™ Fire Protection  
HydroSafe™ Water Protection  
RAID Protection  
Security Protection

Protects data from fire. Up to 1550°F, 30 minutes per ASTM E-119.  
Protects data from flood. Fully submersed, fresh or salt water, 10 foot depth, 72 hours.  
RAID 1 by default. Can be configured to RAID 0, JBOD, or SPAN.  
Kensington Security Slot. Optional Floor Mount / Padlock Kit.

### Media and Connectivity

Internal HDD/SSD  
Hot Swappable HDD  
External Ports  
Supported Clients

3.5" SATA NAS hard drives x2  
No  
USB 3.0 x3 (Type-C x2, Type-A)  
Windows 10, 8.1 and 7, macOS 10.13 High Sierra or newer, most Linux distributions

### Physical

Size (HxWxD)  
Weight  
Power Supply Unit  
Operating Temperature  
Storage Temperature  
Relative Humidity  
Supported RAID Type

5.9in x 11.5in x 9.06in (150mm x 292mm x 230mm)  
31 pounds (14.0614 kg)  
60W 12V 5A Adapter  
5°C to 35°C (40°F to 95°F)  
-10°C to 70°C (15°F to 155°F)  
5% to 95% RH  
RAID 1 (default), RAID 0, JBOD, SPAN

### Environment and Packaging

Environment  
Package Content  
Optional Accessories  
Warranty  
Data Recovery Service

RoHS Compliant  
Main Unit, AC Power Cord, USB Type-C to Type-C cable, USB Type-A to Type-C cable, Quick Start Guide  
Floor Mount / Padlock Kit  
2 years warranty and 2 years Data Recovery Service  
Upgradeable to 5 year warranty and 5 year Data Recovery Service. Certain limitations apply. See website for details.

