



C32G2

() LCD MONITOR

Immersive high speed gaming

General

Model name	C32G2
Product Line	AOC Gaming
Series	G2 Series
Channel	B2C
Classification	Hero
Section	Gaming
Gaming style	Shooters, Action, eSports, FPS (eSports), Beat 'm up, Racing
Launch date	2019-04-01T00:00:00+00:00
Continent	America

Screen

Resolution	1920x1080
Refresh rate	165Hz
Flat / Curved	Curved
Curvature Radius	1500R mm
Backlight	WLED
Panel Type	VA
Aspect ratio	16:9
Display Colours	16.7 Million
Panel Colour in Bits	8
sRGB Coverage (%) (CIE 1931)	120
Adobe RGB Coverage (%) (CIE 1931)	91
NTSC coverage (%) (CIE 1931)	105 %
Active Screen Area (WxH) (mm)	698.4 x 392.85 mm
Scanning Frequency	30 -255kHz (H) 48 -240 Hz (V)
Contrast (static)	3000:1
Contrast (dynamic)	80M:1
Brightness (typical)	250 cd/m ²
Viewing angle (CR10)	178/178 °
Hard Glass	Antiglare + 3H
OSD languages	EN, FR , ES, PT, DE, IT, NL, SE, FI, PL ,CZ, RU, KR, CN (T), CN (S), JP

Exterior

Monitor colour	Black Red
Bezel Type	Narrow
Removable Stand	✓

Ergonomics

Vesa Wallmount	100x100
Tilt	3.5° ±1.5° ~ 21.5° ±1.5° °
Swivel	30° ±2° ~ 30° ±2° °
Height Adjust Amount	130mm

Connectivity and Multimedia

Signal Input	HDMI 2.0 x 2, DisplayPort 1.2 x 1
--------------	-----------------------------------

Multimedia

Audio output	Headphone out (3.5mm)
--------------	-----------------------

Features

Sync Technology	FreeSync
Sync Range	48 - 240
Flicker-free	✓
Blue Light Technology	Low blue light
Kensington Lock	✓

Power / Environmental

Powersupply	Internal
Powersource	100 - 240V 50/60Hz
Power Consumption On (Energystar test method)	31 watt
Power Consumption Standby	0.5 watt
Power Consumption Off	0.3 watt

Approbations / Regulations

TUV-Bauart	✓
FCC	✓
EAC	✓
ISO 9241-307 class I	✓

Warranty

Pixel Policy	Re-Spawned Zero Bad Pixel
Warranty Period	3 Years

Dimensions / Weights

Product Dimensions (incl base) (WxHxD) mm	713.11x530.34x244.86 inch
Carton Dimensions (WxHxD) mm	820x524x227 mm
Product Dimensions (incl base) (WxHxD) mm	713.11x530.34x244.86 mm

What's in the Box?

HDMI cable (m)	1.8 m
DisplayPort Cable (m)	1.8 m
Power Cable C13	1.8 m

Texts and USP

Marketing title	32 inch VA DisplayPort 1.2 x 1, HDMI 2.0 x 2 FreeSync
-----------------	---