

Lenovo 10e Chromebook Tablet 82AM0003US

Product

Lenovo 10e Chromebook Tablet

Region

NA

Country/Region

USA

Machine Type

82AM

TopSeller

TopSeller

Processor

MediaTek MT8183 (8C, 4x A73 @2.0GHz + 4x A53 @2.0GHz)

Graphics

Integrated ARM Mali-G72 MP3 GPU

Chipset

MediaTek SoC Platform

Memory

4GB Soldered LPDDR4X-3200

Display

10.1" WUXGA (1920x1200) WVA 400nits Glossy

Touchscreen

10-point Multi-touch

Storage

32GB eMMC 5.1

WLAN + Bluetooth

Qualcomm QCA6174A 11ac, 2x2 + BT4.2

Case Material

PC / ABS

Color

Iron Grey

Camera

Front 2.0MP / Rear 5.0MP

Microphone

2x, Array

Docking

Keyboard Dock (Pogo Pin, Detachable)

Keyboard

Non-backlit, English

Pen

None

TPM

Google Security Chip H1

Battery

Integrated 31.5Wh

Power Adapter

10W USB-C

Operating System

Chrome OS

Base Warranty

1-year, Mail-in

Bundled Service

None

EAN / UPC / JAN

195235683033

End of Support

2026-10-16

Announce Date

2020-07-21

Recommended Services

Best

3Y Depot + Accidental Damage Protection (School Year Term) (5PS0N75610)

Better

3Y Depot + Accidental Damage Protection One (School Year Term) (5PS0Z44683)

Good

3Y Depot (School Year Term) (5WS0N75691)

Notes:

Battery life is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences.

California Electronic Waste Recycling Fee

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to:

<https://www.calrecycle.ca.gov/Electronics/Consumer>

WWW.LENОВО.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2020. All rights reserved.



Lenovo™

Lenovo 10e Chromebook Tablet Platform Specifications

Product Specifications Reference (PSREF)

Processor	MediaTek® MT8183 Processor 64-bit Octa-Core Processor (4xARM Cortex-A73, up to 2.0GHz; 4xARM Cortex-A53, up to 2.0GHz)	Media reader Ports	None USB 2.0 Type-C™ (with the function of power delivery, data transfer and DisplayPort 1.1a), 3.5mm (0.14inch) combo audio / microphone jack (CTIA), one Pogo keyboard connector <i>* Depending on many factors, actual data transfer speed may be lower than theoretical speed</i>
Graphics	Integrated ARM Mali-G72 MP3 GPU supports external digital monitor via USB Type-C; supports one independent display; Max resolution: 1440x900@60Hz	Control Buttons	Power button, volume control button
Chipset	MediaTek ARM SoC (System on Chip) platform	Camera	<ul style="list-style-type: none"> • <i>Front:</i> 2MP resolution, fixed focus • <i>Rear:</i> 5MP resolution, auto focus, world facing camera
Display	10.1" WUXGA (1920x1200), WVA, 400nits Glossy with AGC Dragontrail™ Pro Glass	Audio support	HD Audio, Maxim Integrated™ MAX98357A codec / stereo speakers, 1W x 2 / dual array microphone, 3.5mm (0.14inch) combo audio / microphone jack (CTIA)
Multi-touch	OGM (one glass metal mesh) multi-touch, supports 10-finger gesture	Security chip	Google Security Chip H1
Memory	4GB max / 3200MHz LPDDR4X, soldered to systemboard	Fingerprint reader	None
Storage	32GB eMMC 5.1 flash memory on board	Battery type	Integrated Li-Polymer 31.5Wh battery
Card slot	None	Battery life	Google Power Load Test: 16.5 hrs <i>* Battery life varies significantly with hardware configurations, settings, usage, & other factors</i>
Docking (Opt)	Chrome keyboard folio, spill-resistant, mechanically-anchored keys, non-backlit	AC adapter	10W or 45W USB Type-C AC adapter
Pen	Supports pen accessory, please see the accessory compatibility for details	Preload	Google Chrome OS™
WLAN	Qualcomm QCA6174A 11ac, 2x2, 2.4 GHz / 5 GHz Wi-Fi Dual Bands, MU-MIMO, Wi-Fi + Bluetooth combo adapter	Limited warranty	<i>One of the following, configurable by model:</i> <ul style="list-style-type: none"> • 1-year mail-in repair service • 1-year limited depot repair service • 2-year/1-yr battery depot repair service
Bluetooth™	Bluetooth 4.2 wireless, integrated in Wi-Fi + Bluetooth combo adapter	Mil-Spec test	MIL-STD-810G military testing
WWAN	None	Environment	EPEAT Silver, ENERGY STAR® 8.0, TCO Certified 8.0, RoHS-compliant
Vibrator	None		
G-sensor	Accelerometer sensor		
P-sensor	None		
L-sensor	None		
E-compass	None		
Hall Sensor	Yes		
Gyroscope	Yes		
Proofing	None		
Dimensions	<i>Tablet:</i> 9.82" x 6.44" x 0.37"; 249.5mm x 163.6mm x 9.45mm <i>Tablet + Keyboard folio:</i> 9.94" x 6.55" x 0.78"; 252.5mm x 166.6mm x 20.0mm		
Weight	<i>Tablet:</i> 520g / 1.14lb <i>Tablet + Keyboard folio:</i> 960g / 2.11lb		
Case color	Iron Grey		
Case material	PC/ABS		

The specifications above may not be available in all regions and might change by region.

Lenovo
July 2020

Lenovo™

Lenovo 10e Chromebook Tablet

