

**msi**

MONITOR

**Optix MAG322CQR**

SEE BEYOND THE GAME. VISUALIZE YOUR VICTORY.

**FEATURE****WQHD**  
2560x1440**165Hz****1ms****HDR**  
READY**CONNECTIONS**

1. 5-Way Navigator
2. 1x Display Port 1.2a
3. 2x HDMI 2.0b
4. 1x USB Type C (For DP and Charge)
5. 1x Earphone
6. 1x USB 2.0 Type B (PC to Monitor)
7. 1x Kensington Lock
8. 2x USB 2.0 Type A

**SPECIFICATION**

Panel Size	31.5" (80 cm)
Panel Resolution	2560 x 1440 (WQHD)
Refresh Rate	165Hz
Response time	1ms(MPRt)
Panel Type	VA
Brightness (nits)	300
Viewing Angle	178°(H)/178°(V)
Aspect Ratio	16:9
Curvature	1500R
Contrast Ratio	3000:1
DCR	100000000:1
Active Display Area (mm)	697.344 (H) x 392.256(V)
Pixel Pitch (H x V)	0.2724 (H) x 0.2724 (V)
Surface Treatment	Anti-glare
Display Colors	1.07B (8bits +2FRC)
DCI-P3 / sRGB	96% / 124%
Video ports	1x DP (1.2a) 2x HDMI (2.0b) 1x USB Type C (DisplayPort Alternate)
USB ports	2x USB 2.0 Type A 1x USB 2.0 Type B
Audio ports	1 x Earphone out
Kensington Lock	Yes
VESA Mounting	100 x 100 mm
Power Type	Internal Adaptor
Power Input	100~240V, 50~60Hz
Signal Frequency	70.56 to 243.38kHz(H) 48 to 165Hz(V)
Adjustment (Tilt)	-5° ~ 20°
Adjustment (Height)	0 - 130mm
Dimension (W x H x D)	710.38 x 513.6 x 266.5 mm / 27.95 x 20.11 x 10.33 inch
Carton Dimension (W x H x D)	947 x 520 x 162 mm / 37.67 x 21.25 x 7.08 inch
Weight (NW / GW)	7kg / 10kg ;15.43lbs/ 21.25lbs
Frameless Design	Yes
Note	Display Port: 2560 x 1440 (Up to 165Hz) HDMI: 2560 x 1440 (Up to 144Hz) DCI-P3 and sRGB follow CIE1976 Standard