

GCS1734DPKIT

4-Port VGA and DisplayPort KVMP Kit with Audio

- Switch between four computers with the push of a button
- Offers the flexibility to mix and match computer connections: VGA and DisplayPort
- Includes 2 x DisplayPort to VGA adapters
- Switching via pushbutton, hotkey, or OSD
- Cost effective, Plug-N-Play solution



Flexibility to Choose VGA and/or DisplayPort

You finally have the flexibility to mix and match your video options with this kit, streamlining and developing efficient workstations by eliminating multiple desktop setups. With the included adapters, IOGEAR's VGA and DisplayPort KVM Solution simplifies the method of sharing four (4) computers using one VGA monitor, keyboard and mouse. This bundle is perfect for a home office or small-to-medium-size business, as it offers the flexibility to choose between VGA and/or DisplayPort connections. Take advantage of your existing DisplayPort computers, and use the included adapters to view your content on a VGA projector, monitor, or display.


- Switch between four computers with the push of a button
- Offers the flexibility to mix and match computer connections: VGA and DisplayPort
- Includes 2 x DisplayPort to VGA adapters
- Switching via pushbutton, hotkey, or OSD
- Cost effective, Plug-N-Play solution
- Control 4 computers with one keyboard, mouse and monitor
- 4-Port VGA KVM with (OSD) On-Screen Display
- 2-Port USB 2.0 Hub built in (USB Type-A)
- Video resolution: 2048x1536
- Switch between computers via push buttons, hotkeys and OSD
- IOGEAR's patented DynaSync intelligently reads and remembers the monitor's settings (EDID) with no delay when switching
- USB or PS/2** mouse and keyboard peripherals
- All cables are included
- OS Support: Windows, Linux, Mac and Sun
- Audio enabled - Full bass response provides 2.1 stereo sound
- Independent (Asynchronous) Hotkey switching between KVM focus, USB peripherals, and audio ports
- Mouse emulation bypass feature supports programmable mice
- Complete keyboard emulation for error free booting
- Sun/Mac keyboard support and emulation***
- Converts your DisplayPort to VGA
 - Connect to a VGA projector, TV or monitor
 - Works with computer systems using DisplayPort
 - Compliant with Displayport Specification 1.1a for both 1.62 Gbps and 2.7 Gbps
 - Support full DisplayPort link tracking
 - Supported resolutions:
 - Full HD 1080p
 - 1920x1200
 - VGA, SVGA, XGA, SXGA and UXGA at 162 MHz pixel rate
 - Support interrupt request output for expansion function
 - Support Deep Sleep Mode (suspend mode)

*IOGEAR's DynaSync provides the EDID support for Windows 7

**PS/2 KVM Cables are available and sold separately.

*** PC keyboard combinations emulate Sun/Mac keyboards and Sun keyboards only work with Sun computers





Requirements

- Console:
- Monitor with VGA capabilities
- Standard 104 key wired USB or PS/2 keyboard
- Standard 2 or 3 button wired USB or PS/2 mouse
- Computers:
- VGA or DisplayPort port
- USB or PS/2 connections

Package Contents

- 1 x 4-Port USB KVMP Switch
- 2 x DisplayPort to VGA Adapters
- 4 x Custom USB KVM Cable
- 1 x PS/2 to USB Adapter
- 1 x Firmware Upgrade Cable
- 1 x Power Adapter
- 1 x Installation Guide
- 1 x Warranty Card

Specifications

Function	GCS1734DPKIT	Dimensions	GCS1734DPKIT
Computer Connections		Physical Properties	
Direct	4	Unit Weight	1.2 lb
CPU Connectors		Unit Package Dimensions	3.8x 8.3x 12.8 in.
Monitor	4 x VGA; 2 x DisplayPort (with Adapters)	Unit Dimension	8x 1.7x 3.5 in.
Keyboard	USB or PS/2	Case Qty	6
Mouse	USB or PS/2	Case Weight	29.5 lb.
Microphone	3.5mm Jack	Case Dimension	17.7x 13.8x 12.6 in.
Audio	3.5mm Jack	Unit Weight with package	5.0 lb
Console Connectors			
Monitor	VGA		
Keyboard	USB		
Mouse	USB		
Microphone	3.5mm Jack		
Audio	3.5mm Jack		
Video Resolution	2048 x 1536 (DDC2B), 1920x1200 (with DP adapters)		
Cable Length	6ft (1.8m)		
Cable Connections			
Input	USB		
Output	USB or PS/2		
LEDs			
USB Peripherals	Green		
Port ID	Orange		
On Line	Orange		