Getting Started

What's Nev

Feature Story

Collaborate

Compute

Security

Connect

Switches

Wireless

Routers

RV

NEW ISR 900

ISR 110

ISR 4000

Services

Connect

Routers

Featured Products

Portfolio



Cisco ISR 900 Series

-NEW-

Create a Highly Secure, Enterprise-class Network with A Router Fit for Small and Medium-sized Businesses



I • C927-4P

150 Mbps Max Crypto Throughput

IOS IP Base x86 2.2 GHz CPU 1 GB DRAM 2 GB Flash 1-port GE-WAN 1-port VADSL Annex A 4-port GE Managed Switch 1-port USB 2.0 Type A External Power Adapter Optional 1 RU l Rack Mount

Optional Under Desk Mount

I• C931-4P

250 Mbps Max Crypto Throughput

IOS IP Base x86 2.2 GHz CPU

1 GB Dram 2 GB Flash 2-port GE-WAN 4-port GE Managed Switch 1-port USB 2.0 Type A Internal Power Supply Optional 1 RU Rack Mount Optional Under Desk Mount

Connect

Routers

NEW ISR 900

Services

Connect Routers

Featured Products

Portfolio



Cisco ISR 1100 Series

Provides Internet Access, Comprehensive Security, and Wireless Services in A Single, High-Performance Device



C1101-4PLTEP

150 Mbps Max Crypto Throughput	IOS XE IP Base	Multicore CPU	4 GB DRAM	4 GB Flash
1-port GE-WAN	LTE Advanced Pluggable	4-port GE Managed Switch	1-port USB 2.0 Type A	



C1111X-8P-DNA-PM ■NEW■

250 Mbps Max Crypto Throughput	SD-WAN IOS XE	Multicore CPU	8 GB DRAM	8 GB Flash	
1-port GE-WAN	1-port GE/SFP-WAN	8-Port GE Managed Switch	Optional PoE/PoE+	1-port USB 2.0 Type A	Optional 1 RU Rack Mount
Cisco DNA E or A or P Subscription	Application Aware Firewall	Snort IPS	URL Filtering	Umbrella Integration	Network Plug-n-Play License



Connect

Routers

NEW ISR 900

Services

Connect

Routers

Featured Products

Portfolio



Cisco RV160/260 Series

With Powerful Performance and Features at an Attractive Price Keep Your Business and Your Employees Productive and Effective













■ RV160W-x-K9-xx

600 Mbps Firewall **Throughput**

50 Mbps IPsec VPN **Throughput**

10 **IPsec VPN Tunnels**

1-port **GE/SFP-WAN**

4-port **GE-LAN**

11ac Wave 2 11n

Dual Radio 1-port USB

External Power **Adapter**

Desktop

■ RV260P-K9-xx

800+ Mbps Firewall **Throughput**

75+ Mbps **IPsec VPN Throughput**

20 **IPsec VPN** Tunnels

1-Year Web Filtering

1-port GE/SFP-WAN

4-port GE-LAN 4-port GE PoE

1-port USB

External Power Adapter

Desktop

1 RU **Rack Mount**

Getting Started

What's New

Feature Story

Collaborate

Compute

Security

Connect

Switches

Wireless

Routers

RV

NEW-ISR 900


15K 900

15R 1100

ISR 4000

Services

Connect Routers



Cotting Storted

What's New

Feature Story

Collaborate

Compute

Security

Connect

Switches

Wireless

Routers

RV

12K 800

NEW ISR 900

ISR 110

ISR 4000

Services

Connect - Routers

Cisco RV Series



Overview

Positioning Map

Platform Spec

Secure, Flexible Connectivity for Small Business

The Cisco RV Series are affordable, highly secure network access devices, designed and built for small businesses. Cisco offers a broad range of small business routers to meet any requirement from basic Internet connectivity to high-capacity, business-critical networking.

Highlights

- Dual Gigabit Ethernet WAN ports for load balancing and/or business continuity (select models)
- Dual USB ports for storage and 3G/4G modem failover (select models)
- Site-to-site and remote access VPN enable highly secure connectivity, making Cisco RV Series perfect for multiple offices and remote employees.
- Strong security by proven stateful packet inspection (SPI) firewall
- Built-in managed switch (all models)
- Built-in IEEE 802.11n/ac-compatible wireless access point (wireless models)
- Easy to set up and use with wizard-based configuration





March - July, 2019 Cisco RV Series

Connect - Routers



Getting Started

What's New

Feature Story

Collaborate

Compute

Security

Connect

Switches

Wireless

Routers

RV

NEW ISR 900

ICD 110

ISR 4000

Services



Connect

Routers

RV

NEW ISR 900

Services

Connect - Routers Cisco RV Series



Overview	Posi	tioni	ng M	ар			Pl	atfor	m Spe	ec								•		
			W	AN Po	rts		LAN	Ports		PoE		IPsec	IPsec VP	N Tunnels	Web		Wire	eless		
Product SKU	Service (CSE) SKU	FE	GE	GE/ SFP	xDSL	3G/ 4G	FE	GE	Ports	Power Budget	IEEE 802.3	Through-	Site-to- Site	Remote Access	Filter- ing	11n	11ac	2.4 GHz	5 GHz	AC Power
RV042-xx	CON-SMBS-V02xxxxx	2	-	-	-	-	4	-	-	-	-	59 Mbps	50	50	-	-	-	-	-	External
RV042G-K9-xx	CON-SMBS-RV02G9xx	-	2	-	-	-	-	4	-	-	-	75 Mbps	50	50	-	-	-	-	-	External
RV130-K9-xx	CON-SMBS-xxxxxxx	-	1	-	-	1*1	-	4	-	-	-	50 Mbps	10	10	-	-	-	-	-	External
RV130-WB-K9-xx	CON-SMBS-xxxxxxx	-	1	-	-	1*1	-	4	-	-	-	50 Mbps	10	10	•	-	-	-	-	External
RV130W-x-K9-xx	CON-SMBS-V10W9xxx	-	1	-	-	1*1	-	4	-	-	-	50 Mbps	10	10	-	•	-	•	-	External
RV130W-x-WB-K9-xx	-	-	1	-	-	1*1	-	4	-	-	-	50 Mbps	10	10	•	•	-	•	-	External
RV132W-x-K9-xx	CON-SMBS-RV13K9xx	1	-	-	1	1*1	3	-	-	-	-	3 Mbps	5	5	-	•	-	•	-	External
RV134W-x-K9-xx	CON-SMBS-RV134Wxx	-	1	-	1	1*1	-	4	-	-	-	20 Mbps	5	5	-	•	•	•	•	External
RV160-K9-xx	CON-SMBS-RV16xxxx	-	-	1	-	-	-	4	-	-	-	50 Mbps	10	10	-	-	-	-	-	External
RV160W-x-K9-xx	CON-SMBS-RV16xxxx	-	-	1	-	-	-	4	-	-	-	50 Mbps	10	10	-	•	•	•	•	External
RV215W-x-K9-xx	CON-SMBS-RV25W9xx	1	-	-	-	1*1	4	-	-	-	-	5 Mbps	1	5	-	•	-	•	-	External
RV260-K9-xx	CON-SMBS-RV260xxx	-	-	1	-	1*1	-	8	-	-	-	75 Mbps	20	20	•*2	-	-	-	-	External
RV260P-K9-xx	CON-SMBS-RV260xxx	-	-	1	-	1*1	-	8	4	60 W	af	75 Mbps	20	20	●*2	-	-	-	-	External
RV260W-x-K9-xx	CON-SMBS-RVxxxxxx	-	-	1	-	1*1	-	8	-	-	-	75 Mbps	20	20	●* ²	•	•	•	•	External
RV320-K9-xx	CON-SMBS-RV3xxxxx	-	2	-	-	1*1	-	4	-	-	-	100 Mbps	25	25	-	-	-	-	-	External
RV325-K9-xx	CON-SMBS-RV35K9xx	-	2	-	-	1*1	-	14	-	-	-	100 Mbps	25	25	-	-	-	-	-	External
RV340-K9-xx	CON-SMBS-RV340Kxx	-	2	=:	-	1*1	-	4	-	-	-	650 Mbps	50	50	●*3	-	-	-	-	External
RV340W-x-K9-xx	-	-	2	-	-	1*1	-	4	-	-	-	650 Mbps	50	50	●*3	•	•	•	•	External
RV345-K9-xx	CON-SMBS-V345K9xx	-	2	-	-	1*1	-	16	-	-	-	650 Mbps	50	50	●*3	-	-	-	-	External
RV345P-K9-xx	CON-SMBS-RV345Pxx	-	2	-	-	1*1	-	16	8	120 W		650 Mbps	50	50	● *3	-	-	-	-	External

^{*1 3}G/4G modem is required. *2 Available for one year. *3 Security License (LS-RV34X-SEC-1YR=) is required.

Connect - Routers

Cisco ISR 800 Series



Getting Started

What's New

Feature Story

Collaborate

Compute

Security

Connect

Switches

Wireless

Routers

ΚV

ISR 800

NEW ISR 900

ICD 110

ISR 4000

Services

Overview Platform Spec Licenses & Accessories

■ Small but Mighty Business-class Routers

Do you have limited space, but need best-in-class routing, voice and video, security, application performance, cloud connection, and wireless capabilities? The Cisco ISR 800 Series routers offer all that in a single device. They are well suited for customer premises and priced for small and midsize businesses.

Highlights

- Cisco IOS Universal Image (IP Base/Advanced Security/Advanced IP Services)
- Dual WAN ports for load balancing and/or business continuity (select models)
- 4G LTE wireless WAN (select models)
- Built-in managed switch (all models)
- Built-in IEEE 802.11n-compatible wireless access point (wireless models)
- Easy to set up and use with wizard-based configuration (Cisco Configuration Professional Express)





Getting Started

What's New

Feature Story

Collaborate

Compute

Security

Connect

Switches

Wireless

Routers

RV

ISR 800

NEW ISR 900

ISR 110

ISR 4000

Services

Connect - Routers Cisco ISR 800 Series



Overview

Platform Spec

Licenses & Accessories

			WAN Ports						LAN Ports		Wireless			Security		Rack
Product SKU	Service (CSE) SKU	Cisco IOS	FE	GE	GE/ SFP	ISDN	xDSL	Voice	FE	GE	AP	4G LTE	AppX	FW	VPN	mount
C819H-K9	CON-SMBS-C819HK9	Advanced IP Services	-	1	-	-	-	-	4	-	-	-	•	•	•	_*3
C819G-LTE-LA-K9	CON-SMBS-C819TEK9	Advanced IP Services	-	1	-	-	-	-	4	-	-	•	•	•	•	_*4
C819GW-LTE-LA-xK9*1	CON-SMBS-C8QT9GWL	Advanced IP Services	-	1	-	-	-	-	4	-	•	•	•	•	•	_*4
C841M-4X/K9	CON-SMBS-C841M4XK	Advanced IP Services	-	2	-	-	-	-	-	4	-	-	-	•	•	_*5
C841M-8X/K9	CON-SMBS-C841M8XK	Advanced IP Services	-	2	-	-	-	-	-	4	-	-	-	•	•	_*5
C867VAE	CON-SMBS-C867VAE	IP Base	-	1	-	-	1	-	3	2	-	-	-	-	-	-
C867VAE-K9	CON-SMBS-C867VAK9	Advanced Security	-	1	-	-	1	-	3	2	-	-	-	•	•	-
C881W-x-K9	CON-SMBS-C881WxK9	Advanced Security	1	-	-	-	-	-	4	-	•	-	-	•	•	-
C891F-K9	CON-SMBS-C891F8BB	Advanced IP Services	1	-	1	1	-	-	-	8	-	-	●* ²	•	•	_*6
C891-24X/K9	CON-SMBS-C89124K9	Advanced IP Services	-	-	2	-	-	-	-	24	-	-	-	•	•	_*7
C892FSP-K9	CON-SMBS-C892FSPK	Advanced IP Services	-	1	1	-	-	-	-	8	-	-	●* ²	•	•	_*6
C897VA-K9	CON-SMBS-C897VAK9	Advanced IP Services	-	-	1	1	1	-	-	8	-	-	●* ²	•	•	_*6
C897VAG-LTE-LA-K9	CON-SMBS-CLTEAGK9	Advanced IP Services	-	-	1	-	1	-	-	8	-	•	●*²	•	•	_*6
C898EAG-LTE-LA-K9	CON-SMBS-C898EAGA	Advanced IP Services	-	-	1	-	1	-	-	8	-	•	●* ²	•	•	_*6
C899G-LTE-LA-K9	CON-SMBS-C89LKEGL	Advanced IP Services	-	1	1	-	-	-	-	8	-	•	●* ²	•	•	_*6

*1 The "x" corresponds to the supported domain. *2 Feature License is required.

^{*3} Optional Floor/Wall Mounting Kit (ACS-810-FWM) and Flat Floor/Wall Mounting Kit (ACS-810-RFWM) are available.

*4 Optional Floor/Wall Mounting Kit (ACS-810-FWM), Flat Floor/Wall Mounting Kit (ACS-810-RFWM), and Din Rail Mounting Kit (ACS-810-DM) are available.

*5 ACS-800M-RM-19 is required. *6 ACS-890-RM-19 is required. *7 ACS-2901-RM-19 is required.

What's Now

Feature Story

Collaborate

Compute

Security

Connect

Switches

Wireless

Routers

 KV

ISR 800

NEW ISR 900

ISR 110

ISR ADDO

Services

Connect - Routers

Cisco ISR 800 Series



Overview

Platform Spec

Licenses & Accessories

Cisco IOS Advanced IP Services Licenses

Product SKU	Description
SL-880-AIS	Cisco IOS Advanced IP Services License for Cisco 881W
L-880-AIS=	Cisco IOS Advanced IP Services License for Cisco 881W (eDelivery)

Cisco IOS Feature Licenses

Product SKU	Description
L-FL-C800-APP=	Cisco IOS APP License for Cisco ISR 891F/892FSP/897VA/899G

Cisco WAN Interface Modules for Cisco ISR 841M

Product SKU	Description
WIM-1T	Serial WAN Module (1-port)
WIM-3G	Multi Mode 3G WAN Module (Dual SIM)
WIM-LTE-AS	4G LTE WAN Module (Single SIM, Bands Supported: B1, B3, B5, B8, B40, B41)

PoE-capable Power Supply Module

Product SKU	Description
800-IL-PM-4	4-port PoE-capable Power Supply Module for Cisco ISR 891F/897VA/897VAG/898EAG/899G

Connect - Routers

Cisco ISR 900 Series NEW



Getting Started

What's New

Feature Story

Collaborate

Compute

Security

Connect

Switches

Wireless

Routers

RV

ISK OUC

NEW ISR 900

ISD 110

ISR 4000

Services

Overview Platform Spec Licenses Transition Guide

■ Enterprise-class Routing for Small and Home Offices

The Cisco ISR 900 Series combines WAN and comprehensive security in a compact, fanless platform. The routers are designed to provide enterprise-class security and connectivity for small to medium-sized businesses.

The ISRs come with a 4-port managed switch, providing LAN ports to connect multiple devices and up to 250 Mbps of VPN throughput for high performance. These small yet powerful fixed configuration routers provide secure broadband, Metro Ethernet, and DSL connectivity. The ISRs deliver integrated security and threat defense, protecting networks from both known and new Internet vulnerabilities and attacks. The ISRs offer easy management and provisioning capabilities through Cisco Configuration Professional Express, Cisco DNA Center, and Cisco IOS Software, with full visibility into and control of network configurations and applications.

Highlights

- Cisco IOS Universal Image (IP Base/SEC/APP)
- High-performance Intel x86 2.2 GHz CPU
- Dual WAN ports for load balancing and/or business continuity
- 4G LTE wireless WAN (Roadmap)
- Built-in managed switch (all models)
- Noiseless, flexible deployment in a fanless design
- Easy to set up and use with wizard-based configuration (Cisco Configuration Professional Express)



Getting Started

What's New

Feature Story

Collaborate

Compute

Security

Connect

Switches

VVireless

Routers

RV

13K 000

NEW ISR 900

SR 110

ISR ADDO

Services

Connect - Routers

Cisco ISR 900 Series NEW



Overview	Platform Spec	Licenses	Transition Guide
----------	---------------	----------	------------------

Cisco ISR 900 Series

Duadwat CVII	0 (005) 0(4)	0: 100	Crypto	WAN Ports			LAN Wireless		A V	Security		DRAM	Power	Rack	
Product SKU Service (CSE) SKU	Cisco IOS	Throughput*1	GE	SFP	xDSL	GE	AP	4G LTE	AppX	FW	VPN	DRAIM	Supply	Mount	
C921-4P	-	IP Base*2	150 Mbps	2	-	-	4	-	-	_*6	_*7	_*7	1 GB	Internal	_*8
C926-4P	-	IP Base*2	150 Mbps	1	-	1*3	4	-	-	_*6	_*7	_*7	1 GB	External	_*8
C927-4P	-	IP Base*2	150 Mbps	1	-	1*4	4	-	-	_*6	_*7	_*7	1 GB	External	_*8
C927-4PM	-	IP Base*2	150 Mbps	1	-	1*5	4	-	-	_*6	_*7	_*7	1 GB	External	_*8
C931-4P	-	IP Base*2	250 Mbps	2	-	-	4	-	-	_*6	_*7	_*7	1 GB	Internal	_*8

*1 Cisco IOS SEC License are required. *2 Cisco IOS SEC License and Cisco IOS APP License can be added.

*3 VDSL/ADSL2+ (Annex B/J). *4 VDSL/ADSL2+ (Annex A). *5 VDSL/ADSL2+ (Annex M).

*6 Cisco IOS APP License is required. *7 Cisco IOS SEC License is required.

*8 ACS-900-RM-19 is required. Optional Under-the-Desk Mounting Kit (ACS-900-DM) is available.









C921-4P, C931-4P

C926-4P, C927-4P, C927-4PM

Getting Started

What's New

Feature Story

Collaborate

Compute

Security

Connect

Switches

Wireless

Routers

RV

ISK OUC

NEW ISR 900

ISR 110

ISR 4000

Services

Connect - Routers

Cisco ISR 900 Series NEW



Overview Platform Spec	Licenses	Transition Guide
------------------------	----------	------------------

Cisco IOS Technology Package Licenses

Product SKU	Description
SL-900-SEC	Cisco IOS SEC License for Cisco ISR 900
SL-900-APP	Cisco IOS APP License for Cisco ISR 900

Cisco IOS Software Licensing and Packaging

A single Cisco IOS universal image encompassing all functions is delivered with Cisco ISR 900 Series. Advanced features can be enabled simply by activating a software license on the Universal image. The following licenses are available:

APP SEC

IP Base

Available as the default: Routing protocols, Access Control Lists (ACL), Network Address Translation (NAT), Quality of Service (QoS), Bidirectional Forwarding Detection (BFD), Virtual Routing and Forwarding (VRF) Lite, IP SLA Responder

Security (SEC)

Includes features for securing network infrastructure: Zone-based fire-wall, IPsec VPN, Dynamic Multipoint VPN (DMVPN), FlexVPN, Group Encrypted Transport (GET) VPN, Secure Sockets Layer (SSL) VPN

Application Experience (APP)

Includes data and application performance features: Layer 2 Tunneling Protocol (L2TP) v3, Multiprotocol Label Switching (MPLS), Performance Routing (PfR) v3, Next-Generation Network-Based Application Recognition (NBAR2), Application Visibility and Control (AVC), IP SLA Initiator, LISP, Virtual Private LAN Services (VPLS), Ethernet over MPLS

Getting Started

What's New

Feature Story

Collaborate

Compute

Security

Connect

Switches

Wireless

Routers

RV

13K 000

NEW ISR 900

ISR 110

ISR 4000

Services

Connect - Routers

Cisco ISR 900 Series NEW



Overview	Platform Spec	Licenses	Transition Guide
Transition Map			

EoS Model	Existing Model	New Model	Description						
CISCO881-K9 CISCO881-SEC-K9		C921-4P	2 x GE-WAN, 4 x GE-LAN managed switch, 1 GB DRAM and 2 GB Flash, Internal power supply, Cisco IOS IP Base, Max 150 Mbps crypto throughput (Cisco IOS SEC License is require						
CISCO881C-K9 CISCO881GC-K9	C881-K9	C931-4P	2 x GE-WAN, 4 x GE-LAN managed switch, 1 GB DRAM and 2 GB Flash, Internal power supply, Cisco IOS IP Base, Max 250 Mbps crypto throughput (Cisco IOS SEC License is required)						
CISCO886-K9 CISCO886-SEC-K9 CISCO886VA-K9 CISCO886VA-SEC-K9	C886VA-K9 C886VAJ-K9	C926-4P	1 x GE-WAN, 1 x VDSL/ADSL2+ (Annex B/J), 4 x GE-LAN managed switch, 1 GB DRAM and 2 GB Flash, External power supply, Cisco IOS IP Base, Max 150 Mbps crypto throughput (Cisco IOS SEC License is required)						
CISCO887-K9 CISCO887-SEC-K9 CISCO887V-K9 CISCO887V-SEC-K9 CISCO887VA-K9 CISCO887VA-SEC-K9	C887VA-K9	C927-4P	1 x GE-WAN, 1 x VDSL/ADSL2+ (Annex A), 4 x GE-LAN managed switch, 1 GB DRAM and 2 GB Flash, External power supply, Cisco IOS IP Base, Max 150 Mbps crypto throughput (Cisco IOS SEC License is required)						
CISCO887M-K9 CISCO887VA-M-K9	C887VAM-K9	C927-4PM	1 x GE-WAN, 1 x VDSL/ADSL2+ (Annex M), 4 x GE-LAN managed switch, 1 GB DRAM and 2 GB Flash, External power supply, Cisco IOS IP Base, Max 150 Mbps crypto throughput (Cisco IOS SEC License is required)						

Connect - Routers

Cisco ISR 1100 Series

WEB

Getting Started

What's New

Feature Story

Collaborate

Compute

Security

Connect

Switches

Wireless

Routers

ΚV

ISR 8

NEW | ISR 900

ISR 1100

ISR 4000

Services

Overview Platform Spec

Licenses & Accessories

Bundles for SD-WAN

Fixed, High-Performance Routers

The Cisco ISR 1100 Series routers are best suited for small and midsize businesses, enterprise branches, and as customer premises equipment in managed services environments. The routers come with 4 or 8 LAN ports in various model options. There are multiple combinations to choose from, including LAN, WLAN, WAN, DSL, LTE, and pluggable, depending on your branch needs. They can be used in ATMs, retail stores, and kiosks, as well as for various other purposes.



- Cisco IOS XE Universal Image (IP Base/SEC/APP)
- High-performance multicore processors for high-speed WAN connections and multiple services
- Dual WAN ports for load balancing and/or business continuity
- 4G LTE wireless WAN (select models)
- Built-in managed switch (all models)
- Optional integrated power supply for distribution of PoE/PoE+
- Built-in IEEE 802.11ac Wave 2-compatible wireless access point (wireless models)
- Cisco Mobility Express for flexible deployment





Cotting Storted

What's New

Feature Story

Collaborate

Compute

Security

Connect

Switches

Wireless

Routers

RV

ISR 800

NEW ISR 900

ISR 1100

Services

Connect - Routers

Cisco ISR 1100 Series



Overview	Platforn	n Spec	Licen	ses & Acces	sories		Bun	dles fo	r SD-	WAN			-		
Durchast CVIII	C (OCF) CKII	0: 100	Crypto Throughput		W	/AN Poi	rts	LAN Wireless		Security		urity	DDAM	Rack	
Product SKU	Service (CSE) SKU	Cisco IOS	Default	Upgradable*1	GE	GE/ SFP	xDSL	GE	AP	4G LTE	AppX	FW	VPN	DRAM	Mount
C1101-4P	-	IP Base*3	50 Mbps	250 Mbps	1	-	-	4	-	-	_*8	_*9	_*9	4 GB	-
C1101-4PLTEP	-	IP Base ^{⋆₃}	50 Mbps	250 Mbps	1	-	-	4	-	_*7	_*8	_*9	_*9	4 GB	-
C1101-4PLTEPWx*2	-	IP Base*3	50 Mbps	250 Mbps	1	-	-	4	•	_*7	_*8	_*9	_*9	4 GB	-
C1109-4PLTE2P NEW	-	IP Base*3	50 Mbps	200 Mbps	1	-	-	4	-	_*7	_*8	_*9	_*9	4 GB	-
C1111-4P	CON-SMBS-C11114P	IP Base*3	50 Mbps	250 Mbps	1	1	-	4	-	-	_*8	_*9	_*9	4 GB	_*10
C1111-8P	CON-SMBS-C11118P	IP Base*3	50 Mbps	350 Mbps	1	1	-	8	-	-	_*8	_*9	_*9	4 GB	_*10
C1111X-8P	CON-SMBS-C11118P	IP Base*3	50 Mbps	350 Mbps	1	1	-	8	-	-	_*8	_*9	_*9	8 GB	_*10
C1111-4PWx*2	CON-SMBS-C111xW4P*2	IP Base*3	50 Mbps	250 Mbps	1	1	-	4	•	-	_*8	_*9	_*9	4 GB	_*10
C1111-8PWx*2	CON-SMBS-C111xW8P*2	IP Base*3	50 Mbps	350 Mbps	1	1	-	8	•	-	_*8	_*9	_*9	4 GB	_*10
C1111-4PLTELA	CON-SMBS-C1114PAL	IP Base*3	50 Mbps	250 Mbps	1	1	-	4	-	•	_*8	_*9	_*9	4 GB	_*10
C1111-4PLTEEA	-	IP Base*3	50 Mbps	250 Mbps	1	1	-	4	-	•	_*8	_*9	_*9	4 GB	_*10
C1111-8PLTELA	CON-SMBS-C1118PAL	IP Base*3	50 Mbps	350 Mbps	1	1	-	8	-	•	_*8	_*9	_*9	4 GB	_*10
C1111-8PLTELAWx*2	CON-SMBS-C11118PW	IP Base*3	50 Mbps	350 Mbps	1	1	-	8	•	•	_*8	_*9	_*9	4 GB	_*10
C1113-8P NEW	-	IP Base*3	50 Mbps	250 Mbps	-	1	1*4	4	-	-	_*8	_*9	_*9	4 GB	_*10
C1117-4P	CON-SMBS-C11174P1	IP Base*3	50 Mbps	250 Mbps	-	1	1*5	4	-	-	_*8	_*9	_*9	4 GB	_*10
C1117-4PWx*2	CON-SMBS-C111xxxx	IP Base ^{⋆₃}	50 Mbps	250 Mbps	-	1	1*6	4	•	-	_*8	_*9	_*9	4 GB	_*10
C1117-4PLTELA	CON-SMBS-C1114PLE	IP Base*3	50 Mbps	250 Mbps	-	1	1*6	4	-	•	_*8	_*9	_*9	4 GB	_*10
C1117-4PLTELAWx*2	CON-SMBS-C111Wx4P	IP Base*3	50 Mbps	250 Mbps	-	1	1*6	4	•	•	_*8	_*9	_*9	4 GB	_*10

^{*1} Cisco IOS IPsec Performance License and Cisco IOS HSEC License are required. *2 The "x" corresponds to the supported domain.
*3 Cisco IOS SEC License, Cisco IOS APP License, Cisco IOS IPsec Performance License, and Cisco IOS HSEC License can be added.
*4 1 G.FAST (Annex A). *5 VA-DSL (Annex A). *6 ADSL2/VDSL2+ (Annex A). *7 Cisco LTE Advanced Pluggable is required.
*8 Cisco IOS APP License is required. *9 Cisco IOS SEC License is required. *10 ACS-1100-RM-19 is required.

Connect - Routers

Cisco ISR 1100 Series

Overview



Getting Started

What's New

Feature Story

Collaborate

Compute

Security

Connect

Switches

Wireless

Routers

RV/

....

NEW ISR 900

ISR 1100

ISR 4000

Services

Cisco IOS Technology Package Licenses

Product SKU	Description
SL-1100-4P-SEC	Cisco IOS SEC License for Cisco ISR 1100 (4-port Model)
SL-1100-8P-SEC	Cisco IOS SEC License for Cisco ISR 1100 (8-port Model)
SL-1100-4P-APP	Cisco IOS APP License for Cisco ISR 1100 (4-port Model)
SL-1100-8P-APP	Cisco IOS APP License for Cisco ISR 1100 (8-port Model)

Platform Spec

Cisco LTE Advanced Pluggable for Cisco ISR 1101-4PLTEP/4PLTEPWx

Product SKU	Description
P-LTEA-LA	LTE Advanced (3GPP Category 6) Pluggable

Cisco IOS Feature Licenses

Product SKU	Description
FL-VPERF-4P-100	Cisco IOS VPERF License for Cisco ISR 1100 (4-port Model)
FL-VPERF-8P-200	Cisco IOS VPERF License for Cisco ISR 1100 (8-port Model)
FL-1100-4P-HSEC	Cisco IOS HSEC License for Cisco ISR 1100 (4-port Model)
FL-1100-8P-HSEC	Cisco IOS HSEC License for Cisco ISR 1100 (8-port Model)

PoE-capable Power Supply Module for Cisco ISR 111x

Bundles for SD-WAN


Licenses & Accessories

Product SKU	Description
ISR-1100-POE2	2-port PoE-capable (2 PoE or 1 PoE+) 115 W Power Supply Module for Cisco 111x (4-port Model)
ISR-1100-POE4	4-port PoE-capable (4 PoE or 2 PoE+) 150 W Power Supply Module for Cisco 111x (8-port Model)

Cisco IOS Software Licensing and Packaging

A single Cisco IOS XE universal image encompassing all functions is delivered with the platform. Advanced features can be enabled simply by activating a software license on the Universal image. The following licenses are available:

- IP Base: Available as the default.
- Security (SEC): Includes features for securing network infrastructure.
- Application Experience (APP): Includes data and application performance features.
- Performance (VPERF): Provides additional IPsec performance 100
 Mbps for ISR 1100-4P and 200 Mbps for ISR 1100-8P.
- High Performance Security (HSEC): Provides High IPsec maximum performance security.



Getting Started

What's New

Feature Story

Collaborate

Compute

Security

Connect

Switches

Wireless

Routers

RV

NEW ISR 900

ISR 1100

ISR 1000

Services

Connect - Routers

Cisco ISR 1100 Series



Overview	Platform Spec	Licenses & Accessories	Bundles for SD-WAN
----------	---------------	------------------------	---------------------------

Cisco ISR 1100 Series Cisco DNA Bundles

Product SKU	Description	SD-WAN Security								
Product Sko	Description	App Aware FW	IPS	URL Filtering	Umbrella Integration					
C1111-4P-DNA	Cisco 1111-4P with Cisco DNA Support	•	-	-	•					
C1111-8P-DNA	Cisco 1111-8P with Cisco DNA Support	•	-	-	•					
C1111X-8P-DNA-PM	Cisco 1111X-8P with Cisco DNA Support	•	•	•	•					
C1111-4PLTELA-DNA	Cisco 1111-4PLTELA with Cisco DNA Support	•	-	-	•					
C1111-8PLTELA-DNA	Cisco 8PLTELA with Cisco DNA Support	•	-	-	•					

- Cisco DNA Licenses for Cisco ISR 1100 Series
- Cloud Management: Provides simplicity of management with Cisco vManage; recommended for all SD-WAN deployments.
- On-Premises Management: Manages WAN using Cisco DNA Center or Cisco vManage on-premises. Cisco DNA Center requires an additional appliance purchase.

Software Package	Bandwidth	Product SKU (Cloud Mana	agement)	Product SKU (On-Premises Management)				
	Danuwium	3-Years	5-Years	3-Years	5-Years			
	10 Mbps	DNA-C-10M-E-3Y	DNA-C-10M-E-5Y	DNA-P-10M-E-3Y	DNA-P-10M-E-5Y			
Cisco DNA Essentials	20 Mbps	DNA-C-20M-E-3Y	DNA-C-20M-E-5Y	DNA-P-20M-E-3Y	DNA-P-20M-E-5Y			
CISCO DINA ESSENTIAIS	50 Mbps	DNA-C-50M-E-3Y	DNA-C-50M-E-5Y	DNA-P-50M-E-3Y	DNA-P-50M-E-5Y			
	100 Mbps	DNA-C-100M-E-3Y	DNA-C-100M-E-5Y	DNA-P-100M-E-3Y	DNA-P-100M-E-5Y			
	10 Mbps	DNA-C-10M-A-3Y	DNA-C-10M-A-5Y	DNA-P-10M-A-3Y	DNA-P-10M-A-5Y			
Ciaco DNA Advantago	20 Mbps	DNA-C-20M-A-3Y	DNA-C-20M-A-5Y	DNA-P-20M-A-3Y	DNA-P-20M-A-5Y			
Cisco DNA Advantage	50 Mbps	DNA-C-50M-A-3Y	DNA-C-50M-A-5Y	DNA-P-50M-A-3Y	DNA-P-50M-A-5Y			
	100 Mbps	DNA-C-100M-A-3Y	DNA-C-100M-A-5Y	DNA-P-100M-A-3Y	DNA-P-100M-A-5Y			

Connect - Routers

Cisco ISR 4000 Series



Getting Started

What's New

Feature Story

Collaborate

Compute

Security

Connect

Switches

Wireless

Routers

RV

NEW ISR 900

100 446

ISR 4000

Services

Overview

Platform Spec

Licenses & Accessories

Bundles

Transition Guide

Meet All Your Needs with One Device

The Cisco ISR 4000 Series routers consolidate many must-have IT functions, including network, security, compute, storage, and unified communications. So you get everything you need in a single platform.

The platform is modular and upgradable, so you can add new services without changing equipment. It supports multiple application-aware services concurrently while maintaining WAN performance of up to 4 Gbps, even during heavy traffic loads. The backplane architecture supports high-bandwidth, module-to-module communication at speeds up to 10 Gbps.

Highlights

- Cisco IOS Universal Image (IP Base/SEC/UC/APP)
- High-performance multicore processors for high-speed WAN connections and multiple services
- Separates control- and data-plane operations (Cisco 4431/4451: the default control-plane memory is 4 GB, upgradable to 16 GB, and the default data-plane memory is 2 GB)
- Cisco Enhanced Services Module (SM-X) and Cisco Network Interface Module (NIM) integrate networking, services, computing, and storage into a single form factor











Connect - Routers
Cisco ISR 4000 Series

WEB

Getting Started

What's New

Feature Story

Collaborate

Compute

Security

Connect

Switches

Wireless

Routers

RV

NEW ISR 900

ISD 110

ISR 4000

Services

Overview	Platform Spec	Licenses & Accessories	Bundles	Transition Guide

		01 100	Throughput		Ports		Expansion Slots		Default	Power	Rack		
Product SKU Service (CSE) SKU	Service (CSE) SKU	Cisco IOS	Default	Max*1	GE	SFP	GE/ SFP	NIM	SM-X	PVDM	Power Supply	Redundancy	Mount
ISR4221/K9	CON-SMBS-ISR4221K	IP Base*2	35 Mbps	1.2 Gbps	1	-	1	2	-	-	External AC	-	1 RU
ISR4321/K9	CON-SMBS-ISR4321K	IP Base*2	50 Mbps	2 Gbps ~	1	-	1	2	-	1	External AC	-	1 RU
ISR4331/K9	-	IP Base*2	100 Mbps	2 Gbps ~	1	1	1	2	1	1	Internal AC	-	1 RU
ISR4351/K9	-	IP Base*2	200 Mbps	2 Gbps ~	-	-	3	3	2	1	Internal AC	-	2 RU
ISR4431/K9	-	IP Base*2	500 Mbps	4 Gbps ~	-	-	4	3	-	1	Internal AC	•	1 RU
ISR4451-X/K9	-	IP Base*2	1 Gbps	4 Gbps ~	-	-	4	3	2	1	Internal AC	•	2 RU

*1 Cisco IOS Booster Performance License is required.

*2 Cisco IOS SEC License, Cisco IOS UC License, and Cisco IOS APP License can be added.





Connect - Routers Cisco ISR 4000 Series

Overview



Transition Guide

Getting Started

What's New

Feature Story

Collaborate

Compute

Security

Connect

Switches

Wireless

Routers

RV

NEW ISR 900

100 440

ISK I IU

ISR 4000

Services

Cisco IOS Technology Package Licenses

Platform Spec

Cisco ios reciliology	1 ackage Licenses						
Product SKU	Description			Compatib	le Models		
Product Sku	Description	4221	4321	4331	4351	4431	4451
SL-4220-SEC-K9	Cisco IOS SEC License for Cisco ISR 4221	•	-	-	-	-	-
SL-4320-SEC-K9	Cisco IOS SEC License for Cisco ISR 4321	-	•	-	-	-	-
SL-4330-SEC-K9	Cisco IOS SEC License for Cisco ISR 4331	-	-	•	-	-	-
SL-4350-SEC-K9	Cisco IOS SEC License for Cisco ISR 4351	-	-	-	•	-	-
SL-44-SEC-K9	Cisco IOS SEC License for Cisco ISR 4400 Series	-	-	-	-	•	•
SL-4320-UC-K9	Cisco IOS UC License for Cisco ISR 4321	-	•	-	-	-	-
SL-4330-UC-K9	Cisco IOS UC License for Cisco ISR 4331	-	-	•	-	-	-
SL-4350-UC-K9	Cisco IOS UC License for Cisco ISR 4351	-	-	-	•	-	-
SL-44-UC-K9	Cisco IOS UC License for Cisco ISR 4400 Series	-	-	-	-	•	•
SL-4220-APP-K9	Cisco IOS APP License for Cisco ISR 4221	•	•	-	-	-	-
L-SL-4320-APP-K9	Cisco IOS APP License for Cisco ISR 4321	-	•	-	-	-	-
L-SL-4330-APP-K9	Cisco IOS APP License for Cisco ISR 4331	-	-	•	-	-	-
L-SL-4350-APP-K9	Cisco IOS APP License for Cisco ISR 4351	-	-	-	•	-	-
L-SL-44-APP-K9	Cisco IOS APP License for Cisco ISR 4400 Series	-	-	-	-	•	•

Licenses & Accessories

Bundles



Connect - Routers Cisco ISR 4000 Series



Transition Guide

Getting Started

What's Nev

Feature Story

Collaborate

Compute

Security

Connect

Switches

Wireless

Routers

RV

13K 000

NEW ISR 900

ISR 110

ISR 4000

Services

Overview Platform Spec Licenses & Accessories Bundles

Cisco IOS Feature Licenses

D 1 . 0101				Compatib	le Models	i	
Product SKU	Description	4221	4321	4331	4351	4431	4451
FL-4320-HSEC-K9	Cisco IOS HSEC License for Cisco ISR 4321*1	-	•	-	-	-	-
FL-4330-HSEC-K9	Cisco IOS HSEC License for Cisco ISR 4331*1	-	-	•	-	-	-
FL-4350-HSEC-K9	Cisco IOS HSEC License for Cisco ISR 4351*1	-	-	-	•	-	-
FL-44-HSEC-K9	Cisco IOS HSEC License for Cisco ISR 4400 Series*1	-	-	-	-	•	•
SW-CCME-UL-ESS	Cisco Unified CME Phone License - Essential	-	•	•	•	•	•
SW-CCME-UL-BASIC	Cisco Unified CME Phone License - Basic	-	•	•	•	•	•
SW-CCME-UL-ENH	Cisco Unified CME Phone License - Enhanced	-	•	•	•	•	•
L-FL-CME-SRST-5	Cisco Unified CME or SRST 5 License*2	-	•	•	•	•	•
L-FL-CME-SRST-25	Cisco Unified CME or SRST 25 License*2	-	•	•	•	•	•
L-FL-CME-SRST-100	Cisco Unified CME or SRST 100 License*2	-	-	•	•	•	•
FL-CUBEE-5-RED	Cisco Unified BEe 5 Redundant Configuration License*2	-	•	•	•	•	•
FL-CUBEE-25-RED	Cisco Unified BEe 25 Redundant Configuration License*2	-	•	•	•	•	•
FL-CUBEE-100-RED	Cisco Unified BEe 100 Redundant Configuration License*2	-	•	•	•	•	•
SL-200-AKC	Cisco IWAN with Akamai Connect 200 Connections License*3	•	•	•	-	-	-
SL-750-AKC	Cisco IWAN with Akamai Connect 200 Connections License*3	-	-	•	•	•	-
SL-1300-AKC	Cisco IWAN with Akamai Connect 1,300 Connections License*3	-	-	•	•	•	•
SL-2500-AKC	Cisco IWAN with Akamai Connect 2,500 Connections License*3	-	-	•	•	-	•
SL-6K-AKC	Cisco IWAN with Akamai Connect 6,000 Connections License*3	-	-	•	•	-	•
FL-4220-PERF-K9	Cisco IOS Performance-on-Demand License for Cisco ISR 4221	•	-	-	-	-	-
FL-4320-PERF-K9	Cisco IOS Performance-on-Demand License for Cisco ISR 4321	-	•	-	-	-	-
FL-4330-PERF-K9	Cisco IOS Performance-on-Demand License for Cisco ISR 4331	-	-	•	-	-	-
FL-4350-PERF-K9	Cisco IOS Performance-on-Demand License for Cisco ISR 4351	-	-	-	•	-	-
FL-44-PERF-K9	Cisco IOS Performance-on-Demand License for Cisco ISR 4400 Series	-	-	-	-	•	•
FL-4220-BOOST-K9	Cisco IOS Booster Performance License for Cisco ISR 4221	•	-	-	-	-	-
FL-4320-BOOST-K9	Cisco IOS Booster Performance License for Cisco ISR 4321	-	•	-	-	-	-
FL-4330-BOOST-K9	Cisco IOS Booster Performance License for Cisco ISR 4331	-	-	•	-	-	-
FL-4350-BOOST-K9	Cisco IOS Booster Performance License for Cisco ISR 4351	-	-	-	•	-	-
FL-4430-BOOST-K9	Cisco IOS Booster Performance License for Cisco ISR 4431	-	-	-	-	•	-
FL-44-BOOST-K9	Cisco IOS Booster Performance License for Cisco ISR 4451	-	-	-	-	-	•

^{*1} Cisco IOS SEC License is required. *2 Cisco IOS UC License is required. *3 Cisco IOS APP License is required.



Connect - Routers

Cisco ISR 4000 Series

WEB

Getting Started

What's Nev

Feature Story

Collaborate

Compute

Security

Connect

Switches

Wireless

Routers

ΚV

NEW ISR 900

1011 300

12K 110

ISR 4000

Services

Cisco Layer 2/3 EtherSwitch Modules

Overview Platform Spec Licenses & Accessories Bundles Transition Guide

Product SKU	Description	Slot	Compatible Models							
Product Sku	Description	SIOU	4221	4321	4331	4351	4431	4451		
NIM-ES2-4	EtherSwitch Module (L2, 4-port GE)	NIM	•	•	•	•	•	•		
NIM-ES2-8	EtherSwitch Module (L2, 8-port GE)	NIM	•	•	•	•	•	•		
NIM-ES2-8-P	EtherSwitch Module (L2, 8-port GE/PoE+)	NIM	-	•	•	•	•	•		
SM-X-ES3-16-P	EtherSwitch Service Module (L2/L3, 16-port GE/PoE+)	SM-X	-	-	•	•	-	•		
SM-X-ES3-24-P	EtherSwitch Service Module (L2/L3, 24-port GE/PoE+)	SM-X	-	-	•	•	-	•		
SM-X-ES3D-48-P	EtherSwitch Service Module (L2/L3, 48-port GE/PoE+)	SM-X	-	-	-	•	-	•		

Cisco Gigabit Ethernet WAN Modules

Product SKU	Description	Slot			Compatib			
Product Sku	Description	3101	4221	4321	4331	4351	4431	4451
NIM-1GE-CU-SFP	GE/SFP Module (1-port)	NIM	•	•	•	•	•	•
NIM-2GE-CU-SFP	GE/SFP Module (2-port)	NIM	-	•	•	•	•	•
SM-X-6X1G	GE/SFP Service Module (6-port)	SM-X	-	-	•	•	-	•
SM-X-4X1G-1X10G	GE/SFP (4-port) or SFP+ (1-port) Service Module	SM-X	-	-	•	•	-	•

Cisco Serial WAN Interface Modules

Draduat SVII	Description	Slot						
Product SKU	Description	Siot	4221	4321	4331	4351	4431	4451
NIM-1T	Serial WAN Module (1-port)	NIM	•	•	•	•	•	•
NIM-2T	Serial WAN Module (2-port)	NIM	•	•	•	•	•	•
NIM-4T	Serial WAN Module (4-port)	NIM	-	•	•	•	•	•
SM-X-1T3/E3	T3/E3 Service Module (1 port)	SM-X	-	-	•	•	-	•

Cisco Async WAN Interface Modules

Product SKU	Description	Slot	Slot			Compatib	le Models		
Product Sku	Description	SIUL	4221	4321	4331	4351	4431	4451	
NIM-16A	Asynchronous Module (16-port)	NIM	•	•	•	•	•	•	
NIM-24A	Asynchronous Module (24-port)	NIM	•	•	•	•	•	•	



Connect - Routers

Cisco ISR 4000 Series

Overview



Getting Started

What's New

Feature Story

Collaborate

Compute

Security

Connect

Switches

Wireless

Routers

ΚV

13K 000

NEW ISR 900

ISR 110

ISR 4000

Services

Platform Spec

Licenses & Accessories

Bundles

Transition Guide

Cisco Multimode VDSL2 and ADSL2/2+ Network Interface Modules

Product SKU	Description	Slot Compatible Models								
Product Sku	Description	3101	4221	4321	4331	4351	4431	4451		
NIM-VAB-A	Multi Mode VDSL2/ADSL/2/2+ (Annex A)	NIM	•	•	•	•	•	•		
NIM-VA-B	Multi Mode VDSL2/ADSL/2/2+ (Annex B)	NIM	•	•	•	•	•	•		
NIM-VAB-M	Multi Mode VDSL2/ADSL/2/2+ (Annex M)	NIM	•	•	•	•	•	•		

Cisco 4G LTE Network Interface Modules

Dundrick CKII	Description	Slot		:				
Product SKU	Description	Slot	4221	4321	4331	4351	4431	4451
NIM-4G-LTE-GA	4G LTE Module for Global	NIM	•	•	•	•	•	•
NIM-4G-LTE-NA	4G LTE Module for North America	NIM	•	•	•	•	•	•
NIM-4G-LTE-ST	4G LTE Module for Sprint	NIM	•	•	•	•	•	•
NIM-4G-LTE-VZ	4G LTE Module for Verizon	NIM	•	•	•	•	•	•
NIM-4G-LTE-LA	4G LTE Module for Asia Pacific, Australia and Latam	NIM	•	•	•	•	•	•
NIM-LTEA-EA	LTE Advanced Module for Europe and North America	NIM	•	•	•	•	•	•
NIM-LTEA-LA	LTE Advanced Module for Asia Pacific, Australia and Latam	NIM	•	•	•	•	•	•

Cisco T1/E1 Voice and WAN Network Interface Modules

Product SKU	Description	Slot			Compatible Models				
Product Sko	Description	3101	4221	4321	4331	4351	4431	4451	
NIM-1MFT-T1/E1	Voice/WAN Module (1-port T1/E1)	NIM	•	•	•	•	•	•	
NIM-2MFT-T1/E1	Voice/WAN Module (2-port T1/E1)	NIM	•	•	•	•	•	•	
NIM-4MFT-T1/E1	Voice/WAN Module (4-port T1/E1)	NIM	-	•	•	•	•	•	
NIM-8MFT-T1/E1	Voice/WAN Module (8-port T1/E1)	NIM	-	•	•	•	•	•	
NIM-1CE1T1-PRI	Voice/WAN Module (1-port T1/E1/G.703)	NIM	-	•	•	•	•	•	
NIM-2CE1T1-PRI	Voice/WAN Module (2-port T1/E1/G.703)	NIM	-	•	•	•	•	•	
NIM-8CE1T1-PRI	Voice/WAN Module (8-port T1/E1/G.703)	NIM	-	•	•	•	•	•	
SM-X-1T3/E3	T3/E3 Service Module (1 port)	SM-X	-	-	•	•	-	•	

Connect - Routers

Cisco ISR 4000 Series

Overview



Transition Guide

Getting Started

What's Nev

Feature Story

Collaborate

Compute

Security

Connect

Switches

Wireless

Routers

ΚV

NEW ISR 900

100 440

ISR 4000

Services

Cisco Analog Voice N	etwork Interface Modules	
		 Compatible Models

Product SKU	Description	Slot	Compatible Models								
Product Sku	Description	Siot	4221	4321	4331	4351	4431	4451			
NIM-2FXSP	Voice Module (2-port FXS)	NIM	-	•	•	•	•	•			
NIM-4FXSP	Voice Module (4-port FXS)	NIM	-	•	•	•	•	•			
NIM-2FXO	Voice Module (2-port FXO)	NIM	-	•	•	•	•	•			
NIM-4FXO	Voice Module (4-port FXO)	NIM	-	•	•	•	•	•			
NIM-2FXS/4FXOP	Voice Module (2-port FXS and 4-port FXO)	NIM	-	•	•	•	•	•			
NIM-4E/M	Voice Module (4-port E/M)	NIM	-	•	•	•	•	•			
NIM-2BRI-NT/TE	Voice Module (2-port BRI)	NIM	-	•	•	•	•	•			
NIM-4BRI-NT/TE	Voice Module (4-port BRI)	NIM	-	•	•	•	•	•			

Licenses & Accessories

Bundles

Cisco Packet Voice Digital Signal Processor Modules (PVDMs)

Platform Spec

Product SKU	Description	Slot	Compatible Models								
Product Sku	Description	3101	4221	4321	4331	4351	4431	4451			
PVDM4-32	High-density Voice DSP Module (16-channel)	PVDM4	-	•	•	•	•	•			
PVDM4-64	High-density Voice DSP Module (32-channel)	PVDM4	-	•	•	•	•	•			
PVDM4-128	High-density Voice DSP Module (64-channel)	PVDM4	-	•	•	•	•	•			
PVDM4-256	High-density Voice DSP Module (128-channel)	PVDM4	-	•	•	•	•	•			
SM-X-PVDM-500	High-density Voice DSP Service Module (768-channel)	SM-X	-	-	•	•	-	•			
SM-X-PVDM-1000	High-density Voice DSP Service Module (1,024-channel)	SM-X	-	-	•	•	-	•			
SM-X-PVDM-2000	High-density Voice DSP Service Module (2,048-channel)	SM-X	-	-	-	●*1	-	•			
SM-X-PVDM-3000	High-density Voice DSP Service Module (3,080-channel)	SM-X	-	-	-	●*1	-	•			

^{*1} Supports up to 1,024 channels.

Cisco UCS E Series Servers

December CVII	CPU	CPU Memory		Internal RAID	Cl-4	Compatible Models						
Product SKU	Cores	Default	Maximum	Drive Slots	RAID	Slot	4221	4321	4331	4351	4431	4451
UCS-EN140N-M2/K9	4	8 GB	8 GB	1	-	NIM	-	•	•	•	•	•
UCS-EN120S-M2/K9	2	4 GB	16 GB	2	0/1	SM-X	-	-	•	•	-	•
UCS-E140S-M2/K9	4	8 GB	16 GB	2	0/1	SM-X	-	-	•	•	-	•
UCS-E160S-M3/K9	6	8 GB	32 GB	2	0/1	SM-X	-	-	•	•	-	•
UCS-E160D-M2/K9	6	8 GB	96 GB	3	0/1/5	SM-X	-	-	-	•	-	•
UCS-E180D-M2/K9	8	8 GB	96 GB	3	0/1/5	SM-X	-	-	-	•	-	•
UCS-E180D-M3/K9	8	16 GB	128 GB	3	0/1/5/10	SM-X	-	-	-	•	-	•
UCS-E1120D-M3/K9	12	16 GB	128 GB	4	0/1/5/10	SM-X	-	-	-	•	_	•



Connect - Routers Cisco ISR 4000 Series

Overview



Transition Guide

Getting Started

What's New

Feature Story

Collaborate

Compute

Security

Connect

Switches

Wireless

Routers

RV

NEW ISR 900

ICD 110

ISR 4000

Services

Cisco ISR 4000 Series Bundles						
Platform	Product SKU	Service (CSE) SKU				
Cisco ISR 4221	ISR4221-SEC/K9	CON-SMBS-ISR4221S				
CISCO ISR 4221	ISR4221-AX/K9	-				
	ISR4321-SEC/K9	-				
	ISR4321-V/K9	-				
Cisco ISR 4321	ISR4321-VSEC/K9	-				
	ISR4321-AX/K9	-				
	ISR4321-AXV/K9	-				
	ISR4331-SEC/K9	-				
	ISR4331-V/K9	-				
Cisco ISR 4331	ISR4331-VSEC/K9	-				
	ISR4331-AX/K9	-				
	ISR4331-AXV/K9	-				
	ISR4351-SEC/K9	-				
	ISR4351-V/K9	-				
Cisco ISR 4351	ISR4351-VSEC/K9	-				
	ISR4351-AX/K9	-				
	ISR4351-AXV/K9	_				

Platform Spec

Platform	Product SKU	Service (CSE) SKU
	ISR4431-SEC/K9	-
	ISR4431-V/K9	-
Cisco ISR 4431	ISR4431-VSEC/K9	-
	ISR4431-AX/K9	-
	ISR4431-AXV/K9	-
	ISR4451-X-SEC/K9	-
	ISR4451-X-V/K9	-
Cisco ISR 4451	ISR4451-X-VSEC/K9	-
	ISR4451-X-AX/K9	-
	ISR4451-X-AXV/K9	-

Bundles

Cisco ISR 4000 Series Bundles Comparison

Dundles	Characters Included in CKII	Bundled Licenses/Modules					
Bundles	Characters Included in SKU	IOS SEC	IOS UC	IOS APP	PVDM4		
Security Bundles	SEC	•	-	-	-		
Voice Bundles	V	-	•	-	•		
Voice Security Bundles	VSEC	•	•	-	•		
Application Experience Bundles	AX	•	-	•	-		
Application Experience Voice Bundles	AXV	•	•	•	•		

Licenses & Accessories

Connect - Routers Cisco ISR 4000 Series

Overview



Transition Guide

Bundles

Getting Started

What's Nev

Feature Story

Collaborate

Compute

Security

Connect

Switches

Wireless

Routers


RV

NEW ISR 900

ICD 110

ISR 4000

Services



Licenses & Accessories

- Cisco DNA Licenses for Cisco ISR 4000 Series
- Cloud Management: Provides simplicity of management with Cisco vManage; recommended for all SD-WAN deployments.
- On-Premises Management: Manages WAN using Cisco DNA Center or Cisco vManage on-premises. Cisco DNA Center requires an additional appliance purchase.

Platform Spec

Coffeen Dooleans	Bandwidth	Product SKU (Cloud Mana	agement)	Product SKU (On-Premises Management)		
Software Package	Danuwium	3-Years	5-Years	3-Years	5-Years	
	10 Mbps	DNA-C-10M-E-3Y	DNA-C-10M-E-5Y	DNA-P-10M-E-3Y	DNA-P-10M-E-5Y	
Cisco DNA Essentials	20 Mbps	DNA-C-20M-E-3Y	DNA-C-20M-E-5Y	DNA-P-20M-E-3Y	DNA-P-20M-E-5Y	
	50 Mbps	DNA-C-50M-E-3Y	DNA-C-50M-E-5Y	DNA-P-50M-E-3Y	DNA-P-50M-E-5Y	
	100 Mbps	DNA-C-100M-E-3Y	DNA-C-100M-E-5Y	DNA-P-100M-E-3Y	DNA-P-100M-E-5Y	
	500 Mbps	DNA-C-500M-E-3Y	DNA-C-500M-E-5Y	DNA-P-500M-E-3Y	DNA-P-500M-E-5Y	
	1 Gbps	DNA-C-1G-E-3Y	DNA-C-1G-E-5Y	DNA-P-1G-E-3Y	DNA-P-1G-E-5Y	
	10 Mbps	DNA-C-10M-A-3Y	DNA-C-10M-A-5Y	DNA-P-10M-A-3Y	DNA-P-10M-A-5Y	
	20 Mbps	DNA-C-20M-A-3Y	DNA-C-20M-A-5Y	DNA-P-20M-A-3Y	DNA-P-20M-A-5Y	
Ciasa DNA Advantaga	50 Mbps	DNA-C-50M-A-3Y	DNA-C-50M-A-5Y	DNA-P-50M-A-3Y	DNA-P-50M-A-5Y	
Cisco DNA Advantage	100 Mbps	DNA-C-100M-A-3Y	DNA-C-100M-A-5Y	DNA-P-100M-A-3Y	DNA-P-100M-A-5Y	
	500 Mbps	DNA-C-500M-A-3Y	DNA-C-500M-A-5Y	DNA-P-500M-A-3Y	DNA-P-500M-A-5Y	
	1 Gbps	DNA-C-1G-A-3Y	DNA-C-1G-A-5Y	DNA-P-1G-A-3Y	DNA-P-1G-A-5Y	

Getting Started

What's New

Feature Story

Collaborate

Compute

Security

Connect

Switches

Wireless

Routers

₹Υ

NEW ISR 900

105 440

ISR 4000

Services

Connect - Routers





Overview Platform Spec Licenses & Accessories Bundles Transition Guide

Benefits of Upgrading to Cisco ISR 4000 Series

Features		ISR 1800/2800/3800	ISR 1900/2900/3900	ISR 4000	Benefits
	Maximum throughput	Up to 50 Mbps	Up to 350 Mbps	Up to 4 Gbps	4 to 10 times greater performance than ISR G2 at lower price
	Cisco Application Visibility and Control (AVC)	-	•	•	Visibility into 1000+ applications for capacity planning and prioritization
Insights and Experiences	Intelligent path selection (Cisco Performance Routing [PfR] v3)	-	•	•	Real-time analytics to help ensure application experience and lower costs with path selection
<u> </u>	WAN optimization (Cisco Wide Area Application Services [WAAS] and Akamai)	-	•	•	Improved application performance and WAN offload with Layer 4 through 7 optimization and intelligent caching
	Pay-as-you-grow performance and services	-	-	•	Ability to buy what you need today and upgrade anytime without a complete equipment upgrade
	Cisco ONE Software Suites	-	•	•	Predictable OpEx, license portability, and investment protection
Automation and Assurance	Cisco Intelligent WAN app with Application Policy Infrastructure Controller Enterprise Module (APIC-EM)	-	•	•	Automated provisioning for faster SD-WAN deployments
Security and Compliance	Cisco Firepower Threat Defense for ISR	-	•	•	Industry-leading advanced threat defense
	Cisco Umbrella Branch (OpenDNS)	=	=	•	Protection from malware, botnets, phishing, and targeted online attacks using real-time threat intelligence
	Cisco Stealthwatch Learning Network License	-	•	•	Branch network visibility and device-level incident response with packet capture and machine learning (ISR 2900/3900 Series requires UCS E-Series blade)
	Multicore hardware VPN acceleration	-	-	•	High-performance encryption for secure WAN
Virtualization	Enterprise Network Functions Virtualization	-	-	•	Simplified operations and deployment of virtual network services on any platform
	Native Application Hosting	-	-	•	No need for additional network devices in the branch
	Integrated compute with Cisco UCS E-Series servers	-	•	•	Local compute resources for applications, data backup, and analytics
	Cisco IOS XE operating system			•	Multi-core processing increases network services performance and availability