




Let's Talk R400 Camera Specs

Ideal for entryways and parking lots



8MP image sensor
3840 x 2160 resolution



4K, Ultra-HD video



102° - 44° Diagonal FoV
94° - 39° Horizontal FoV
62° - 22° Vertical FoV



3.6mm - 11mm motorized
varifocal lens



Up to 60 days of
on-camera storage



IP66 weather resistance
IK10 impact resistance



Optional unlimited cloud
archiving available



Camera starts
at \$1299



Rhombus 10-year
Warranty included

About the R400

Constructed with a fully weatherproof and vandal-resistant exterior shell, the R400 is a powerful enterprise security camera, delivering sharp 4K video and amazing performance. With a varifocal lens and 3X motorized zoom with autofocus, users can manually adjust camera settings for optimal video from far or close distances.

Paired with the Enterprise Console License, the R400 camera provides proactive security powered by Artificial Intelligence and Computer Vision.

Camera Specs

Night Vision: Infrared illuminators (130ft in low light)

Aperture: F/1.5

Pan / Tilt / Zoom: 3X optical zoom + up to 3X digital PTZ

Ethernet: 10 / 100Mbps, MDI/MDI-X Auto Sensing

Power-over-Ethernet: Standard 802.3af for one-cable installation

Power Consumption: Max 11.7 watts

Onboard Storage Included: 512GB, 1TB

Dimensions: 134mm (5.27in) x 118mm (4.64in)

Operating Temperature: -55° to 55° C (-67° to 131° F)

Operating Humidity: <90% RH

In the Box: Torx key, mounting screws, anchors

Baseline Steady State: 10 - 30 Kbps per camera

HD WAN Live Streaming: 530 - 720 Kbps per camera

CE, FCC, NDAA, TAA Compliant