



SPECIFICATION

Model Name	MAG B460 TORPEDO
CPU Support	Supports 10 th Gen Intel® Core™ and Pentium® Gold / Celeron® processors
CPU Socket	LGA 1200 Socket
Chipset	Intel® B460 Chipset
Graphics Interface	2x PCI-E 3.0 x16 slots Support 2-way AMD® CrossFire™ Technology
Display Interface	DisplayPort, HDMI - Requires Processor Graphics
Memory Support	4 DIMMs, Dual Channel DDR4-2933MHz (Max.)
Expansion Slots	2x PCI-E 3.0 x1 slots
Storage	2x M.2 slots, 6x SATA 6Gb/s
SATA RAID	RAID 0, 1, 5, 10 – Available on ports SATA1 to SATA6
USB ports	7x USB 3.2 Gen 1 5Gbps (1 Type-C+ 6 Type-A) 6x USB 2.0
LAN	Realtek®8125B 2.5G LAN
Audio	8-Channel (7.1) HD Audio with Audio Boost

FEATURE



Extended Heatsink Design

MSI extended PWM heatsink and enhanced circuit design ensures even high-end processors to run in full speed.




M.2 Shield FROZR

M.2 thermal accessory. Keeps M.2 SSDs safe while preventing throttling, making them run faster.



Twin Turbo M.2

With 2 x M.2 slots. Running at PCI-E Gen3 x4 maximizes performance for NVMe based SSDs.



2.5G LAN

Onboard 2.5G LAN with LAN manager, delivering the best online gaming experience.



Front Type-C USB 3.2 Gen 1 5Gbps

Compatible with the latest PC chassis and perfect for external drives and other mobile devices.



Core Boost

With premium layout and fully digital power design to support more cores and provide better performance.



DDR4 Boost


Advanced technology to deliver pure data signals for the best gaming performance and stability.



Audio Boost

Reward your ears with studio grade sound quality for the most immersive audio experience.

CONNECTIONS



- Keyboard / Mouse
- DisplayPort
- 2.5G LAN Port
- HD Audio Connectors
- USB 2.0
- HDMI
- USB 3.2 Gen 1 5Gbps Type-A
- USB 3.2 Gen 1 5Gbps Type-A
- Optical S/PDIF OUT