eDatasheet

HP Neverstop Laser MFP 1202nw (5HG93A)

High-volume, low-cost laser printing with easy mobility, exceptional quality, and MFP versatility[4]

Exceptional value right out of the box – up to 60% savings on toner[1] with 5000 pages of toner included.[2] Print, scan, and copy, and restore toner in seconds with a mess-free experience.[3] Print and scan virtually anywhere with HP Smart app.[4]



Up to 60% savings on toner every time you reload[1]
Count on toner savings right out of the box.[1] Get up to 60% savings on toner every time you reload.[1]

Mess-free reloadable toner in seconds[3]
Get a mess-free experience,[3] and easily restore toner levels with the toner reload kit.[6]

Save time printing from virtually anywhere[4]
Print, scan, and copy virtually anywhere, and receive notifications on your phone, with HP Smart app.[4]



Featuring

Up to 60% savings on toner[1] [1]

Thousands of pages right out of the box [2]

Freedom to work anywhere [4]

Simple, mess-free reload[3] [3,6]

Extend your printing reach

No network, no problem [7]

Specifications

Print Resolution Technologies	HP FastRes 1200 (600 x 600 x 2 dpi)
Print quality black (best)	Up to 600 x 600 x 2 dpi
Print speed black (ISO, A4)	Up to 20 ppm
Print speed black (ISO, letter)	Up to 21 ppm
Print speed	Print speed up to 21 ppm (black)
Functions	Print, copy, scan
Duplex printing	Manual (driver support provided)
Duty cycle (monthly, A4)	Up to 20,000 pages
Duty cycle (monthly, letter)	Up to 20,000 pages
Printer smart software features	Apple AirPrint™, Mopria-certified, HP Auto-On/Auto-Off, Wi-Fi Direct, HP Smart App, HP Smart Task
Copier smart software features	ID Copy
Scanner advanced features	No
Energy savings feature technology	HP Auto-On/Auto-Off Technology
Replacement cartridges	HP 143A Black Original Neverstop Laser Toner Reload Kit (Yield ~2500 pages); HP 143AD Dual pack Black Original Neverstop Laser Toner Reload Kit (Yield ~2x2500 pages); HP 144A Black Original Laser Imaging Drum (includes ~5000 pages of inbox toner, useful life of ~20000 pages) Declared black toner page yield value in accordance with ISO/IEC 19752 and continuous printing. Actual yields vary considerably based on images printed and other factors. For details see http://www.hp.com/go/learnaboutsupplies[3]
Supplies feature	HP Neverstop Laser Technology
Connectivity, standard	Hi-Speed USB 2.0 port; Built-in WiFi 802.11b/n/g; Fast Ethernet 10/100 Base
Network capabilities	Fast Ethernet 10/100 Base
Wireless capability	Yes
Mobile printing capability	Apple AirPrint™; Google Cloud Print™; HP Smart App; Mopria™ Certified; Wi-Fi® Direct Printing
Network protocols, supported	TCP/IP: IPv4; IPv6; IP Direct Mode; LPD; SLP; Bonjour; WS-Discovery; BOOTP/DHCP/AutoIP; SNMP v 1/2/3; HTTP/HTTPS
Software included	For Windows OS: HP Software Installer, HP Software Uninstaller (exclude Win8+), HP PCLmS Printer Driver, HP Device Experience (DXP), HP Web Services Assist (HP Connected), Device Setup & Software, Online user manuals, HP Printer Assistant, HP Scan Driver, HP Scan Application, HP Product Improvement Study. For Mac OS: Welcome Screen, (Directs users to HP.com or OS App Source for LaserJet Software)
Compatible Operating Systems	Windows® 10, 8.1, 8, 7: 32-bit or 64-bit, 2 GB available hard disk space, CD-ROM/DVD drive or Internet connection, USB port, Internet Explorer. Apple®OS X El Capitan (v10.11) macOS Sierra (v10.12) macOS High Sierra, (v10.13); 1.5 GB HD; Internet required; USB Linux (For more information, see https://developers.hp.com/hp-linux-imaging-and-printing) *(Not supporting Windows® XP (64-bit) and Windows Vista® (64-bit). Not all "Compatible Operating Systems" are supported with INBOX software; Full solution software available only for Windows 7 and newer; For Windows Server 2008 R2 64-bit, 2012 64-bit, 2012 R2 64-bit, 2016 64-bit only print driver is installed. Windows RT OS for Tablets (32 & 64-bit) uses a simplified HP print driver built into the RT OS; Linux systems use in-OS HPLIP software.)*
Sustainable impact specifications	Mercury-free
Energy star certified	Yes
Energy efficiency	ENERGY STAR® qualified
Blue Angel compliant	Yes, Blue Angel DE-UZ 205—only ensured when using Original HP supplies
Copy speed (black, normal quality, A4)	Up to 20 cpm
Copy speed black (normal, letter)	Up to 20 cpm
Scan file format	JPG, RAW (BMP), PNG, TIFF, PDF
Scan technology	D-CIS
Scanner type	Flatbed
Display area (imperial)	1.26 x 1.26 in
Display area (metric)	32 x 32 mm
Display	ICON LCD
Minimum dimensions (W x D x H)	380.5 x 293.4 x 287 mm *(Dimensions vary as per configuration)*

Minimum dimensions (W x D x H)	14.98 x 11.55 x 11.3 in *(Dimensions vary as per configuration)*
Weight	8.78 kg
Weight	19.36 lb
Power consumption	338 watts (Active Printing), 3.3 watts (Ready), 0.95 watts (Sleep), 0.1 watts (Manual off)[2]
Power supply type	Internal (Built-in) power supply
What's in the box	HP Neverstop laser1202nw Printer; Preinstalled HP Black Original Imaging Drum (~5000 pages yield, ~20000 pages useful life); Reference guide; Setup guide; Regulatory flyer; Support flyer; Warranty guide; Power cord; USB cable[1]
Services (Care Pack)	UC4X6E - HP 1y Onsite Exchange NS L 1xxx MFP SVC; UB4X8E - HP 2y Onsite Exchange NS L 1xxx MFP SVC; UB4X9E - HP 3y Onsite Exchange NS L 1xxx MFP SVC; UB4Y0E - HP 4y Onsite Exchange NS L 1xxx MFP SVC; UC4X7E - HP 5y Onsite Exchange NS L 1xxx MFP SVC; UB4Y1E - HP 2y NBD Exchange NS L 1xxx MFP SVC; UB4Y2E - HP 3y NBD Exchange NS L 1xxx MFP SVC; UB4Y3E - HP 4y NBD Exchange NS L 1xxx MFP SVC; UB4Y4E - HP 2y Std Exchange NS L 1xxx MFP SVC; UB4Y5E - HP 3y Std Exchange NS L 1xxx MFP SVC; UB4Y6E - HP 4y Std Exchange NS L 1xxx MFP SVC; UB4Y7E - HP 2y Return to Depot NS L 1xxx MFP SVC; UB4Y8E - HP 3y Return to Depot NS L 1xxx MFP SVC; UB4Y9E - HP 4y Return to Depot NS L 1xxx MFP SVC
Warranty	HP one year hardware limited warranty. For full terms and conditions, visit: http://www.hp.com/go/orderdocuments.

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

[1] Based on internal HP comparison of MSRP and cost-per-page of in-class HP LaserJet Pro M16/17 and HP LaserJet Pro MFP M29/M30 with standard-fill HP 47A Black Original LaserJet Toner Cartridge, as of March 2019. For details see http://www.hp.com/go/learnaboutsupplies

[2] Actual yield varies considerably based on content of printed pages and other factors. Average based on ISO/IEC 19752 and continuous printing. For details see http://www.hp.com/go/learnaboutsupplies

[3] HP internal research and Keypoint Intelligence-Buyers Lab 2018 study commissioned by HP. For details see http://www.keypointintelligence.com/HPNeverstop

[4] Requires the HP Smart app download. For details on local printing requirements see http://www.hp.com/go/mobileprinting. Certain features/software are available in English language only.

[6] Toner reload kit is not included with the printer; please purchase separately.

[7] Mobile device needs to be connected to Wi-Fi Direct® signal of a Wi-Fi Direct-supported AiO or printer prior to printing. Details at http://www.hp.com/go/mobileprinting. Wi-Fi Direct® is a registered trademark of Wi-Fi Alliance®.

Technical Specifications Footnotes

[1] HP Black Original Laser Imaging Drum (introductory ~5,000 page black toner yield provided, with ~20,000 page Imaging Drum useful life). Actual yields vary considerably based on images printed and other factors. For details see http://www.hp.com/go/learnaboutsupplies

[2] Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. Power consumption values typically based on measurement of 115 V device.

[3] Declared black toner page yield value in accordance with ISO/IEC 19752 and continuous printing. Actual yields vary considerably based on images printed and other factors. For details see http://www.hp.com/go/learnaboutsupplies. HP W1103A and HP W1104A replacement supplies are not imported, sold, nor warrantied in China.

Learn more at
http://www.hp.com/uk

© Copyright 2020 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.