



B615 ESSENTIAL SURGE PROTECTOR

Protect home and office computers, electronics, and home theater equipment

The Essential Surge Protector B615 from CyberPower offers vital surge protection for common home and office devices such as computers and electronics. It prevents spikes in energy caused by storms and electrical power surges from reaching your electronic equipment. The B615 provides 1,500 joules of protection with 6 outlets and a long, 15-foot power cord.

Features of the B615 include automatic shutdown, metal oxide varistor (MOV) technology, 15-foot power cord, keyhole mounting slots, and impact-resistant casing. This surge suppressor comes with a Limited Lifetime Warranty and a Connected Equipment Guarantee.

TYPICAL APPLICATIONS

- Personal Computers
- Chargers
- Personal Electronics

FEATURES

- Surge suppression: 1,500 J
- Volts: 125 V
- Circuit breaker: 15 A
- Plug type: NEMA 5-15P
- Plug style: Right-angle 45° offset
- Outlet type: 6 NEMA 5-15R (surge-protected)
- Power cord: 15 ft
- Model color: White
- EMI/RFI Filtration: Yes
- Warranty: Limited Lifetime
- Connected Equipment Guarantee: \$150,000



SPECIFICATIONS

| CHARGER CHARACTERISITCS | | SURGE PROTECTION & FILTERING | |
|-------------------------|-------------------------------------|------------------------------|---------------------------|
| Charger auto-restart | Yes, when utility power is restored | Attenuation | 32 dB |
| INPUT | | Clamping Voltage | 600V (H-N, H-G, N-G) |
| Circuit Breaker | 15 A | EMI/RFI Filtration | 150 KHz 100 MHz Yes |
| Cord Length | 15 ft (4.6 m) | Maximum Surge Current | 45,000 A |
| Input Plug Type | NEMA 5-15P | Maximum Surge Current H-G | 15,000 A |
| Maximum Input Current | 15 A | Maximum Surge Current H-N | 15,000 A |
| Plug Style | Right Angle - 45° Offset | Maximum Surge Current N-G | 15,000 A |
| OUTPUT | | Maximum Surge Voltage | 6,000 V |
| Outlet Type | 6 NEMA 5-15R | Response Time | <1 Nanosecond |
| Outlets - Total | 6 | Surge Suppression (Joules) | 1,500 J |

B615

ESSENTIAL SURGE PROTECTOR

SPECIFICATIONS CONT.

| PHYSICAL | |
|--------------------------|--|
| Color | White |
| Form Factors Supported | Keyhole (Wall Mount or Under-counter Installation) |
| Material of Construction | Plastic |

| DIMENSIONS | |
|--|------------------------|
| Physical Dimensions - Width/Height/Depth (cm) | 4.45 x 3.81 x 24.77 cm |
| Physical Dimensions - Width/Height/Depth (mm) | 44 x 38 x 248 mm |
| Physical Dimensions - Width/Height/Depth (in.) | 1.75 x 1.5 x 9.75 in. |
| Weight (kg) | 0.77 kg |
| Weight (lb) | 1.70 lbs. |

| SHIPPING DIMENSIONS | |
|---|---------------------------|
| Shipping Dimensions - Width/Height/Depth (cm) | 16.51 x 30.0 x 5.31 cm |
| Shipping Dimensions - Width/Height/Depth (mm) | 165.1 x 299.97 x 53.09 mm |
| Shipping Dimensions - Width/Height/Depth (in) | 6.5 x 11.81 x 2.09 in. |
| Shipping Weight (kg) | 0.98 kg |
| Shipping Weight (lbs.) | 2.15 lbs. |

| CERTIFICATIONS | |
|----------------|---------------------------|
| Environmental | RoHS Compliant |
| Safety | UL1449 3rd Edition cUL |

| WARRANTY | |
|-------------------------------|---------------------------|
| CEG Amount | \$150 ,000 |
| Connected Equipment Guarantee | Lifetime |
| Product Warranty | Limited Lifetime Warranty |