


# HP P22 G4 22 FHD Monitor (1A7E4AA)



## The amazingly affordable business display.

Put your content front and center on the HP P22 G4 FHD Monitor. The stylish, sleek design delivers essential presentation features, visual comfort, and advanced connectivity at a remarkable price point.



### Crisp images for all your content.

Easily navigate documents and spreadsheets and work in multiple applications side by side on the 21.5-inch diagonal Full HD IPS screen with vibrant 1920 x 1080 resolution.

### Stylishly designed.

Complement your workspace with a contemporary display that has a 3-sided micro-edge bezel for practically unlimited sightlines and virtually seamless multi-display[1] setups. See clearly from almost anywhere in the room with 178° viewing angles.

### Versatile connectivity.

Quickly connect to your devices and additional displays through the HDMI and DisplayPort™ connectors. Get legacy device compatibility from the VGA.

## Featuring

### Create an efficient workspace.

Attach your HP PC or select HP Thin Client directly behind the display. [2]

### Adjust your view.

Filter blue light emission and shift colors to a warmer spectrum for more comfortable viewing with HP Low Blue Light mode.

### Place it where you need it.

Free up valuable desk space with mounting options enabled by the 100-mm VESA pattern. [3]

### Responsibly made.

Energy efficiency and environmental sustainability are built into every ENERGY STAR® and TCO certified, EPEAT® 2019 registered, and low halogen display. [5,6]

### Complete the picture.

Customize a total solution with options designed for your display, like the HP S101 Speaker Bar. [4]

## Specifications

Display size (diagonal)	21.5"
Panel technology	IPS
Display size (diagonal)	54.61 cm (21.5")
Aspect ratio	16:9 <sup>[1]</sup>
Native resolution	FHD (1920 x 1080)
Resolutions supported	1024 x 768; 1280 x 1024; 1280 x 720; 1280 x 800; 1366 x 768; 1440 x 900; 1600 x 900; 1680 x 1050; 1920 x 1080; 640 x 480; 720 x 400; 800 x 600
Pixel pitch	0.247 mm
Brightness	250 nits <sup>[1]</sup>
Contrast ratio	1000:1 <sup>[1]</sup>
Response time (typical)	5ms GtG (with overdrive) <sup>[1]</sup>
Minimum dimensions (W x D x H)	49.73 x 4.59 x 30.11 cm (Without stand.)
Minimum dimensions (W x D x H)	19.59 x 1.81 x 11.85 in (Without stand.)
Dimensions With Stand (W x D x H)	49.73 x 21.16 x 45.49 cm
Weight	4.14 kg (With stand.)
Weight	9.12 lb (With stand.)
Display features	Asset control; On-screen controls; Plug and Play; User controls; Low blue light mode; Anti-glare
Display Input Type	1 DisplayPort™ 1.2 in (with HDCP support); 1 HDMI 1.4 (with HDCP support); 1 VGA
Onscreen controls	Brightness; Color control; Exit; Image control; Information; Management; Power control; Input control; Menu control
Display colors	Up to 16.7 million colors supported (through FRC technology)
Display scan frequency (horizontal)	30-86 KHz
Display scan frequency (vertical)	48-75 Hz
Webcam	No integrated camera
Power	Input voltage 100 to 240 VAC
Power consumption	21 W (maximum), 19 W (typical), 0.3 W (standby)
Operating temperature range	5 to 35°C
Operating humidity range	20 to 80% non-condensing
Sustainable impact specifications	Arsenic-free display glass; Low halogen; Mercury-free display backlights; TCO Certified
Certifications and compliances	Australian-New Zealand MEPS; BSMI; CB; CCC; CE; CEL; CSA; EAC; Energy Star; FCC; ICES; ISO 9241-307; KC; KCC; NOM; PSB; TUV-S; UL; VCCI; Vietnam MEPS; WEEE; ISC
Physical security	Security lock-ready <sup>[3]</sup>
UPC number	(A2K) 195122230715; (A2N) 195122230722; (AB0) 195122230739; (AB1) 195122230746; (AB2) 195122230753; (AB4) 195122230760; (ABA) 195122230777; (ABB) 195122230784; (ABG) 195122230791; (ABT) 195122230807; (ABU) 195122230814; (ABV) 195122230821; (ABY) 195122230838; (ACJ) 195122230845; (ACQ) 195122230852; (AKL) 195122230876; (AR6) 195122230883; (UUF) 195122230890; (UUZ) 195122230906
What's in the box	Monitor; DisplayPort™ cable; HDMI cable; VGA cable; AC power cable

## Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

## Messaging Footnotes

[1] Each display sold separately.

[2] HP Desktop Mini, HP Chromebox, and HP Thin Client sold separately. Requires HP B300 PC Mounting Bracket for Monitors, sold separately.

[3] Mounting hardware sold separately.

[4] Each accessory sold separately.

[5] Based on US EPEAT® registration according to IEEE 1680.1-2018 EPEAT®. Status varies by country. Visit [www.epeat.net](http://www.epeat.net) for more information.

[6] External power supplies, power cords, cables and peripherals are not Low Halogen. Service parts obtained after purchase may not be Low Halogen.

## Technical Specifications Footnotes

[1] All specifications represent the typical specifications provided by HP's component manufacturers, actual performance may vary either higher or lower.

[3] Lock is sold separately.

---

© Copyright 2021 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. ENERGY STAR is a registered trademark owned by the U.S. Environmental Protection Agency.

