

UX10

FULLY RUGGED 10.1" TABLET

10.1" IPS FHD LumiBond® 2.0 sunlight display
8th generation Intel® Core™ processor
Intel UHD graphics 620
Full-size 82 key detachable backlit keyboard option
Optional integrated 4G LTE broadband wireless
802.11ac next generation WiFi
Purpose-built tablet with many configurable options
MIL-STD 810G and IP65 certified
Industry-leading bumper-to-bumper warranty



8th Gen Intel Core Processor

With the latest Intel Core i5 or Intel Core i7 processor, the UX10 rugged tablet was designed for speed and efficiency. Clocking in at up to 1.9GHz and with Turbo Boost speeds up to 4.8GHz, the UX10 has the power needed for the most demanding tasks.



Built to Survive

The UX10 features an exterior case that is specifically engineered to protect the computer against drops, shocks, spills, vibration and more. The sealed design of the UX10 protects it against dust and moisture. The UX10 has been independently tested and certified to MIL-STD 810G, IP65 and MIL-STD 461G standards.



Superior Display/Touch Interface

The UX10 features a 10.1" IPS FHD display that utilizes our revolutionary LumiBond 2.0 technology to achieve a display that is more readable, and offers better contrast and more crisp colors than any other rugged tablet display. The 10.1" widescreen display is ideally suited to run Windows and view your apps.



Right-Sized Versatility

UX10's optimized display size and overall ergonomics are readily accepted by workers, which means improved productivity and faster ROI. The UX10 is a purpose-built tablet with many configurable options.



Full-Size 82 Key Detachable Keyboard

Unlike our competitors' products that have small keyboards with small keys, the UX10 features a full-sized 82-key detachable backlit keyboard with standard-sized keys. The UX10 lets you type the way you're used to typing.



Bumper-to-Bumper Warranty

Accidents happen. Only Getac offers bumper-to-bumper coverage standard on every UX10 rugged tablet.

GETAC UX10

Specifications



Getac

GetacSales_US@getac.com
www.getac.com
949.681.2900

Ruggedness	MIL-STD 810G and IP65 certified MIL-STD 461G ready ¹ Vibration & drop resistant e-Mark certified	Communications	10/100/1000 base-T Ethernet Intel Dual Band Wireless-AC 9260 (802.11ac) Bluetooth (v5.0) Optional dedicated GPS Optional 4G LTE mobile broadband with integrated GPS
Operating System	Windows® 10 Professional, 64 bit	Security	Intel vPro™ Technology (per CPU options) TPM 2.0 Optional HF RFID reader Optional LF/HF RFID reader, or Smart Card reader Optional magnetic stripe reader, or fingerprint reader Cable lock slot NIST BIOS compliant Optional Absolute™ DDS software
CPU	Intel® Core™ i7-8665U vPro 1.9 to 4.8GHz processor 8MB Intel Smart Cache Intel Core i7- 8565U 1.8 to 4.6GHz processor 8MB Intel Smart Cache Intel Core i5-8365U vPro 1.6 to 4.1GHz processor 6MB Intel Smart Cache Intel Core i5-8265U 1.6 to 3.9GHz processor 6MB Intel Smart Cache	Power	AC Adapter (65W, 100-240VAC, 50/60Hz) Li-Ion smart battery (11.1V, 4200mAh) x 1 Optional high capacity battery (10.8V, 9240mAh) x 1 Optional bridge battery
Memory	8GB DDR4 expandable to 16GB	Dimensions and Weight	TABLET: 10.82" x 7.51" x 0.88" (275 x 191 x 22.4 mm) 2.68 lbs (1.22 kg) TABLET + OPTIONAL KEYBOARD: 11.22" x 10.43" x 1.53" (285 x 265 x 38.8 mm) 4.58 lbs (2.08 kg) OPTIONAL HIGH CAPACITY BATTERY: (incremental over standard) 0.43" (11mm) ^{††}
Storage	AES SSD 256GB / 512GB / 1TB [†]	Temperature	Operating Temp: -20°F to 145°F / -29°C to 63°C Storage Temp: -60°F to 160°F / -51°C to 71°C Humidity: 95% RH, non-condensing
VGA Controller	Intel UHD Graphics 620	I/O Interfaces	FHD webcam x 1 or Optional Windows Hello face-authentication camera (front-facing) x 1 8M pixels auto focus rear camera x 1 Headphone out / mic-in combo x 1 DC in Jack x 1 USB 3.1 Gen 2 Type-A x 1 HDMI x 1 Docking connector x 1 Optional RF antenna pass-through for GPS, WLAN, and WWAN
Display	10.1" IPS FHD TFT LCD (1920 x 1200) 1000 nits LumiBond™ 2.0 sunlight readable LED display with capacitive 10-point multi-touch technology and hard-tip stylus Optional digitizer	Warranty	3 Year bumper-to-bumper warranty standard [‡]
Keyboard	6 tablet buttons (Windows, Power, Function Key, Camera Capture / Barcode Reader Trigger, Volume Up, Volume Down)		
Expansion Slot	Top Side Tablet Optional 1D/2D imager barcode reader, or serial port, or MicroSD slot, or USB 3.0 Type-A port, or USB 3.1 Gen 1 Type-C port, or LAN port (RJ-45), or VGA port, or HF RFID reader. Right Side Optional magnetic stripe reader, or fingerprint reader, or serial port+LAN port (RJ-45) Back Side Optional LF/HF RFID, or Smart Card reader, or bridge battery, or bridge battery+Smart Card reader		

Specification subject to change without notice.

¹ Requires MIL-STD 461G 90W AC Adapter sold separately.

[†] For storage, 1GB = 1 billion bytes; actual formatted capacity less.

^{††} Weight varies by configuration and manufacturing process.

[‡] 3 year bumper-to-bumper warranty standard. For warranty terms and conditions visit www.getac.com

Copyright 2019, Getac, All Rights Reserved. Getac and the Getac logo are either registered trademarks or trademarks of Getac Technology Corporation in the United States and/or other countries. Microsoft and Windows are registered trademarks of Microsoft Corporation in the United States and in other countries. All other trademarks are the property of their respective owners.