













SPECIFICATIONS

Model Name	GeForce RTX™ 3080 GAMING X TRIO 10G
Graphics Processing Unit	NVIDIA® GeForce RTX™ 3080
Interface	PCI Express® Gen 4
Cores	TBD
Core Clocks	TBD
Memory Speed	TBD
Memory	10GB GDDR6X
Memory Bus	320-bit
Output	DisplayPort x 3 (v1.4a) / HDMI 2.1 x 1
HDCP Support	Y
Power consumption	TBD
Power connectors	8-pin x 3
Recommended PSU	TBD
Card Dimension (mm)	323 x 140 x 56mm
Weight (Card / Package)	TBD
DirectX Version Support	12 API
OpenGL Version Support	4.6
Maximum Displays	4
VR Ready	Y
Digital Maximum Resolution	7680x4320

CONNECTIONS



FEATURES

- 
TRI FROZR 2
 TRI FROZR 2 offers the perfect balance between cool temperatures and quiet fans during endless gaming sessions.
- 
TORX FAN 4.0
 A masterpiece of teamwork, fan blades work in pairs to create unprecedented levels of focused air pressure.
- 
Core Pipe
 Precision-crafted heat pipes ensure max contact to the GPU and spread heat along the full length of the heatsink.
- 
Airflow Control
 Don't sweat it, Airflow Control guides the air to exactly where it needs to be for maximum cooling.
- 
Graphene Backplate
 A composite Graphene backplate reinforces the graphics card while providing passive thermal conduction properties.
- 
Ball Bearing
 Extremely durable double-ball bearings spin your TORX FANS for years of intense gaming sessions in zero noise.
- 
Custom PCB
 The custom PCB has been engineered with hardened circuits and optimized trace routing for performance and reliability.
- 
Dragon Center
 MSI's exclusive Dragon Center software lets you monitor, tweak and optimize MSI products in real-time.
- 
Mystic Light
 Mystic Light gives you complete control of the RGB lighting for MSI devices and compatible RGB products.