

# ThinkStation P620 30E0004WUS

## Product

ThinkStation P620

## Region

NA

## Country/Region

USA

## Machine Type

30E0

## TopSeller

TopSeller

## Processor

AMD Ryzen Threadripper PRO 3955WX (16C / 32T, 3.9 / 4.3GHz, 8MB L2 / 64MB L3)

## Discrete Graphics

NVIDIA Quadro P2200 5GB

## Chipset

AMD WRX80

## Memory

2x 16GB RDIMM DDR4-3200 ECC

## HDD Controller

Integrated SATA controller

## M.2 SSD RAID Controller

Integrated NVMe controller

## Internal Disk Drive

None

## M.2 SSD Drive

1x 512GB SSD M.2 PCIe 3.0 NVMe Opal

## Optical

9.0mm DVD±RW

## Media Reader

15-in-1 Card Reader

## Onboard Ethernet

1x 10GbE RJ-45

## Additional Ethernet

None

## WLAN + Bluetooth

None

## Optional Rear Ports

None

## Chassis Intrusion Switch

Chassis Intrusion Switch

## Cover Lock

Lock Kit with Common Key

## Keyboard

USB Traditional Keyboard, Black, English

## Mouse

USB Calliope Mouse

## Power Supply

1000W Platinum Fixed

## Diagnostic

Front 4-Digit Diagnostic LED

## System Management

AMD PRO

## Operating System

Windows 10 Pro 64, English

## Bundled Software

None

## Base Warranty

3-year, Onsite

## Bundled Service

3Y Premier Support Upgrade from 3Y Onsite (5WS0U26649)

## EAN / UPC / JAN

195348524308

## End of Support

2028-10-04

## Announce Date

2020-09-04

## Notes:

### California Electronic Waste Recycling Fee

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>



[WWW.LENOVO.COM](http://WWW.LENOVO.COM)

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2020. All rights reserved.



# ThinkStation P620 Platform Specifications

Product Specifications Reference (PSREF)

Form factor	33L Tower													
Dimensions	165mm/6.5" W x 460mm/18.1" D x 446mm/17.6" H (with feet)													
Weight	Maximum configuration: 52.91 lb (24kg)													
Processor Support	Processor	# of Cores	# of Threads	Base Frequency	Cache	TDP	Memory Types							
	AMD Ryzen Threadripper PRO 3995WX	64	128	2.7GHz	256MB L3	280W	DDR4-3200							
	AMD Ryzen Threadripper PRO 3975WX	32	64	3.5GHz	128MB L3	280W	DDR4-3200							
	AMD Ryzen Threadripper PRO 3955WX	16	32	3.9GHz	64MB L3	280W	DDR4-3200							
	AMD Ryzen Threadripper PRO 3945WX	12	24	4.0GHz	64MB L3	280W	DDR4-3200							
Processor Sockets	1x Socket sWRX4													
Chipset	AMD WRX80													
Memory Sockets	8 DIMM sockets with 8 channels													
Memory Types	DDR4-3200 RDIMM ECC, 8GB / 16GB / 32GB / 64GB available													
Memory Capacity	512GB with 8 x 64GB DDR4-3200 RDIMMs													
Memory Protection	ECC													
Expansion slots	Slot 1 (CPU)	PCIe 4.0 x16, full height, full length												
	Slot 2 (CPU)	PCIe 4.0 x8, full height, full length												
	Slot 3 (CPU)	PCIe 4.0 x16, full height, full length												
	Slot 4 (CPU)	PCIe 4.0 x16, full height, full length												
	Slot 5 (CPU)	PCIe 4.0 x16, full height, full length												
	Slot 6 (IOH)	PCIe 4.0 x8, full height, full length												
Discrete Graphics Offering	Graphics	Memory	Pow-er	Connector	SLI / NVlink	Max Qty								
	Quadro P620	2GB GDDR5	40W	4xminiDP	-	4								
	Quadro P1000	4GB GDDR5	50W	4xminiDP	-	4								
	Quadro P2200	5GB GDDR5	75W	4xDP	-	4								
	Quadro RTX 4000	8GB GDDR6	160W	3xDP, 1xVirtualLink	-	4								
	Quadro RTX 5000	16GB GDDR6	265W	4xDP, 1xVirtualLink	NVLink	2								
	Quadro RTX 6000	24GB GDDR6	295W	4xDP, 1xVirtualLink	NVLink	2								
	Quadro RTX 8000	48GB GDDR6	295W	4xDP, 1xVirtualLink	NVLink	2								
Storage Controller	Storage Controller	Type	Interface	RAID	Cache									
	Integrated SATA controller	Std	SATA 6Gb/s	0/1/10/5	-									
	Integrated NVMe controller	Std	PCIe NVMe	0/1/10/5	-									
Storage Type	Disk Type	Interface	RPM	Offering										
	3.5" SATA HDD	SATA 6Gb/s	7.2K	1TB/2TB/4TB										
	M.2 PCIe SSD	PCIe 3.0 NVMe	-	256GB/512GB/1TB/2TB										
	M.2 PCIe SSD	PCIe 4.0 NVMe*	-	256GB/512GB/1TB										
* M.2 PCIe 4.0 SSD is available later this year														
Storage Support	Up to 5x 3.5" SATA HDD: • 4x 3.5" HDD bay • 1x Flex Bay (Front Access Storage Enclosure or 5.25" Slim ODD and HDD cage)													
	Up to 11x M.2 SSD: • 2 via onboard M.2 • 8 via two quad M.2 to PCIe adapter (only supports PCIe 3.0 SSD) • 1 via Single M.2 to PCIe adapter (only supports PCIe 3.0 SSD)													
	Power supply													
Power supply	One fixed 1000W, autosensing, 92%, 80 PLUS Platinum qualified													
	Optical													
	Optional one slim optical, DVD or DVD±RW													
Media reader	Optional UHS-II 15-in-1 USB 3.2 Gen 1 reader on flex module													
	Network interfaces													
Integrated one 10GbE ethernet (Marvell AQtion AQN-107). Optional PCIe ethernet or wireless adapters are available														
WLAN + Bluetooth														
Optional Intel Wireless-AC 9260, 2x2, 2.4GHz/5GHz, 802.11ac, Bluetooth 5.1														



# ThinkStation P620



Lenovo