

## Color imageCLASS LBP623Cdw

Print up to 22 ppm

Print up to 8-1/2" x 14"

250-sheet maximum paper capacity

One-year limited warranty standard

The Canon Color imageCLASS LBP623Cdw offers feature-rich capabilities in a high-quality, reliable printer that's ideal for almost any office environment. The 5-line, black-and-white LCD panel allows you to navigate through the menu seamlessly and customize the settings to access the features you use most.

Color  
Compact  
Printer



### WORKFLOW EFFICIENCY

- Supports certain compatible mobile printing solutions.<sup>1</sup>
- Out-of-the-box, standard two-sided printing help to reduce paper consumption.
- Designed for small print jobs with first-print-out time as fast as 10.3 seconds.



### USER EXPERIENCE

- High-capacity, all-in-one cartridge helps reduce overall supply costs.
- Canon's PosterArtist Lite<sup>2</sup> software allows you to design up to legal-sized prints and signage utilizing over 1,300 templates, photos, and clipart with designs to suit a wide variety of business environments.
- Create Wi-Fi<sup>®</sup> Direct hotspot from the printer to establish direct connection to mobile device(s) without the need for an external router.



### SUSTAINABILITY

- A combination of fusing technologies and low-melting-point toner minimizes power requirements and helps achieve lower energy consumption.
- Encourage environmentally conscious work practices by enabling multiple settings that can help save paper and energy.
- ENERGY STAR<sup>®</sup> certified and currently rated EPEAT<sup>®</sup> Silver.<sup>3</sup>

### GENUINE<sup>®</sup> CONSUMABLES

Always look for the Canon anti-counterfeiting hologram on your Canon GENUINE product packaging.



Cartridge	Item No.	Yield
054 Black	3024C001	1,500 Pages
054 H Black	3028C001	3,100 Pages
054 Cyan	3023C001	1,200 Pages
054 H Cyan	3027C001	2,300 Pages
054 Magenta	3022C001	1,200 Pages
054 H Magenta	3026C001	2,300 Pages
054 Yellow	3021C001	1,200 Pages
054 H Yellow	3025C001	2,300 Pages

Use of Canon GENUINE toner cartridges helps provide longer equipment life, high yields, reliable performance, high-quality output, and minimal jamming or issues.

### EXTENDED SERVICE PLANS AVAILABLE FOR PURCHASE

#### Canon eCarePAK (Exchange/Carry-In)

Canon Extended Service Plans offer coverage beyond the standard one-year warranty,<sup>4</sup> up to four years. Canon's service and support network is 100% U.S.-based.

One-Year: 5707B042  
Two-Year: 5707B043  
Three-Year: 5707B044  
Four-Year: 5707B045



**eCarePAK**  
Extended Service Plan

**Main Unit****Core Functions**

Standard: Print

**Item Code**

3104C023

**Processor**

Canon Custom Processor

**Control Panel**

5-line LCD

**Memory**

1 GB

**Standard Interface Connection**

USB 2.0 x2 (Host), USB 2.0 x1 (Device) High-Speed, 10/100/1000Base-T Ethernet (Network), Wi-Fi 802.11b/g/n, Wi-Fi® Direct Connection

**Paper Capacity (Letter, 20 lb. Bond)**

Standard: 250 Sheets

**Paper Sources (Letter, 20 lb. Bond)**

Standard: 250-sheet Paper Cassette, 1-sheet Stack Bypass

**Paper Output Capacity (Letter, 20 lb. Bond)**

Standard: 75 Sheets

**Supported Media Types**Cassettes: Thin, Plain, Recycled, Color, Thick, Coated, Label, Letter, Envelope (10 Envelopes)  
Manual Feed: Thin, Plain, Recycled, Color, Thick, Coated, Slot: Label, Letter, Envelope (1 Envelope)**Supported Media Sizes**Cassettes: Letter, Legal, Statement, Executive, Envelope: COM10, Monarch, C5, DL, Custom (Min. 3" x 5" to Max. 8.5" x 14")  
Manual Feed: Letter, Legal, Statement, Executive Slot: Envelope: COM10, Monarch, C5, DL Custom (Min. 3" x 5" to Max. 8.5" x 14")**Supported Media Weights**Cassettes: 16 lb. Bond to 53 lb. Bond (60 to 200 g/m<sup>2</sup>)  
Manual Feed: 16 lb. Bond to 53 lb. Bond (60 to 200 g/m<sup>2</sup>)  
Slot:**Warm-up Time**From Power On: 13 Seconds or Less  
From Sleep: 6.1 Seconds or Less  
Mode:**Dimensions (W x D x H)**Standard: 17.2" x 16.8" x 11.5"  
(Desktop): (437 mm x 425 mm x 292 mm)  
Box: 21.8" x 22.2" x 15"  
(553 mm x 564 mm x 381 mm)**Installation Space (W x D x H)**Standard: 17.0" x 40.0" x 11.3"  
(Desktop): (430 mm x 1011 mm x 287 mm)**Weight<sup>5</sup>**Unit: Approx. 35.2 lb. (16.0 kg)  
Boxed Weight: Approx. 41.8 lb. (19.0 kg)**Supported OS**

Windows® 10/Windows 8.1/Windows 7/Windows Server 2008/Windows Server 2008 R2/Windows Server 2012/Windows Server 2012 R2/Windows Server 2016/Mac OS X v10.9.5 (or later)

**What Comes In The Box**

LBP623Cdw Product, Cartridge 054 CMY Starter: 680 Yield/Black Starter: 910 Yield, Power Cord, Starter Guide, User Software DVD-ROM, Warranty Card

**Print Specifications****Printing Method**

Laser Beam Printing

**Print Speed (BW/Color)<sup>6</sup>**

Up to 22 ppm (Letter); Up to 17.9 ppm (Legal)

**First-Print-Out Time**

Approx. 10.3 Seconds

**Recommended Monthly Page Volume**

150 - 2,500 Pages

**Print Resolution (dpi)**

600 x 600

**Standard Page Description Languages**

UFR II, PCL®6, PCL®5, Adobe® PostScript® 3™

**Double-Sided Printing**

Automatic (Standard)

**Direct Print**

Available from USB Memory (JPEG, TIFF, PDF)

**Printing from Mobile and Cloud-based Services<sup>1</sup>**

Apple® AirPrint®, Canon PRINT Business, Mopria™ Print Service

**Available Software for Download**

Print Drivers, MF Scan Utility, PosterArtist Lite 3.20.00

**Security Specifications****Authentication**

Standard: Department ID Authentication

**Network**

Standard: IP/MAC Address Filtering, IPSEC, TLS Encrypted Communication, SNMP V3.0, IEEE 802.1X(Wired Only), IPv6, SMTP Authentication, POP Authentication, POP Authentication before SMTP

**Document**

Standard: Secure Print

**Wi-Fi Authentication Methods**Wi-Fi: WEP 64/128 bit, WPA-PSK (TKIP/AES), Infrastructure: WPA2-PSK (AES)  
Mode:  
Wi-Fi Access: WPA2-PSK (AES)  
Point:**Environmental Specifications****Operating Environment**Temperature: 50 to 86° F  
Humidity: 20 to 80% RH (no condensation)**Power Requirements**

AC 120-127 V:6.5 A, 60 Hz

**Power Consumption**Maximum: Approx. 900 W  
Standby: Approx. 7.9 W  
Sleep Mode: Approx. 0.7 W  
Typical: 0.21 kWh  
Electricity Consumption (TEC) Rating:**Standards**ENERGY STAR® Qualified, Rated EPEAT Silver<sup>3</sup>

<sup>1</sup> Canon PRINT Business is a free app available on the App Store® and Google Play™ Store. For more information, including compatibility, please visit <https://www.usa.canon.com/mobile-app>. Please see the respective websites for Apple AirPrint and Mopria Print Service for compatibility and additional information.

<sup>2</sup> Please visit [www.usa.canon.com/support](http://www.usa.canon.com/support) to download software.

<sup>3</sup> For latest EPEAT rating (Gold/Silver/Bronze), please visit [www.epeat.net](http://www.epeat.net).

<sup>4</sup> Limited warranty program is subject to certain conditions and restrictions. See warranty card for details.

<sup>5</sup> Includes consumables.

<sup>6</sup> Print speed is based on internal testing. Print speed may vary, depending on the number of copies selected as well as the settings for size, type, and orientation of paper.



As an ENERGY STAR partner, Canon U.S.A., Inc. has qualified this model as meeting the ENERGY STAR energy efficiency criteria through an EPA recognized certification body. ENERGY STAR and the ENERGY STAR mark are registered U.S. marks. Canon, imageCLASS, and the GENUINE logo are registered trademarks of Canon Inc. in the United States and may also be registered trademarks or trademarks in other countries. Wi-Fi is a registered trademark of the Wi-Fi Alliance. Android and Google Play are trademarks of Google Inc. Mac and the App Store are trademarks of Apple Inc., registered in the United States and/or other countries. AirPrint and the AirPrint logo are trademarks of Apple Inc. Mopria and the Mopria logo are trademarks of the Mopria Alliance, Inc. Windows and Windows Server are trademarks of Microsoft Inc. in the United States and/or other countries. All other referenced product names and marks are trademarks of their respective owners. Canon products offer certain security features, yet many variables can impact the security of your devices and data. Canon does not warrant that use of these features will prevent security issues. Nothing herein should be construed as legal or regulatory advice concerning applicable laws; customers must have their own qualified counsel determine the feasibility of a solution as it relates to regulatory and statutory compliance. Specifications and availability subject to change without notice. Not responsible for typographical errors.

©2020 Canon U.S.A., Inc. All rights reserved.

0920-iCLBP623-PDF-IH

